




PHILIPS  
LED  
Bulb (Dimmable)  
4W (25W)  
E26  
Cool White  
Dimmable



046677543112

## Designed to be seen

New contemporary twist to the industrial lighting trend featuring a portfolio of highly-stylized, giant lument LED bulbs that are designed to be seen.

### Long life

- Long life bulbs - Lasts up to 15 years

### Create a warm atmosphere

- Dimmable

### High quality light

- Cool, white light

### Modern Style

- Modern style LED

### Vintage style, modern LED technology

- Bulb as a fixture

# PHILIPS

# Highlights

## 15,000-hour rated average life



With a lifetime of up to 15,000 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 15 years.

### Dimmable

This bulb can be used with most dimmers to create your desired ambience with smooth dimming to 10% of full light levels. Please check the dimmability compatibility chart to be certain that your particular dimmer can be used with this bulb.

## Cool, white light



This bulb has a color temperature of 4000K providing you with an extra cool, fresh and crisp light.

### Modern

Modern design for contemporary interior décor, with a unique sleek look perfect for any home with an industrial/chic feel. It features a smoky grey glass with a thin, single vertical filament and a black finish base to match your décor. Cooler light output for crisp and clean ambience.

## Bulb as a Fixture

New contemporary twist to the industrial lighting trend, featuring a portfolio of highly stylized giant filament LED bulbs that are designed to be seen. Use with hanging pendant or cord lights to highlight the beauty of the bulb itself.

# Specifications

## Bulb characteristics

- Dimmable: Yes
- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: E26
- Technology: LED

## Bulb dimensions

- Height: 10.8 cm
- Weight: 0.03 kg
- Width: 6 cm

## Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 20,000

## Light characteristics

- Color consistency: 6SDCM
- Color rendering index (CRI): 80
- Color temperature: 4000 K
- Light Color Category: Cool White
- Nominal luminous flux: 150 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light

## Miscellaneous

- EyeComfort: Yes

## Other characteristics

- Lamp current: 40 mA
- Mercury content: 0 mg
- Efficacy: 37 lm/W

**Packaging information**

- EAN: 046677543112
- EOC: 543116
- Product title:  
4A19/MOD/840/E26/CL/GL/DIM  
4/1BC

**Power consumption**

- Power factor: 0.7
- Voltage: 120 V
- Wattage: 4 W
- Wattage equivalent: 25 W

**Rated values**

- Rated lifetime: 15,000 hour(s)
- Rated luminous flux: 150 lumen
- Rated power: 4 W

**Packaging dimensions and weight**

- EAN/UPC - product: 046677543112
- Net weight: 0.062 kg
- Gross weight: 0.081 kg
- Height: 18.400 cm
- Length: 6.600 cm
- Width: 14.000 cm
- SAP EAN/UPC - Piece: 046677543112
- Material number (12NC):  
929002000703
- EAN/UPC - Case: 50046677543117
- SAP Gross Weight EAN (Piece): 0.081  
kg
- Net Weight: 0.062 kg
- SAP Height (Piece): 18.400 cm
- SAP Length (Piece): 6.600 cm
- SAP Width (Piece): 14.000 cm



Issue date: 2020-02-20  
Version: 0.395

© 2020 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)