

# PHILIPS

Linear tube

LED

11.5W-25W

G13

Daylight

046677544232



## LED tube that works directly from your power line

Eliminate ballast maintenance with Philips MainsFit LED tubes. This T8 tube is designed to replace T8 and T12 tubes on shunted and non-shunted sockets, looks and feels like fluorescent, and has a bright white light with long lifetime.

### High quality light

- Cool, energizing light

### Choose a simple replacement for your old bulbs

- Perfect replacement T8 linear fluorescent application

### Choose for a sustainable solution

- You can trust what the Philips packaging is saying.

# Highlights

## 3500K [LED Lamps]



This bulb has a color temperature of 3500K providing you with a cool, energizing light, perfect for creating an inviting ambiance to host friends or wind down with a book.

## No UV or IR

The beam of light is free of infra-red meaning no heat is radiated, and no ultra-violet light means that fabric and items under this light won't fade.

## Similar to linear fluorescents

The perfect quick and easy replacement for T8 linear fluorescent tubes. It fits directly into standard T8 linear fluorescent G13 sockets.

# Specifications

## Bulb characteristics

- Dimmable: Non Dimmable
- Intended use: Indoor
- Lamp shape: Linear tube
- Socket: G13
- Technology: LED
- Lamp shape code: T8
- Control: On/off switch

## Bulb dimensions

- Height: 90.88 cm
- Width: 2.59 cm

## Durability

- Average life (at 2.7 hrs/day): 51 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 50,000 hour(s)
- Number of switch cycles: 50,000

## Light characteristics

- Application: Task lighting
- Beam angle: 180 degree(s)
- Color consistency: 5SDCM
- Color rendering index (CRI): 82
- Color temperature: 5000 K
- Light Color Category: Daylight
- Nominal luminous flux: 1400 lumen
- Starting time: <0.9 s
- Warm-up time to 60% light: Instant full light

## Other characteristics

- Lamp current: 47~101 mA
- Efficacy: 121 lm/W

## Packaging information

- Product family: MainsFit
- EAN: 046677544232
- EOC: 544239
- Product title: 11.5T8/COR/36-850/MF14/G 1/4 SIOC

## Power consumption

- Power factor: >0.9
- Voltage: 120-277 V
- Wattage: 11.5 W
- Wattage equivalent: 25 W

## Product dimensions & weight

- Length: 90.88 cm

## Rated values

- Rated beam angle: 180 degree(s)
- Rated lifetime: 50,000 hour(s)
- Rated luminous flux: 1400 lumen
- Rated power: 11.5 W

## Technical specifications

- Frequency: 50-60 Hz

## Packaging dimensions and weight

- EAN/UPC - product: 046677544232
- Net weight: 1.600 kg
- Gross weight: 2.500 kg
- Height: 8.700 cm
- Length: 19.200 cm
- Width: 95.500 cm
- Material number (12NC): 929001934523



Issue date: 2023-11-08  
Version: 0.202

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)