

PHILIPS

Linear tube

LED

16W-25-28-30-32W

G13

Cool White

046677544249



Simple T8 LED replacement for fluorescent tubes

Philips InstantFit LED tubes easily replace fluorescent T8 tubes operated on instant-start electronic ballasts, no rewiring needed. This glass LED linear bulb looks and feels like fluorescent and has a daylight effect and long lifetime.

High quality light

- Cool, white light

Choose a simple replacement for your old bulbs

- Perfect replacement T8 linear fluorescent application

Choose for a sustainable solution

- You can trust what the Philips packaging is saying.

Highlights

Cool, white light



This bulb has a color temperature of 4000K providing you with an extra cool, fresh and crisp light.

Similar to linear fluorescents

The perfect quick and easy replacement for T8 linear fluorescent tubes. It fits directly into standard T8 linear fluorescent G13 sockets.

No UV or IR

The beam of light is free of infra-red meaning no heat is radiated, and no ultra-violet light means that fabric and items under this light won't fade.

Specifications

Bulb characteristics

- Dimmable: Non Dimmable
- Intended use: Indoor
- Lamp shape: Linear tube
- Socket: G13
- Technology: LED
- Lamp shape code: T8
- Control: On/off switch

Bulb dimensions

- Height: 121.23 cm
- Weight: 0.22 kg
- Width: 2.78 cm

Durability

- Average life (at 2.7 hrs/day): 37 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 36,000 hour(s)
- Number of switch cycles: 50,000

Light characteristics

- Application: Task lighting
- Color consistency: 6SDCM
- Color rendering index (CRI): 80
- Color temperature: 4000 K
- Light Color Category: Cool White
- Nominal luminous flux: 1800 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light

Other characteristics

- Lamp current: 110-330 mA
- Efficacy: 112 lm/W

Packaging information

- Product family: InstantFit
- EAN: 046677544249
- EOC: 544247
- Product title: 16T8/LED/48-840/IF18/G 1/8 SIOC

Power consumption

- Power factor: >0.9
- Voltage: 120-277, 347 V
- Wattage: 16 W
- Wattage equivalent: 25-28-30-32 W

Product dimensions & weight

- Length: 121.23 cm

Rated values

- Rated beam angle: 240 degree(s)
- Rated lifetime: 36,000 hour(s)
- Rated luminous flux: 1800 lumen
- Rated power: 16 W

Technical specifications

- Frequency: 20-120 Hz

Packaging dimensions and weight

- EAN/UPC - product: 046677544249
- Net weight: 2.500 kg
- Gross weight: 4.400 kg
- Height: 15.500 cm
- Length: 128.400 cm
- Width: 24.700 cm
- Material number (12NC): 929001960623



Issue date: 2023-11-08
Version: 0.202

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com