

PHILIPS

Spot (Dimmable)

LED

4W-50W

GU10

Bright White Light

Dimming

046677544935



Dimmable LED light with a focused bright beam

Philips dimmable LED GU10 spot light bulbs are a long lasting, energy efficient replacement for halogen spots. They have a bright white light and are ideal for accent lighting in recessed, track, and decorative fixtures.

High quality light

- Designed for the comfort of your eyes

Light beyond illumination

- Dimmable
- Instant on

Highlights

Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get the glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Instant on

Dimmable

This bulb can be used with most dimmers to create your desired ambience with smooth dimming to 10% of full light levels. Please check the dimmability compatibility chart to be certain that your particular dimmer can be used with this bulb.

Specifications

Bulb characteristics

- Dimmable: Yes
- Intended use: Indoor
- Lamp shape: Spot
- Socket: GU10
- Lamp shape code: MR16
- Control: Wall dimmer ; On/off switch

Durability

- Nominal lifetime: 25,000 hour(s)
- Number of switch cycles: 50,000

Light characteristics

- Application: Task lighting, Accent lighting
- Color rendering index (CRI): 90
- Nominal luminous flux: 380 lumen

Other characteristics

- Lamp current: 50 mA
- Efficacy: 95 lm/W

Power consumption

- Power factor: 0.7

Product dimensions & weight

- Length: 5.4 cm

Rated values

- Rated beam angle: 35 degree(s)
- Rated peak intensity: 600 cd
- Rated power: 4 W

Technical specifications

- Frequency: 50-60 Hz

Bulb characteristics

- Application: Task lighting, Accent lighting
- EAN/UPC - product: 046677544935
- Rated beam angle: 35 degree(s)
- Lamp current: 50 mA
- Net weight: 0.147 kg
- Intended use: Indoor
- Gross weight: 0.167 kg
- Lamp shape: Spot
- Color rendering index (CRI): 90
- Height: 19.200 cm
- Rated peak intensity: 600 cd
- Socket: GU10
- Number of switch cycles: 50,000
- Length: 11.200 cm
- Power factor: 0.7
- Rated power: 4 W
- Width: 4.800 cm
- Nominal luminous flux: 380 lumen
- Length: 5.4 cm
- Lamp shape code: MR16
- Control: Wall dimmer ; On/off switch
- Frequency: 50-60 Hz



Issue date: 2022-05-11
Version: 0.144

© 2022 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com