




PHILIPS
LED
Reflector (Dimmable)
8.5W-75W
E26
Dimming



046677546793

The more you dim, the warmer the light

Not all LEDs dim the same. Philips dimmable LED PAR30L spot light bulbs with a warm glow effect work like halogen bulbs by getting warmer in tone when dimmed. Other LED bulbs simply get less bright, without a cozy glow.

High quality light

- Designed for the comfort of your eyes

Choose a simple replacement for your old bulbs

- Similar shape and size as halogen reflector

Light beyond illumination

- Instant on

PHILIPS

Highlights

Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get

the glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Instant on

Replaces halogen spot



With its beautifully shaped design and familiar dimensions, this is a modern lighting, LED reflector. The perfect sustainable replacement for traditional halogen reflectors.

Specifications

Bulb characteristics

- Dimmable: Dimmable
- Intended use: Indoor
- Lamp shape: Reflector
- Socket: E26
- Technology: LED
- Lamp shape code: PAR30L

Bulb dimensions

- Height: 11.6 cm
- Weight: 0.24 kg
- Width: 9.4 cm

Durability

- Average life (at 2.7 hrs/day): 25 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 25,000 hour(s)
- Number of switch cycles: 50,000

Light characteristics

- Application: Task lighting, Accent lighting
- Beam angle: 40 degree(s)
- Color consistency: 4SDCM
- Color rendering index (CRI): 90
- Color temperature: 2200-3000 K
- Starting time: 0.5 s
- Warm-up time to 60% light: Instant full light

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Lamp current: 80 mA
- Mercury content: 0 mg
- Efficacy: 100 lm/W

Packaging information

- Product family: Warm Glow
- EAN: 046677546793
- EOC: 546796
- Product title: 8.5PAR30L/LED/930-22/F40/WG/G T20 4/1BC

Power consumption

- Power factor: 0.8
- Voltage: 120 V
- Wattage: 8.5 W
- Wattage equivalent: 75 W

Rated values

- Rated beam angle: 40 degree(s)
- Rated lifetime: 25,000 hour(s)
- Rated peak intensity: 1315 cd
- Rated power: 8.5 W

Packaging dimensions & weight

- SAP EAN/UPC - Piece: 046677546793
- EAN/UPC - Case: 50046677546798
- SAP Gross Weight EAN (Piece): 0.294 kg
- Net Weight: 0.256 kg
- SAP Height (Piece): 22.400 cm
- SAP Length (Piece): 9.900 cm
- SAP Width (Piece): 15.500 cm



Issue date: 2019-12-09
Version: 0.126

© 2019 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com