


PHILIPS  
LED  
Bulb (Dimmable)  
8W-60W  
E26  
Dimming

046677549497



# The right light makes the moment

Philips LEDs with a dimmable warm glow effect, enables light levels to dim to the warm tones of traditional bulbs. You can change the ambience from functional lighting to an inviting and cozy atmosphere.

#### **Add a beautiful sparkle to your home**

- Classic glass LED

#### **Choose a simple replacement for your old bulbs**

- Similar shape and size as standard incandescent bulb

#### **Choose for a sustainable solution**

- Long life bulbs - Lasts up to 15 years
- Saves up to 80% Energy

# PHILIPS

**High quality LED light that lasts for decades**

- Designed for the comfort of your eyes

# Highlights

## Glass Design

The look you love, the performance you expect. Classic glass designs replicate the beautiful.

## Replaces standard incandescent

With its beautiful design and familiar shape, this energy-saving LED bulb is the perfect sustainable replacement for traditional incandescent bulbs.

## 15,000-hour rated average life



With a lifetime of up to 15,000 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 15 years.

## Saves up to 80% Energy



Enjoy the energy-savings of LEDs without sacrificing light quality. Instantly save over 80% in energy by replacing your existing incandescent or halogen bulbs

## Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

# Specifications

## Bulb characteristics

- Dimmable: Yes
- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: E26
- Technology: LED
- Type of glass: Clear

## Bulb dimensions

- Height: 10.8 cm
- Weight: 0.04 kg
- Width: 6 cm

## Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 20,000

## Light characteristics

- Beam angle: 300 degree(s)
- Color consistency: 4SDCM
- Color rendering index (CRI): 90
- Color temperature: 2700-2200 K
- Nominal luminous flux: 800 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light

## Miscellaneous

- EyeComfort: Yes

## Other characteristics

- Lamp current: 85 mA
- Mercury content: 0 mg
- Efficacy: 100 lm/W

**Packaging information**

- EAN: 046677549497
- EOC: 549493
- Product title: 8A19/PER/927-922/CL/G/E26/WGX 1FB T20

**Power consumption**

- Power factor: 0.75
- Voltage: 120 V
- Wattage: 8 W
- Wattage equivalent: 60 W

**Rated values**

- Rated beam angle: 300 degree(s)
- Rated lifetime: 15,000 hour(s)
- Rated luminous flux: 800 lumen
- Rated power: 8 W

**Packaging dimensions & weight**

- SAP EAN/UPC - Piece: 046677549497
- EAN/UPC - Case: 50046677549492
- SAP Gross Weight EAN (Piece): 0.052 kg
- Net Weight: 0.030 kg
- SAP Height (Piece): 12.000 cm
- SAP Length (Piece): 6.600 cm
- SAP Width (Piece): 6.600 cm



Issue date: 2019-12-09  
Version: 0.131

© 2019 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)