

# PHILIPS

Bulb (Dimmable)

LED

8.8W-60W

E26

Daylight

Dimming

046677550233



## Bright LED lighting with excellent light quality

Familiar shapes you know and love. They use around 80% less energy than traditional light bulbs and last ten times longer.

### **Choose a simple replacement for your old bulbs**

- Similar shape and size as standard incandescent bulb

### **Choose for a sustainable solution**

- Long life bulbs - Lasts up to 15 years
- Saves up to 80% Energy

# Highlights

## Replaces standard incandescent

With its beautiful design and familiar shape, this energy-saving LED bulb is the perfect sustainable replacement for traditional incandescent bulbs.

## 15,000-hour rated average life



With a lifetime of up to 15,000 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 15 years.

## Saves up to 80% Energy



Enjoy the energy-savings of LEDs without sacrificing light quality. Instantly save over 80% in energy by replacing your existing incandescent or halogen bulbs

# Specifications

## Bulb characteristics

- Dimmable: Yes
- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: E26
- Technology: LED
- Type of glass: Clear

## Bulb dimensions

- Height: 10.8 cm
- Weight: 0.04 kg
- Width: 6 cm

## Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 20,000

## Light characteristics

- Color consistency: 4SDCM
- Color rendering index (CRI): 90
- Color temperature: 5000 K
- Light Color Category: Daylight
- Nominal luminous flux: 800 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light

## Miscellaneous

- EyeComfort: Yes

## Other characteristics

- Lamp current: 105 mA
- Efficacy: 90 lm/W

## Packaging information

- EAN: 046677550233
- EOC: 550236
- Product title:  
8.8A19/PER/950/CL/G/E26/DIM  
4/2BCT20

**Power consumption**

- Energy Star Certified: Yes
- Power factor: 0.7
- Voltage: 120 V
- Wattage: 8.8 W
- Wattage equivalent: 60 W

**Product dimensions & weight**

- Length: 10.8 cm

**Rated values**

- Rated lifetime: 15,000 hour(s)
- Rated luminous flux: 800 lumen
- Rated power: 8.8 W

**Technical specifications**

- Frequency: 60 Hz

**Bulb characteristics**

- EAN/UPC - product: 046677550233
- Height: 10.8 cm
- Average life (at 2.7 hrs/day): 15 year(s)
- Lamp current: 105 mA
- Net weight: 0.064 kg
- Rated lifetime: 15,000 hour(s)
- Intended use: Indoor
- Weight: 0.04 kg
- Lumen maintenance factor: 70%
- Color consistency: 4SDCM
- Gross weight: 0.100 kg
- EAN: 046677550233
- Energy Star Certified: Yes
- Rated luminous flux: 800 lumen
- Lamp shape: Non directional bulb
- Width: 6 cm
- Color rendering index (CRI): 90
- Height: 22.400 cm
- EOC: 550236
- Socket: E26
- Number of switch cycles: 20,000
- Color temperature: 5000 K
- EyeComfort: Yes
- Length: 6.600 cm
- Product title:  
8.8A19/PER/950/CL/G/E26/DIM  
4/2BCT20
- Power factor: 0.7
- Rated power: 8.8 W
- Technology: LED
- Light Color Category: Daylight
- Width: 15.500 cm
- Voltage: 120 V
- Type of glass: Clear
- Nominal luminous flux: 800 lumen
- Material number (12NC):  
929002207903
- Wattage: 8.8 W
- Length: 10.8 cm
- Starting time: <0.5 s
- Wattage equivalent: 60 W
- Warm-up time to 60% light: Instant  
full light
- Frequency: 60 Hz



Issue date: 2022-06-12  
Version: 0.204

© 2022 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)