



PHILIPS  
LED  
Reflector (Dimmable)  
8.5W-75W  
E26  
Daylight  
Dimming



04667755311

## Dimmable LED light with a focused bright beam

Philips dimmable LED PAR spot light bulbs are a long lasting, energy efficient replacement for halogen spots. They have a day light effect and are ideal for general and flood lighting.

### Dimmable

- Dimmable

### Instant on

- Instant on

### Comfortable LED light that is easy on your eyes

- Designed for the comfort of your eyes

**PHILIPS**

# Highlights

## Dimmable

This bulb can be used with most dimmers to create your desired ambience with smooth dimming to 10% of full light levels. Please check the dimmability compatibility chart to be certain that your particular dimmer can be used with this bulb.

## Instant on Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get the glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

# Specifications

## Bulb characteristics

- Dimmable: Yes
- Intended use: Indoor
- Lamp shape: Directional reflector
- Socket: E26
- Technology: LED

## Bulb dimensions

- Height: 116 mm
- Weight: 0.24 kg
- Width: 94 mm

## Durability

- Average life (at 2.7 hrs/day): 25 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 25,000 hour(s)
- Number of switch cycles: 50,000

## Light characteristics

- Beam angle: 40 degree(s)
- Color consistency: 4SDCM
- Color rendering index (CRI): 90
- Color temperature: 5000 K
- Light Color Category: Daylight
- Starting time: 0.5 s
- Warm-up time to 60% light: Instant full light

## Miscellaneous

- EyeComfort: Yes

## Other characteristics

- Lamp current: 80 mA
- Mercury content: 0 mg
- Lamp current: 100 lm/W

## Packaging information

- EAN: 046677553111
- EOC: 553115
- Product title: 8.5PAR30L/LED/950/F40/DIM/G T20 4/1BC

## Power consumption

- Power factor: 0.8
- Voltage: 120 V
- Wattage: 8.5 W
- Wattage equivalent: 75 W

## Rated values

- Rated beam angle: 40 degree(s)
- Rated lifetime: 25,000 hour(s)
- Rated peak intensity: 1315 cd
- Rated power: 8.5 W

## Packaging dimensions & weight

- SAP EAN/UPC - Piece: 046677553111
- EAN/UPC - Case: 50046677553116
- SAP Gross Weight EAN (Piece): 0.294 kg
- Net Weight (Piece): 0.256 kg
- SAP Height (Piece): 22.400 cm
- SAP Length (Piece): 9.900 cm
- SAP Width (Piece): 15.500 cm



Issue date: 2019-09-10  
Version: 0.65

© 2019 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)