

PHILIPS

Reflector

LED

10W-90W

E26

Bright White Light

046677553586



Long lasting LED light with a focused bright beam

Philips LED PAR spot light bulbs are a perfect replacement for your halogen spots. They have a warm halogen-like light with the performance and long life you expect from LED technology. Ideal for general and flood lighting.

Choose a simple replacement for your old bulbs

- Similar shape and size as halogen reflector

Choose for a sustainable solution

- You can trust what the Philips packaging is saying.

Light beyond illumination

- Instant on

Highlights

Replaces halogen spot



With its beautifully shaped design and familiar dimensions, this is a modern lighting, LED reflector. The perfect sustainable replacement for traditional halogen reflectors.

No UV or IR

The beam of light is free of infra-red meaning no heat is radiated, and no ultra-violet light means that fabric and items under this light won't fade.

Instant on

Specifications

Bulb characteristics

- Dimmable: Non Dimmable
- Intended use: Indoor, Outdoor
- Lamp shape: Reflector
- Socket: E26
- Technology: LED
- Lamp shape code: PAR38
- Control: On/off switch

Bulb dimensions

- Height: 12.9 cm
- Weight: 0.368 kg
- Width: 12.2 cm

Durability

- Average life (at 2.7 hrs/day): 11 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 11,000 hour(s)
- Number of switch cycles: 50,000

Light characteristics

- Application: Task lighting, Accent lighting
- Beam angle: 40 degree(s)
- Color consistency: 4SDCM
- Color rendering index (CRI): 90
- Color temperature: 3000 K
- Light Color Category: Bright White Light
- Nominal luminous flux: 900 lumen
- Warm-up time to 60% light: Instant full light

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Lamp current: 97 mA
- Efficacy: 90 lm/W

Packaging information

- EAN: 046677553586
- EOC: 553552
- Product title:
10PAR38/LED/930/F40/ND/G/ULW
T20 4/2FB

Power consumption

- Power factor: 0.8
- Voltage: 120 V
- Wattage: 10 W
- Wattage equivalent: 90 W

Product dimensions & weight

- Length: 12.9 cm

Rated values

- Rated beam angle: 40 degree(s)
- Rated lifetime: 11,000 hour(s)
- Rated peak intensity: 1533 cd
- Rated power: 10 W

Technical specifications

- Frequency: 50-60 Hz

Bulb characteristics

- Application: Task lighting, Accent lighting
- EAN/UPC - product: 046677553586
- Rated beam angle: 40 degree(s)
- Height: 12.9 cm
- Average life (at 2.7 hrs/day): 11 year(s)
- Beam angle: 40 degree(s)
- Lamp current: 97 mA
- Net weight: 0.772 kg
- Rated lifetime: 11,000 hour(s)
- Intended use: Indoor, Outdoor
- Weight: 0.368 kg
- Lumen maintenance factor: 70%
- Color consistency: 4SDCM
- Gross weight: 0.840 kg
- EAN: 046677553586
- Lamp shape: Reflector
- Width: 12.2 cm
- Color rendering index (CRI): 90
- Height: 11.500 cm
- EOC: 553552
- Rated peak intensity: 1533 cd
- Socket: E26
- Number of switch cycles: 50,000
- Color temperature: 3000 K
- EyeComfort: Yes
- Length: 13.100 cm
- Product title: 10PAR38/LED/930/F40/ND/G/ULW T20 4/2FB
- Power factor: 0.8
- Rated power: 10 W
- Technology: LED
- Light Color Category: Bright White Light
- Width: 21.500 cm
- Voltage: 120 V
- Nominal luminous flux: 900 lumen
- Material number (12NC): 929001949563
- Wattage: 10 W
- Length: 12.9 cm
- Wattage equivalent: 90 W
- Lamp shape code: PAR38
- Warm-up time to 60% light: Instant full light
- Control: On/off switch
- Frequency: 50-60 Hz



Issue date: 2022-06-12
Version: 0.150

© 2022 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com