

# PHILIPS

Reflector

LED

10W-90W

E26

Bright White Light

046677553586



## Long lasting LED light with a focused bright beam

Philips LED PAR spot light bulbs are a perfect replacement for your halogen spots. They have a warm halogen-like light with the performance and long life you expect from LED technology. Ideal for general and flood lighting.

### Choose a simple replacement for your old bulbs

- Similar shape and size as halogen reflector

### Choose for a sustainable solution

- You can trust what the Philips packaging is saying.

### Light beyond illumination

- Instant on

# Highlights

## Replaces halogen spot



With its beautifully shaped design and familiar dimensions, this is a modern lighting, LED reflector. The perfect sustainable replacement for traditional halogen reflectors.

## No UV or IR

The beam of light is free of infra-red meaning no heat is radiated, and no ultra-violet light means that fabric and items under this light won't fade.

## Instant on

# Specifications

## Bulb characteristics

- Dimmable: Non Dimmable
- Intended use: Indoor, Outdoor
- Lamp shape: Reflector
- Socket: E26
- Technology: LED
- Lamp shape code: PAR38
- Control: On/off switch

## Bulb dimensions

- Height: 12.9 cm
- Weight: 0.368 kg
- Width: 12.2 cm

## Durability

- Average life (at 2.7 hrs/day): 11 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 11,000 hour(s)
- Number of switch cycles: 50,000

## Light characteristics

- Application: Task lighting, Accent lighting
- Beam angle: 40 degree(s)
- Color consistency: 4SDCM
- Color rendering index (CRI): 90
- Color temperature: 3000 K
- Light Color Category: Bright White Light
- Nominal luminous flux: 900 lumen
- Warm-up time to 60% light: instant full light

## Miscellaneous

- EyeComfort: Yes

## Other characteristics

- Lamp current: 97 mA
- Efficacy: 90 lm/W

## Packaging dimensions and weight

- Net weight: 0.772 kg

## Packaging information

- EAN: 046677553586
- EOC: 553552
- Product title:  
10PAR38/LED/930/F40/ND/G/ULW  
T20 4/2FB

## Power consumption

- Power factor: 0.8
- Voltage: 120 V
- Wattage: 10 W
- Wattage equivalent: 90 W

## Product dimensions & weight

- Length: 12.9 cm

## Rated values

- Rated beam angle: 40 degree(s)
- Rated lifetime: 11,000 hour(s)
- Rated peak intensity: 1533 cd
- Rated power: 10 W

## Technical specifications

- Frequency: 50-60 Hz

**Packaging dimensions and weight**

- EAN/UPC - product: 046677553586
- Gross weight: 0.840 g
- Height: 11.500
- Length: 13.100
- Width: 21.500
- Material number (12NC): 929001949563



Issue date: 2023-11-08  
Version: 0.151

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)