

PHILIPS
LED
Spot (Dimmable)
5.2W-35W
GU5.3
Bright White Light
Dimming

046677553876



Dimmable LED light with a focused bright beam

Philips dimmable LED MR16 spot light bulbs are a long lasting, energy efficient replacement for halogen spots. They have a bright white light and are ideal for accent lighting in recessed and track lighting fixtures.

High quality light

- Designed for the comfort of your eyes

Light beyond illumination

- Dimmable
- Instant on

PHILIPS

Highlights

Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get the glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Instant on

Dimmable

This bulb can be used with most dimmers to create your desired ambience with smooth dimming to 10% of full light levels. Please check the dimmability compatibility chart to be certain that your particular dimmer can be used with this bulb.

Specifications

Bulb characteristics

- Dimmable: Dimmable
- Intended use: Indoor
- Lamp shape: Spot
- Socket: GU5.3
- Technology: LED
- Lamp shape code: MR16

Bulb dimensions

- Height: 4.45 cm
- Weight: 0.05 kg
- Width: 5.05 cm

Durability

- Average life (at 2.7 hrs/day): 25 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 25,000 hour(s)
- Number of switch cycles: 50,000

Light characteristics

- Application: Task lighting, Accent lighting
- Beam angle: 35 degree(s)
- Color consistency: 6SDCM
- Color rendering index (CRI): 80
- Color temperature: 3000 K
- Light Color Category: Bright White Light
- Warm-up time to 60% light: Instant full light

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Lamp current: 500 mA
- Mercury content: 0 mg
- Efficacy: 80 lm/W

Packaging information

- EAN: 046677553876
- EOC: 553875
- Product title: 5.2MR16/LED/830/F35/DIM/G/12V T20 4/1BC

Power consumption

- Power factor: 0.7
- Voltage: 12 V
- Wattage: 5.2 W
- Wattage equivalent: 35 W

Rated values

- Rated beam angle: 35 degree(s)
- Rated lifetime: 25,000 hour(s)
- Rated peak intensity: 1000 cd
- Rated power: 5.2 W

Packaging dimensions & weight

- SAP EAN/UPC - Piece:
046677553876
- EAN/UPC - Case: 50046677553871
- SAP Gross Weight EAN (Piece): 0.072
kg
- Net Weight: 0.055 kg
- SAP Height (Piece): 13.500 cm
- SAP Length (Piece): 10.000 cm
- SAP Width (Piece): 5.200 cm



Issue date: 2019-12-09
Version: 0.74

© 2019 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com