

# PHILIPS

Bulb (Dimmable)

LED

4.5W-60W

E26

Amber Light

Dimming

046677556792



## Designed to be seen

Modern technology meets iconic design. Get the look and feel of vintage incandescent bulbs with extra warm light and energy saving LED technology.

### Choose for a sustainable solution

- Saves up to 80% Energy

### Light beyond illumination

- Dimmable

# Highlights

## Saves up to 80% Energy



Enjoy the energy-savings of LEDs without sacrificing light quality. Instantly save over 80% in energy by replacing your existing incandescent or halogen bulbs

## Dimmable

This bulb can be used with most dimmers to create your desired ambience with smooth dimming to 10% of full light levels. Please check the dimmability compatibility chart to be certain that your particular dimmer can be used with this bulb.

# Specifications

## Bulb characteristics

- Dimmable: Yes
- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: E26
- Technology: LED
- Bulb Finish: Amber

## Bulb dimensions

- Height: 10.6 cm
- Weight: 0.03 kg
- Width: 6 cm

## Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 20,000

## Light characteristics

- Color consistency: 6SDCM
- Color rendering index (CRI): 80
- Color temperature: 2000 K
- Light Color Category: Amber Light
- Nominal luminous flux: 300 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: 0.5 s
- Correlated Color Temperature (Nom): 2000 K
- Luminous Efficacy (rated) (Nom): 66.00 lm/W
- Luminous Flux: 300 lumen

## Miscellaneous

- EyeComfort: Yes

## Other characteristics

- Lamp current: 40 mA
- Efficacy: 66 lm/W
- EU RoHS compliant: Yes

## Packaging information

- EAN: 046677556792
- EOC: 556795
- Product title: 4.5A19/VIN/820/E26/CL/GL/DIM 4/FB T20

## Power

- Power Factor (Fraction): 0.7

## Power consumption

- Energy Star Certified: No
- Power factor: 0.7
- Voltage: 120 V
- Wattage: 4.5 W
- Wattage equivalent: 60 W
- Power Consumption: 4.5 W

## Product dimensions and weight

- Length: 10.6 cm

## Rated values

- Rated lifetime: 15,000 hour(s)
- Rated luminous flux: 300 lumen
- Rated power: 4.5 W

## Technical specifications

- Frequency: 60 Hz
- Dimmable: Yes
- Line Frequency: 60 Hz
- Cap-Base: E26 | Single Contact Medium Screw



Issue date: 2023-11-08  
Version: 0.209

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)