






Project:	
Spec Type:	
Catalog No:	7705LxCVA
Qty	
Line Notes:	

Incredible efficacy & boundless lighting choices mean the re-engineered Sona suspended LED is destined to become a future classic. Flexible up/down distributions and tailored LED optics mean you always have the right light for every task.

Ordering guide



^{*} Nominal values within a range. Down kits reduce output & efficacy. Consult photometry data for CRI, color temp, lumens & distribution of chosen configuration.

Mount Type Consult separate mounting spec sheet for mount type options: Ledalite Suspended Mounting Options Endcaps - Integrated Controls Please indicate with check mark. Response Daylight Single Zone (DS) SpaceWise DT Occupancy & Daylight Sensor (SZ)







[†] Not all wiring types are available with all configurations. Consult Philips Ledalite for a complete list of available options.

4500 lm/4ft 75% Up 3000/3500/4000K

Optical System

 $\label{light Chamber Upper: Lateral-facing LED arrays deliver light into both the upper and lower hemispheres, giving a highly efficient, native 70% up / 30% down distribution with a wide, homogeneous upper batwing distribution. A fully indirect version with a solid lower housing can be specified, as well as a 50% down-light kit option.$

1 Light Chamber Lower: A downward-facing LED array aims light into the lower hemisphere, for a highly efficient, fully direct distribution or optional 80% down version.

2 Light Chambers: Both lateral-facing and downwardfacing LED arrays are combined in separate upper and lower chambers for the ultimate in up/down distribution control.

Lenses: On the upper surface an engineered diffuser smooths the light distribution on the ceiling and acts as a dust cover. On the lower surface, two 4" wide optics are available: either a curved, engineered acrylic diffuse lens flush to the housing; or a white louver with regressed diffuser for improved high angle cut-off and visual comfort.

Endcaps

Diecast aluminum endcaps, either Sculpted (curved) or Flat

Finish

High quality powder coated, available in matte white, black or titanium silver. Other custom colors, including pacific aqua, are available on request. White sensors only.

Housing

Precision formed 18 gauge cold-rolled steel. Cross section size (approx.): $2.6\,^{\rm h}$ x $9\,^{\rm w}$ (suspended) or $7.4\,^{\rm w}$ (wall mount).

Weight

Maximum: Suspended 4.9lb/ft, Wall 3.4lb/ft

Electrical

Factory pre-wired to section ends with quick-wire connectors.

Standard Drivers

Philips Advance Xitanium 0-10V, 1-100%. Philips Advance Xitanium Sensor Ready, 5-100%. Class 2 rated output. Consult Philips Ledalite for other available drivers.

Standard Battery Pack

Philips Bodine, 90 min, 10W, Class 2 rated output, Emergency lumen output = 10W x luminaire efficacy x 1.1. Typical output: suspended 1400lm, wall 1200lm.

Lumen Maintenance

LEDs have been tested by the manufacturer in accordance with IESNA LM-80-08. At an ambient temperature of 25°C, the LED lumen maintenance expectation according to IES TM-21-11 is: L80 (12k) >72,000 hrs (Reported methodology) L80 (12k) 110,000 hrs (Projected methodology).

Source Color

LEDs rated for color rendering CRI >80, R9 >0 and fixture to fixture color accuracy within 3 SDCM.

Controls

Suspended version (1 light chamber only) available with the following integrated controls: Response Daylight Sensors SpaceWise DT Occupancy & Daylight Sensors w/ advanced grouping & Dwell Time.

*SpaceWise DT commissioning is via a compatible Android phone and Philips Field App. Compatible wireless dimming wall switches are available for dimming. 347V is not available as a standard option. For more information, please refer to www.philips.com/spacewise

Mounting

Suspended: Rapid installation sling mount at joints and ends. High strength aircraft cable and stainless steel gripper provide unlimited vertical adjustment and are independently tested to stringent safety standards. Variable mounting along the length of the housing is available for certain configurations upon request. Wall: A hidden steel rail and bracket system attaches to the existing structure and supports housings close to the wall. Mount positioning is fully variable along the modules to accommodate site conditions, spaced up to $4\frac{1}{2}$ on center and within 6" of an end or joint.

Joints

Self-aligning, gasketed joining system with hands-free wiring feature.

Approvals

Certified to UL, CSA and IES standards. Most suspended versions (except 1 light chamber down with louver) are DesignLights Consortium® qualified. Please see the DLC QPL list for exact catalog numbers (www.designlights.org/QPL).

Warranty


Philips indoor professional luminaires 5 year LED warranty: www.philips.com/warranties

Environment

Rated for dry or damp locations in operating ambient temperatures 0–40°C (32–104°F). Certain luminaire components may be adversely affected by contaminants. Damage caused by sulfur, chlorine, petroleum based solutions or other contaminants in the area of operation are not covered under warranty. Not suitable for natatorium environments.

Due to continuing product improvements, Philips Ledalite reserves the right to change the specifications without notice.


Dimensions - Cross Section




4500 lm/4ft 75% Up 3000/3500/4000K

Dimensions - Modules

Suspended - Side view, no end caps




Optics and Styles




4500 lm/4ft 75% Up 3000/3500/4000K

Photometry @ CRI>80, 3500K



74% Up / 26% Down



Candela Distribution

Vertical	Horizontal Angle Z					
Angle	0	22.5	45	67.5	90	Lumens
0	469	469	469	469	469	0
5	460	465	465	471	473	44
15	415	427	449	480	492	128
25	351	371	416	478	508	195
35	269	295	356	440	490	229
45	172	199	267	361	426	216
55	98	113	160	253	318	165
65	61	70	81	140	185	103
75	32	38	43	50	54	48
85	9	17	21	21	17	19
90	0	0	0	0	0	0
95	44	58	84	100	94	86
105	151	204	281	335	352	288
115	264	406	588	703	734	542
125	372	591	860	1021	1064	704
135	440	637	896	1057	1102	647
145	472	611	810	943	983	486
155	484	567	697	792	821	315
165	486	522	582	633	649	165
175	486	493	497	506	511	49
180	486	486	486	486	486	0

Values per 4ft unit

Fixture photometry has been conducted in accordance with IESNA LM-79-08

IES files for this and other photometric options can be downloaded online at www.lightingproducts.philips.com

Coefficients of Utilization (%)

DCD	Ceiling:		8	0			70			50		0
RCR	Wall:	70	50	30	10	70	50	30	50	30	10	0
0		101	101	101	101	90	90	90	70	70	70	26
1		93	89	85	82	82	79	76	61	59	58	22
2		84	77	72	67	75	69	65	54	51	48	19
3		77	68	61	56	69	61	55	48	44	40	16
4		71	60	53	47	63	54	48	42	38	35	14
5		65	54	46	40	57	48	42	38	33	30	12
6		59	48	40	35	53	43	37	34	29	26	11
7		55	43	36	30	49	39	32	31	26	23	10
8		51	39	32	27	45	35	29	28	23	20	9
9		47	36	28	24	42	32	26	26	21	18	8
10		44	32	26	21	39	29	23	23	19	16	7

Avg. Luminance (cd/m2)

Vertical	Horizontal Angle				
Angle	0	45	90		
55	1528	2370	4628		
65	1285	1581	3517		
75	1099	1267	1531		
85	893	1390	1058		

Distribution

Hemisphere	74% Up / 26% Down
Peak/Zenith	2.30
Peak Output	1116 cd
Glare Control	Meets RP-1-12 recommendations for VDT-Normal spaces

4500 lm/4ft 75% Up 3000/3500/4000K

Optical Performance @ 120V


Nominal Spec:	3000K	3500K	4000K
Flux (lm)	4254	4428	4523
Efficacy (lm/W)	127.7	133.0	135.0
Power (W)	33.3	33.3	33.5
CCT (K)	3020	3378	3958
CRI	84	83	84
R9	11	9	11
x	0.4361	0.4138	0.3835
у	0.4048	0.3976	0.3820
Duv	0.0003	0.0012	0.0016

Electrical Performance @ CRI>80, 3500K

Input Voltage	120V	277V	347V
Input Power	33.3W	33.1W	33.6W
Input Current	0.28A	0.12A	0.10A
Power Factor	0.996	0.966	0.964
Total Harm. Distortion	6.3%	9.6%	9.0%

Tested values - contact technical support for rated values. Off-state power zero unless certain controls are specified.

With SpaceWise DT, standby power <0.5W (120V) or <0.8W (277V).





use of this publication.