










SMTT






SMS



TCS LE/LF Max. 16 A.





TPS LE/LF Max. 6 A.




Philips Lighting
www.philips.com

CVC 471/473



CVC 471/473



Use Philips lamps for optimum performance
Funzionamento ottimale garantito con lampade Philips
Resultados óptimos con lámparas Philips
Toimii parhaiten Philips-lamppujen kanssa
Funciona melhor com lâmpadas Philips no interior
Werkt het best met Philips-lampen

Fonctionnement optimal avec lampes Philips
Bestes Betriebsergebnis mit Philips-Lampen
Fungerer bedst med Philips-lamper
Fungerer mest optimalt med Philips-lamper
Fungerar bäst med lampor från Philips

4422 003 62883
07/10
Printed in the Netherlands
Data subject to change

SmartForm

TCS 461/471/477 and LE/LF TPS 461/463/471/473/477 and LE/LF

Installation instructions

Instructions de montage Montageanleitung Montage instruktie Istruzioni di montaggio Instrucciones de montaje Instruções de montagem Monteringsinstruktioner Monteringsvejledning Kokoontäyttö- ja kiinnitysohjeet Montaj yönergesi Οδηγίες συναρμολόγησης Instrukcja montażu Szerelési utasítások Návod k montáži ИНСТРУКЦИЯ ПО МОНТАЖУ Návod k montáži


IP 20 - IP 40

This luminaire must be earthed.
Ce luminaire doit être mis à la terre.
Diese Leuchte muß geerdet werden.
Dit armatuur moet worden geaard.
Questa armatura deve essere collegata a terra.
La Luminaria debe estar conectada a tierra.

Class I




TCS



All dimensions are in mm

Power (W)	L	W3	A	B	CI	C2
13/14/20/24 W	640	332	65	80	400	-
25/28/50/54 W	1240	332	65	80	1000	267
32/35/45/49/73/80 W	1540	332	65	80	1300	267

TPS



SMT1 / SMTT / SMT2


All dimensions are in mm

Power (W)	L	W3	A	CI	C2
25/28/50/54 W	1240	332	65	1140	127
32/35/45/49/73/80 W	1540	332	65	1440	127

SMS

All dimensions are in mm

Power (W)	L	W3	A	CI	C2
25/28/50/54 W	1240	332	65	1158	109
32/35/45/49/73/80 W	1540	332	65	1458	109



PHILIPS

L

—

BLACK / BROWN

⏏

YELLOW - GREEN

N

—

BLUE

DA

DA

+

/T/LL/LS

—

ORANGE / BROWN

—

/NS

—

PURPLE / GREY

⏏

eller

⏏

Vigtigt !

Lederen med grøn/gul isolation må kun tilsluttes en klemme mærket

TCS

2x

⬆

⬆

①

②

⬇

②

⬇

+

—

SW-EL

L

⏏

N

①

⬇

②

⬇

N

⏏

L

TPS

SMTI

⏏

⏏

C1

SMTT

⏏

⏏

C1

SMT2

⏏

⏏

C1

SMTI/SMT2

⏏

⏏

SMTT

⏏

⏏

SMS

⏏

⏏

C2

TPS

⬇

⬇

⬇

⬇

N

⏏

L

+

—

+ /T/LL/LS

— /NS

SMTI / SMTT / SMT2

②

⬆

⬆

③

⬆

①

⬆

⬆

⬆

SMS

⬆

⬆

⬆

⬆

SMT2

56

⬆

⬆

⬆

⬆

⬆

2x

⬆

N

⏏

L

⬆

⬆

N

⏏

L

DA

— /NS

+ /T/LL/LS

CLICK

⏏