Day-Brite LFI by (s)ignify

Recessed

ClearAppeal 1x4

1CAX up to 4500 lumens



Day-Brite / CFI ClearAppeal LED recessed is a fully luminous aperture luminaire providing modern appeal to architectural spaces. Featuring a regressed aesthetic with balanced glare gradient, ClearAppeal delivers high performing even illumination and high visual comfort. Its architectural style, coupled with controls options, makes ClearAppeal an ideal choice for applications such as office, institutional, and healthcare, where energy savings and customized effect are desired.

Cat.No:
Type:
Lamps: Qty:
Notes:

Project:

Location

Options

ClearAppeal now offers AccuRender technology for the highest color quality at the highest efficacy.

Efficacy

Ordering guide - standard & wireless controls

Lumens

Ceiling

Width Family

Standard configurations available with all choices, unless otherwise noted. Base configurations selections indicated by blue.

Color

example: 1CAXG38L840-4-DS-UNV-DIM-SWZCS

	,	Туре	(nominal de	elivered)		,			6-	.	Diffu	ser							
1	CAX	G						-	4]-	DS]-		-	-		_		
1 1'	CAX ClearAppeal Gen 2		Base configuratio 38B 3800 Standard configuratio 30L 3000 45L 4500 Other lumer packages made ordered increments of from 3000 t lumens	ens))) ay in	Blank H ⁵	Standard High	830 835 840 850 <u>Accul</u> 930 935 940	80 CRI, 3000K 80 CRI, 3500K 80 CRI, 5000K 80 CRI, 5000K Render ^{8,9} 90 CRI, 3500K 90 CRI, 4000K	4 4'		DS D (s	iffuse imooth)	UNV 347	Univo Volta 120-2 volt 347V	age, 277	DIM ¹ SDIM LDE LDEH DALI	Dimming Step dimming to 40% input power Lutron LDE5, 5% dimming Lutron LDE1, 1% dimming DALI dimming	F1 F2 F1/D F2/5W F2/6W GLR BSL10LST ⁴ BSL6LST ⁴ DSC CHIC ³ ER100 ^{4,6,7}	3/8" flex, 3 wire 18 gauge 6' 3/8" flex, 4 wire 18 gauge 6' 3/8" twin flex, 3 wire 18 gauge 6' for dimmable luminaires 3/8" single flex, 5 wire 18 gauge 6' for dimmable luminaires 3/8" single flex, 6 wire 18 gauge 6' for dimmable and emergency luminaires Fusing, fast blow Bodine 10W selftesting battery pack Bodine 6W selftesting battery pack Quick driver disconnect Chicago Plenum rated UL924 listed sensor bypass relay, factory installed between driver &
	ring guid le: 1CAXG3		DS-LV-P)													GTD/E ^{4,6} GTD/SNSR ^{4,6,7}	sensor UL924 listed Bodine GTD factory installed on driver input UL924 listed Bodine GTD factory
Width	Family		Ceiling Type	Lumen (nomin	-	rered)	Effica	ісу	Cole	or			Leng	th	Cente	er Diffuser		SWZCS ^{2,10}	installed between driver and sensor Interact Pro scalable sensor with integral daylight & occupancy
1	CAX		G							-	-		4]-	DS]-		CWZDZ?	sensing, advanced grouping with dwell time
1 1'	CAX ClearA	ppeal Gen 2	G Grid	30L 38L	rd conf 3000 3800 4500	igurations	Blank	Standard	830 835 840 850	80 80	CRI, 3 CRI, 4		4 4'		DS D	iffuse (smo	ooth)	SWZDT ² RADIO ²	SpaceWise only sensor, daylighting and occupancy, advanced grouping with dwell time Interact Pro RF sensor, enables wireless connected lighting control
Voltag	e	Driver				Options												IAOSB ^{2,10}	Interact Office advanced wireless sensor bundle, integral SC1500 w/
LV Lov	_ v voltage	POE Pow	er over ether	net		EMPOE 600		egral emer										AG WL	IoT capabilities for enterprise scale projects Antimicrobial Finish Wet location listed

Interact Office advanced wired sensor bundle, integral SC2000

w/IoT capabilities for enterprise scale projects

Center

Voltage

Driver

Footnotes

- 1 Integral controls options dimmable to 5% via wireless wall switch. Non-controls options are 0-10v dimmable to 1% for Standard configurations, and to 10% for Base configurations.
- 2 Specify only with -DIM driver option.
- 3 CHIC option not provided with air return functionality.
- 4 Not available with 347V.
- 5 High efficacy option may only be ordered with Standard lumen configurations.
- 6 Must be installed in conjunction with a UL1008 device.
- 7 Must be ordered with an integral sensing option.
- 8 AccuRender is 90CRI with R₉>50.
- 9 Option is qualified as Engineered-to-Order (ETO) ready. Lead times and minimum order quantities may vary, please consult factory. (DLC Standard efficacy only)
- 10 Must order IRT9015 Interact commissioning remote with each system order.

Accessories (order separately)

- FSF414 1'x4' surface mount field installation kit (field assembled)
- FMA14 1'x4' "F" mounting frame for NEMA "F" ceiling
- CAXGDS14L 1'x4' ClearAppeal Gen2 replacement lens • CAXGDS14LC - 1'x4' ClearAppeal Gen2 with controls replacement lens

SWZCS accessories (order separately)

• IRT9015 - handheld remote for grouping and configuration (at least one remote required for any SWZCS installation).









up to 4500 lumens

Application

- · Ideal for modern offices, institutional, retail, and healthcare applications.
- · Modern architectural styling to complementary space.
- $\bullet \ \mathsf{Full} \ \mathsf{width} \ \mathsf{luminous} \ \mathsf{lens} \ \mathsf{provides} \ \mathsf{smooth} \ \mathsf{brightness} \ \mathsf{and} \ \mathsf{high} \ \mathsf{visual} \ \mathsf{comfort}.$
- Directs a controlled amount of light to higher angles to eliminate "cave effect" without creating glare.
- Available in standard efficacy and high efficacy (H) configurations up to 130lm/W.
- 80 CRI minimum source provides a balanced spectral power distribution.
- · AccuRender 90 CRI source provides preferred color quality.
- Suitable for use with NEMA G (15/16") and NFG (9/16") suspended t-grid ceilings. NEMA F flange ceilings require the FMA24 accessory (ordered separately).

Construction/Finish

- $\boldsymbol{\cdot}$ Robust and durable dieformed embossed steel housing and end caps.
- Molded one-piece acrylic diffuser may be removed without tools for access to LED boards and driver(s).
- Unique spring retainers ensure the diffuser is centered in the housing opening at all times.
- T-bar grid clips are built into luminaire end caps for quick and easy installation, no extra parts.
- Air return functionality is standard for all configurations. See air flow and noise data on page 4.

Energy data

Configuration	Nominal CCT/ CRI	Flux (lm)	Input Power (W)	Efficacy (LPW)	DLC
1CAXG38B835	3500K/80	4034	34	118	Standard
1CAXG38B840	4000K/80	4029	34	117	Standard
1CAXG30L835	3500K/80	3054	26	116	Standard
1CAXG30L840	4000K/80	3054	27	115	Standard
1CAXG30LH835	3500K/80	3014	24	124	Standard
1CAXG30LH840	4000K/80	3086	24	127	Premium
1CAXG38L835	3500K/80	3885	34	114	Standard
1CAXG38L840	4000K/80	3888	34	114	Standard
1CAXG38LH835	3500K/80	3777	30	126	Premium
1CAXG38LH840	4000K/80	3873	30	130	Premium
1CAXG45L835	3500K/80	4619	41	112	Standard
1CAXG45L840	4000K/80	4620	42	111	Standard
1CAXG45LH835	3500K/80	4590	36	126	Premium
1CAXG45LH840	4000K/80	4706	36	130	Premium

Dimensions

- Suitable for end to end continuous row mounting. 1" gap between luminaires requires chase nipple to accommodate through wiring (by others).
- Sheetmetal componets are multi-stage phosphate treated for maximum corrosion resistance and finish coat is high reflectance basked white enamel.
- Integral louvers on housing ends allow air from the heated space to return to a pressurized plenum.

Electrical

- \cdot Driver and LED board are accessible from below by easy removal of lens.
- Non-controls Base configurations 0-10V dimmable to 10%.
- · Non-controls Standard configurations 0-10V dimmable to 1%.
- Standard configurations with controls options dimmable via wireless switches (see below).
- Predicted L70 lumen maintenance up to 80,000 hours at 25°C ambient for all configurations.
- Emergency battery packs accessible from above. To estimate lumen output in emergency mode, multiply emergency pack wattage by luminaire efficacy, then by 1.10.
- The GTD/E option is used to bypass wall switches and allow luminaire operation on auxiliary power. Generator transfer requires installation in conjunction with a UL1008 listed device.
- The GTD/SNSR option is used to bypass integrated sensor control in the event of utility power loss. Generator transfer requires installation in conjunction with a UL1008 listed device.
- Compliance to CAN ICES-005-A/ NEB-005-A and FCC Part 15-A.

Validation


- · cETLus listed for use in damp locations
- When ordered with -WL option code, suitable for use in wet locations with covered ceilings
- Rated for direct contact with insulation (IC)
- · CCEA Chicago Plenum listed
- ClearAppeal luminaires are Designlights Consortium® qualified. Please see the DLC QPL list for exact catalog numbers, www.designlights.org/QPL

Environmen

Rated for dry or damp locations in operating ambient temperatures 0-30°C (32-86°F). Many luminaire components, such as reflectors, refractors, lenses, sockets, lampholders, and LEDs are made from various types of plastics which can be adversely affected by airborne contaminants. If sulfur based chemicals, petroleum based products, cleaning solutions, or other contaminants are expected in the intended area of use, consult factory for compatibility. Not suitable for natatorium environments.

Warranty

5 year manufacturer's limited warranty.
 Visit signify.com/warranties for complete warranty information.



up to 4500 lumens

Wireless Controls Options

SpaceWise DT (SWZDT)

- Standalone daylight and occupancy sensing with advanced grouping, wireless mesh networking and dwell time.
- Commissioning via compatible Android phone and Philips Field App
- Dimming via compatible Zigbee wireless wall switch only (see link below for details)
- Register for the commissioning app at http:// registration.componentcloud.philips.com/ appregistration/
- · Integral sensing options may not be combined
- For more information including recommended switches, refer to the following: -

SWZDT - www.usa.lighting.philips.com/systems/lighting-systems/spacewise

Emergency Options (ER100)

- Power Sensing (Factory default) Recommended UL924 option requires unswitched power sense line, absence of voltage on the normal circuit triggers luminaire to 100% output
- Power Interruption Detection (Field option) Detects AC power interruption >30ms triggers 90 minute emergency mode with luminaire at 100% output

ClearAppeal shown with integral sensor



Interact Pro scalable sensor for Foundation, Advanced & Enterprise tiers (SWZCS and an evolution of SpaceWise)

- SWZCS is a connected sensor with integral occupancy and daylight sensing and supports wireless mesh connectivity.
- The sensor works in the Foundation mode (similar to SpaceWise) when configured without a gateway or in an Interact Pro Advanced or Enterprise mode if a compatible gateway is used.
- Interact Pro includes an App, a portal and a broad portfolio of wireless luminaires, lamps and retrofit kits all working on the same system.
- Startup is implemented via Interact Pro App (Android or iPhone) & BlueTooth connectivity.
 The App provides flexibility to choose between a gateway or non gateway mode for setup.
- Setup with the gateway requires wired internet access to the gateway. It is possible to add a gateway at a later point.
- Prepare project configuration steps remotely and use IRT9015 remote onsite to identify and group devices together.
- · Compatible with:
- SWS200 wireless scene switch
- Battery powered IP42 presence sensor OCC sensor IA CM WH 10/1
- Battery powered IP42 presence & daylight sensor OCC-DL sensor IA CM IP42 WH
- LCN3110: Battery powered IP65 presence sensor, OCC sensor IA CM IP65WH
- -LCN3120: Battery powered IP65 presence & daylight sensor, OCC-DL sensor IA CM
- For more information on Interact Pro visit: www.interact-lighting.com/ interactproscalablesystem

Radio only sensor (RADIO)

- Integral RADIO only sensor simply enables wireless mesh connectivity to the luminaire without any occupancy or daylight sensing.
- Ideal for applications where sensing functionality is managed by other Interact devices and the luminaire only needs to have wireless connectivity.

Interact Pro scalable sensor bundles for Enterprise tier

- IAOSB option in addition to occupancy and daylight sensing supports advanced IoT capabilities such as people estimation analysis, desk level temperature & humidity sensing, noise classification, and BLE beacon.
- Compatible with SWS200 wireless scene switch and Interact Ready wireless battery powered sensors.
- Use Interact software and insights to increase building efficiency, achieve building wide integration and optimize space through occupancy analytics.
- Requires compatible Gateway and internet connectivity for commissioning.
- For more information, visit:
 www.interact-lighting.com/office or
 www.usa.lighting.philips.com/systems/system areas/offices

Wired Controls Options Interact Office Wired (PoE)

- PoE based IoT connected lighting solution for large enterprises that span across multiple floors, buildings and require multiple gateways.
- Use Interact software and insights to increase building efficiency, achieve building wide integration and optimize space through occupancy analytics.
- IAOSB option in addition to occupancy and daylight sensing supports advanced IoT capabilities such as people estimation analysis, desk level temperature & humidity sensing, noise classification, and BLE beacon.
- PoE lighting controller is accessible from below.

- Integral sensor option for occupancy sensing (PIR) and/or daylight harvesting available for additional energy savings.
- Optional integral emergency controller and battery pack provides 600lm nominal output.
 Test switch and indicator light mounted on side of chassis on one end.
- Emergency battery has a 3 month pre-installed shelf life, and must be stored and installed in environments of 20C to 30C (-4F to 86F) ambient, and 45-85% relative humidity.
- For more information, visit: www.interactlighting.com/office or www.usa.lighting.philips. com/systems/system-areas/offices

Energy Data (PoE)

Configuration	Nominal CCT/CRI	Flux (lm)	DC Power (W)*	Efficacy (LPW)
1CAXG30L840	4000K/80	3059	25	125
1CAXG38L840	4000K/80	3902	32	122
1CAXG45L840	4000K/80	4637	40	117

^{*}DC power supply


up to 4500 lumens

	Interact Pro scalable system						
	recent for	A CONTRACTOR OF THE PROPERTY O					
	Foundation	Advanced	Enterprise				
Dimming, grouping, and zoning	~	✓	~				
Bluetooth and ZigBee enabled	~	✓	~				
Motion sensing and daylight harvesting	~	✓	~				
Integration with 0-10V and phase dimming fixtures	~	✓	~				
Code compliance	~	✓	~				
Granular dimming and dwell time	~	✓	~				
Energy reporting and monitoring		✓	~				
Scheduling		✓	~				
Demand response		✓	~				
BMS integration (BACnet)			~				
Floor plan visualization			~				
IoT sensors for wellness			~				
IoT Apps for productivity			~				

Currently supported maximum system size

To be able to design the lighting system correctly for the customer, it is important to know the prime characteristics of the system, its possibilities and limitations.

System level	
Total number of gateways	Unlimited
Total number of devices	200 per network
 luminaires with integrated sensors 	150
smart TLEDS	150
Total number of ZGP devices (sensors and switches)	50
· sensors	30
· switches	50
zones and groups	64
Group level	
Recommended number of lights	40 (recommended 25)
Number of ZGP devices	5
Number of scenes	16




up to 4500 lumens

Air return



Integral louvers on housing ends allow air from the heated space to return to a pressurized plenum.

Return Air Data



		2x4 Return Air - noise criteria									
CFM		44	56.5	69	75.5	82	94	108			
NC (dB)	<15	19	21.5	24	27	30	35	39			

Photometry

1x4 ClearAppeal recessed LED, base configuration, 3800 nominal delivered lumens

LER - 117

 Catalog No.
 1CAXG38B840-4-DS-UNV-DIM

 Test No.
 40617

 S/MH
 1.2

 Lamp Type
 LED

 Lumens
 4033

 Input Watts
 34

Comparative yearly lighting energy cost per 1000 lumens – \$2.05 based on 3000 hrs. and \$.08 pwr KWH.

The photometric results were obtained in the Day-Brite laboratory which is NVLAP accredited by the National Institute of Standards and Technology.

Photometric values based on test performed in compliance with LM-79.

Candle	power	

Aligie	EIIU	43	CIUSS	Dack-43
0	1528	1528	1528	1528
5	1494	1522	1531	1522
15	1425	1452	1462	1452
25	1297	1318	1320	1318
35	1120	1139	1137	1139
45	915	938	944	938
55	697	732	739	732
65	443	517	478	517
75	227	244	217	244
85	52	45	40	45

ight distribution									
Degrees	Lumens	% Luminaire							
0-30	1158	28.7							
0-40	1868	46.3							
0-60	3237	80.3							
0-90	4033	100.0							
0_100	4022	100.0							

Average Luminance								
Zone	End	45°	Cross					
45	4436	4544	4574					
55	4164	4372	4413					
65	3593	4196	3876					
75	3005	3236	2870					
85	2029	1762	1585					

Coefficients of Utilization

EFFECTIVE FLOOR CAVITY REFLECTANCE 20 PER (pfc=0.20)									
pfc =	20								
Ceil		80			70		5	0	
Wall	70	50	30	70	50	30	50	30	
RCR									
0	118	118	118	115	115	115	111	111	
1	109	104	100	106	102	97	97	94	
2	98	91	83	96	89	82	85	81	
3	91	80	71	88	79	70	76	68	
4	82	70	61	81	69	61	67	59	
5	76	64	55	73	63	54	59	53	
6	70	56	48	68	56	47	55	46	
7	66	52	42	64	51	42	50	41	
8	60	47	39	58	46	39	46	38	
9	56	44	35	56	42	34	41	34	
10	53	40	32	52	40	32	39	32	

up to 4500 lumens

1x4 ClearAppeal recessed LED, standard configuration, 3800 nominal delivered lumens

LER - 114

 Catalog No.
 1CAXG38L840-4-DS-UNV-DIM

 Test No.
 40615

 S/MH
 1.2

Lumens 3888 Input Watts 34

Comparative yearly lighting energy cost per 1000 lumens – **\$2.11** based on 3000 hrs. and \$.08 pwr KWH.

The photometric results were obtained in the Day-Brite laboratory which is NVLAP accredited by the National Institute of Standards and Technology.

Photometric values based on test performed in compliance with LM-79.

Candlepower

Angle	End	45	Cross	Back-45
0	1480	1480	1480	1480
5	1447	1475	1483	1475
15	1381	1406	1416	1406
25	1257	1277	1278	1277
35	1086	1104	1100	1104
45	887	908	914	908
55	675	709	715	709
65	422	467	446	467
75	219	238	209	238
85	50	44	39	44

Light Distribution

Degrees	Lumens	% Luminaire
0-30	1121	28.8
0-40	1809	46.5
0-60	3135	80.6
0-90	3891	100.0
0-180	3891	100.0

Average Luminance

Zone	End	45°	Cross
45	4298	4402	4429
55	4034	4235	4275
55	3424	3786	3616
75	2895	3145	2770
35	1954	1711	1530

Coefficients of Utilization

EFFECTIVE FLOOR CAVITY REFLECTANCE 20 PER (pfc=0.20)								
pfc =	20							
Ceil		80			70		50	
Wall	70	50	30	70	50	30	50	30
RCR								
0	118	118	118	115	115	115	111	111
1	109	104	100	106	102	97	97	94
2	98	91	84	96	89	82	85	81
3	91	80	71	88	79	70	76	68
4	82	70	63	81	69	61	67	59
5	76	64	55	73	63	54	60	53
6	70	56	48	68	56	47	55	46
7	66	52	42	64	51	42	50	41
8	60	47	39	59	46	39	46	38
9	56	44	35	56	42	34	41	34
10	54	40	33	52	40	32	39	32

1x4 ClearAppeal recessed LED, high efficacy configuration, 3800 nominal delivered lumens

LER - 130

Catalog No. 1CAXG38LH840-4-DS-UNV-DIM

 Test No.
 40623

 S/MH
 1.2

 Lamp Type
 LED

 Lumens
 3877

 Input Watts
 30

Comparative yearly lighting energy cost per 1000 lumens – \$1.85 based on 3000 hrs. and \$.08 pwr

The photometric results were obtained in the Day-Brite laboratory which is NVLAP accredited by the National Institute of Standards and Technology.

Photometric values based on test performed in compliance with LM-79.

Candlepower

Angle	End	45	Cross	Back-45
0	1480	1480	1480	1480
5	1447	1474	1481	1474
15	1382	1403	1410	1403
25	1258	1271	1271	1271
35	1087	1098	1095	1098
45	887	903	908	903
55	677	705	710	705
65	424	463	443	463
75	219	236	210	236
85	50	44	40	44

Light Distribution

-		
Degrees	Lumens	% Luminaire
0-30	1119	28.9
0-40	1804	46.5
0-60	3123	80.6
0-90	3876	100.0
0-180	3877	100.0

Average Luminance

Zone	Zone End		Cross		
45	4301	4377	4403		
55	4044	4214	4243		
65	3438	3756	3595		
75	2901	3126	2776		
85	1950	1734	1573		

Coefficients of Utilization

EFFECTIVE FLOOR CAVITY REFLECTANCE 20 PER (pfc=0.20)									
pfc =	20								
Ceil		80			70			50	
Wall	70	50	30	70	50	30	50	30	
RCR									
0	118	118	118	115	115	115	111	111	
1	109	104	100	106	102	97	97	94	
2	98	91	84	96	89	82	85	81	
3	91	80	71	88	79	70	76	68	
4	82	70	63	81	69	61	67	59	
5	76	64	55	73	63	54	60	53	
6	70	56	48	68	56	47	55	46	
7	66	52	42	64	51	42	50	41	
8	60	47	39	59	46	39	46	38	
9	56	44	35	56	42	34	41	34	
10	54	40	33	52	40	32	39	32	



© 2022 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The informatior presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Signify North America Corporation 400 Crossing Blvd, Suite 600 Bridgewater, NJ 08807 Telephone 855-486-2216 Signify Canada Ltd. 281 Hillmount Road, Markham, ON, Canada L6C 2S3 Telephone 800-668-9008

All trademarks are owned by Signify Holding or their respective owners.