PHILIPS

Linear

Sona suspended (1LC Up)


4500 lm/4ft 70% Up 3000/3500/4000K



Project:		
Spec Type:		
Catalog No:	7705LxCAA	
Qty		
Line Notes:		

Incredible efficacy & boundless lighting choices mean the re-engineered Sona suspended LED is destined to become a future classic. Flexible up/ down distributions and tailored LED optics mean you always have the right light for every task.


Ordering guide



* Nominal values within a range. Down kits reduce output & efficacy. Consult photometry data for CRI, color temp, lumens & distribution of chosen configuration.

† Not all wiring types are available with all configurations. Consult Philips Ledalite for a complete list of available options.

Mounting Hardware





4500 lm/4ft 70% Up 3000/3500/4000K

Optical System

1 Light Chamber Upper: Lateral-facing LED arrays deliver light into both the upper and lower hemispheres, giving a highly efficient, native 70% up / 30% down distribution with a wide, homogeneous upper batwing distribution. A fully indirect version with a solid lower housing can be specified, as well as a 50% down-light kit option. 1 Light Chamber Lower: A downward-facing LED array

aims light into the lower hemisphere, for a highly efficient, fully direct distribution or optional 80% down version. **2 Light Chambers:** Both lateral-facing and downwardfacing LED arrays are combined in separate upper and lower chambers for the ultimate in up/down distribution control.

Lenses: On the upper surface an engineered diffuser smooths the light distribution on the ceiling and acts as a dust cover. On the lower surface, two 4" wide optics are available: either a curved, engineered acrylic diffuse lens flush to the housing; or a white louver with regressed diffuser for improved high angle cut-off and visual comfort.

Endcaps

Diecast aluminum endcaps, either Sculpted (curved) or Flat.

Finish

High quality powder coated, available in matte white, black or titanium silver. Other custom colors, including pacific aqua, are available on request. White sensors only.

Housing

Precision formed 18 gauge cold-rolled steel. Cross section size (approx.): 2.6"h x 9"w (suspended) or 7.4"w (wall mount).

Weight

Maximum: Suspended 4.9lb/ft, Wall 3.4lb/ft

Electrical

Factory pre-wired to section ends with quick-wire connectors.

Standard Drivers

Philips Advance Xitanium 0-10V, 1-100%. Philips Advance Xitanium Sensor Ready, 5-100%. Class 2 rated output. Consult Philips Ledalite for other available drivers.

Standard Battery Pack

Philips Bodine, 90 min, 10W, Class 2 rated output, Emergency lumen output = 10W x luminaire efficacy x 1.1. Typical output: suspended 1400lm, wall 1200lm.

Lumen Maintenance

LEDs have been tested by the manufacturer in accordance with IESNA LM-80-08. At an ambient temperature of 25°C, the LED lumen maintenance expectation according to IES TM-21-11 is: L_{80} (12k) >72,000 hrs (**Reported** methodology) L_{80} (12k) 110,000 hrs (**Projected** methodology).

Source Color

LEDs rated for color rendering CRI >80, R9 >0 and fixture to fixture color accuracy within 3 SDCM.

Controls

Suspended version (1 light chamber only) available with the following integrated controls: Response Daylight Sensors SpaceWise DT Occupancy & Daylight Sensors w/ advanced grouping & Dwell Time.

*SpaceWise DT commissioning is via a compatible Android phone and Philips Field App. Compatible wireless dimming wall switches are available for dimming. 347V is not available as a standard option. For more information, please refer to www.philips.com/spacewise

Mounting

Suspended: Rapid installation sling mount at joints and ends. High strength aircraft cable and stainless steel gripper provide unlimited vertical adjustment and are independently tested to stringent safety standards. Variable mounting along the length of the housing is available for certain configurations upon request. Wall: A hidden steel rail and bracket system attaches to the existing structure and supports housings close to the wall. Mount positioning is fully variable along the modules to accommodate site conditions, spaced up to 4½' on center and within 6" of an end or joint.

Joints

Self-aligning, gasketed joining system wth hands-free wiring feature.

Approvals

Certified to UL, CSA and IES standards. Most suspended versions (except 1 light chamber down with louver) are DesignLights Consortium[®] qualified. Please see the DLC QPL list for exact catalog numbers (www.designlights.org/QPL).

Warranty


Philips indoor professional luminaires 5 year LED warranty: www.philips.com/warranties

Environment

Rated for dry or damp locations in operating ambient temperatures 0-40°C (32-104°F). Certain luminaire components may be adversely affected by contaminants. Damage caused by sulfur, chlorine, petroleum based solutions or other contaminants in the area of operation are not covered under warranty. Not suitable for natatorium environments.

Due to continuing product improvements, Philips Ledalite reserves the right to change the specifications without notice.

Dimensions - Cross Section




4500 lm/4ft 70% Up

3000/3500/4000K

Dimensions - Modules

Suspended - Side view, no end caps



Optics and Styles

	A Curved Acrylic Lens	
V White Louver		


4500 lm/4ft 70% Up

3000/3500/4000K

Photometry @ CRI>80, 3500K

90^{-}_{-}

68% Up / 32% Down



All results are according to IESNA LM-79-2008: Approved Method for the Electrical and Photometric Testing of Solid-State Lighting. The U.S. Department of Energy (DOE) verifies product test data and results.

Visit www.lightingfacts.com for the Label Reference Guide.

Registration Number: F46Z-EK2321 (5/5/2017) Model Number: 7705LBCAA Type: Luminaire - Linear

Candela Distribution

Vertical	Horizontal Angle					Zonal
Angle	0	22.5	45	67.5	90	Lumens
0	486	486	486	486	486	0
5	482	486	485	484	484	46
15	466	470	471	471	471	133
25	434	438	441	445	445	203
35	386	392	399	401	400	248
45	326	333	342	340	341	260
55	255	264	268	268	270	237
65	175	183	187	189	192	184
75	92	99	107	114	117	113
85	23	34	46	55	59	50
90	2	15	26	36	41	0
95	41	54	79	84	83	83
105	138	190	268	318	338	272
115	234	373	563	679	716	516
125	317	532	819	989	1042	666
135	372	566	835	1001	1049	600
145	408	545	753	885	929	448
155	432	512	650	746	778	292
165	447	480	545	595	614	154
175	454	461	469	476	483	46
180	458	458	458	458	458	0

Coefficients of Utilization (%)

RCR	Ceiling:			0			70			50		0
RCR	Wall:	70	50	30	10	70	50	30	50	30	10	0
0		103	103	103	103	93	93	93	74	74	74	32
1		94	89	85	82	84	80	77	64	62	60	27
2		85	78	71	66	76	70	65	56	52	49	22
3		77	68	61	55	69	61	55	49	45	41	18
4		71	60	52	46	63	54	47	43	38	35	16
5		65	53	45	39	58	48	41	39	33	30	13
6		59	48	40	34	53	43	36	35	29	26	12
7		55	43	35	29	49	39	32	31	26	22	10
8		51	39	31	26	46	35	28	28	23	20	9
9		47	35	28	23	42	32	25	26	21	18	8
10		44	32	25	20	39	29	23	24	19	16	7

Avg. Luminance (cd/m2)

-		•	
Vertical	He	orizontal Ang	zle.
Angle	0	45	90
55	3987	3971	3923
65	3706	3638	3642
75	3164	3191	3339
85	2210	3094	3614

Distribution

Hemisphere	68% Up / 32% Down
Peak/Zenith	2.35
Peak Output	1076 cd
Glare Control	Meets RP-1-12 recommendations for VDT-Normal spaces

Values per 4ft unit

IESNA LM-79-08 IES files for this and other photometric options can be downloaded online at

Fixture photometry has been

conducted in accordance with

www.lightingproducts.philips.com

4500 lm/4ft 70% Up 3000/3500/4000K

Optical Performance @ 120V

Nominal Spec:	3000K	3500К	4000K
Flux (lm)	4371	4551	4648
Efficacy (lm/W)	132.1	137.5	139.6
Power (W)	33.1	33.1	33.3
CCT (K)	3020	3378	3958
CRI	84	83	84
R9	11	9	11
x	0.4361	0.4138	0.3835
У	0.4048	0.3976	0.3820
Duv	0.0003	0.0012	0.0016

Electrical Performance @ CRI>80, 3500K

Input Voltage	120V	277V	347V		
Input Power	33.1W	32.9W	33.6W		
Input Current	0.28A	0.12A	0.10A		
Power Factor	0.996	0.966	0.964		
Total Harm. Distortion	6.3%	9.6%	9.0%		
Tested values – contact technical support for rated values. Off-state power zero unless certain controls are specified.					

With SpaceWise DT, standby power <0.5W (120V) or <0.8W (277V).

© 2017 Philips Lighting Holding B.V. Il rights reserved. Philips reserves the right to make changes in specifications and/or to discontinue any product at any time without notice or obligation and will not be liable for any consequences resulting from the use of this publication. www.philips.com/luminaires



Philips Lighting, North America Corporation 200 Franklin Square Drive, Somerset, NJ 08873 Tel. 855-486-2216

Philips Lighting Canada Ltd., 281 Hillmount Rd, Markham, ON, Canada L6C 2S3 Tel. 800-668-9008