




Vectra combines distinctive styling with Ledalite's revolutionary MesoOptics technology to bring the best of nature's luminous aesthetics to indoor environments.

Ordering guide



Upgrades & Accessories Please indicate with check mark.	Integrated Controls Please indicate with check mark.
Flex Whip (6' length)	Response Daylight Single Zone (DS)
Drywall Kit	







^{*} Nominal values within a range. Consult photometry data for CRI, color temp, lumens & distribution of chosen configuration. † Not all wiring types are available with all configurations. Consult Philips Ledalite for a complete list of available options.

Vectra

2'x2', 3600 lm 3000/3500/4000K

Optical System

The optical frame assembly consists of an acrylic panel with a layer of protected MesoOptics film which efficiently provides a luminous, controlled, low glare 3-dimensional batwing distribution. The optical frame ends are constructed from die-formed cold-rolled steel assembled together with extruded aluminum profiles in a sturdy frame. The frame is hinged to allow easy access to the inside of the fixture. Maintenance can be performed from below the ceiling.

Housing

Die-formed, post-painted, 22 gauge cold-rolled steel housing. Multiple wire entrances are available (top or side) to allow continuous row mounting of fixtures. Optional frame restraint is available to provide additional safety support.

Mounting

Compatible with lay-in acoustical ceilings using an exposed 9/16", 15/16" or slot T-grid suspension system (NEMA types G, NFG & NFGS). Integral mounting tabs are provided which handle different T-grid heights.

Finish

Housing and Frame: Post-painted, high quality powder coat. Available in white only.

Due to continuing product improvements, Philips Ledalite reserves the right to change the specifications without notice.

Weight

Maximum 25lb.

Electrical

LED boards are easily field replaceable. Fixtures are factory pre-wired and tested for all circuits. Driver access from below the ceiling. Optional armored cable flex whips are supplied in 6' lengths.

Standard Driver

Philips Advance Xitanium 0-10V, 1-100%. Class 2 rated output. Consult Philips Ledalite for other available drivers.

Standard Battery Pack

Philips Bodine, 90 min, 10W, Class 2 rated output, Emergency lumen output = $10W \times luminaire$ efficacy x 1.1. Typical output: 900lm.

Lumen Maintenance

LEDs have been tested by the manufacturer in accordance with IESNA LM-80-08. At an ambient temperature of 25°C, the LED lumen maintenance expectation according to IES TM-21-11 Reported methodology is L₇₀ (12k) >52,000 hrs.

Source Color

LEDs rated for standard color rendering CRI >80, R9 >0 and fixture to fixture color accuracy within 3 SDCM.

Controls

Available with integrated Response Daylight sensor, which dims the luminaire when daylight is present. Contact Philips Ledalite for additional functionality.

Approvals

Certified to UL, IES & CSA Standards. City of Chicago Approved CCEA (housing option C). Type IC Rated.

Warranty

Five-year luminaire limited warranty including LED boards and driver. www.philips.com/warranties.


Environment

Rated for dry or damp locations in operating ambient temperatures of $0-25^{\circ}\mathrm{C}$ (32–77°F). Many luminaire components, such as reflectors, refractors, lenses, sockets, lamp holders, and LEDs are made from various types of plastics which can be adversely affected by airborne contaminants. If sulfur based chemicals, petroleum based products, cleaning solutions, or other contaminants are expected in the intended area of use, consult factory for compatibility. Damage caused by sulfur, chlorine, petroleum based solution or other contaminants are not covered under warranty. Not suitable for natatorium environments.

Integrates with most common T-Grid ceiling types


Mounting

Options and Details




1″ T-Bar Height 1-1/2″ T-Bar Height 1-11/16″ T-Bar Height


Cross Section



Photometry @ CRI>80, 3500K



0% Up / 100% Down



Candela Distribution

Vertical		Hor	izontal A	ngle		Zonal
Angle	0	22.5	45	67.5	90	Lumen:
0	1056	1056	1056	1056	1056	0
5	1071	1068	1067	1065	1065	103
15	1164	1157	1141	1124	1118	325
25	1291	1272	1230	1181	1163	567
35	1291	1269	1203	1133	1106	746
45	1017	1008	969	903	874	737
55	660	664	660	631	615	580
65	359	373	391	395	389	384
75	146	165	191	207	211	198
85	28	38	50	55	56	54
90	0	0	0	0	0	0
95	0	0	0	0	0	0
105	0	0	0	0	0	0
115	0	0	0	0	0	0
125	0	0	0	0	0	0
135	0	0	0	0	0	0
145	0	0	0	0	0	0
155	0	0	0	0	0	0
165	0	0	0	0	0	0
175	0	0	0	0	0	0
180	0	0	0	0	0	0

Fixture photometry has been conducted in accordance with IESNA LM-79-08

IES files for this and other photometric options can be downloaded online at www.lightingproducts.philips.com

Coefficients of Utilization (%)

RCR	Ceiling:		8	10			70			50		0
KCK	Wall:	70	50	30	10	70	50	30	50	30	10	0
0		119	119	119	119	116	116	116	111	111	111	100
1		109	105	101	97	107	102	99	98	95	92	85
2		100	92	85	80	97	90	84	86	81	77	71
3		91	81	73	66	89	79	72	76	70	65	60
4		83	72	63	56	81	70	62	68	61	55	52
5		77	64	55	49	75	63	55	61	53	48	45
6		71	58	49	42	69	57	48	55	47	42	39
7		65	52	43	37	64	51	43	50	42	37	34
8		61	47	39	33	59	47	39	45	38	33	30
9		57	43	35	30	55	43	35	42	34	29	27
10		53	40	32	27	52	39	32	38	31	27	25

Avg. Luminance (cd/m2)

Vertical	Horizontal Angle				
Angle	0	45	90		
55	3684	3684	3433		
65	2720	2962	2947		
75	1806	2363	2610		
85	1029	1837	2057		

Distribution Summary

Hemisphere	0% Up / 100% Down		
Spacing Along (0°)	1.69		
Spacing Across (90°)	1.54		



2'x2', 3600 lm 3000/3500/4000K

Optical Performance

Flux (lm)	3705	3692	3555
Efficacy (lm/W)	86.0	85.9	82.1
Power (W)	43.1	43.0	43.3
ССТ (К)	4012	3472	3073
CRI	83	83	83
R9	24	22	21
x	0.3825	0.4109	0.4358
у	0.3860	0.4023	0.4107
Duv	0.0040	0.0040	0.0030

Electrical Performance @ CRI>80, 3500K

Input Voltage	120V	347V
Input Power	43.0W	37.8W
Input Current	0.36A	0.11A
Power Factor	0.992	0.970
Total Harm. Distortion		9.0%

Tested values – contact technical support for rated values. Off-state power zero unless certain controls are specified.

