




5900 lm/4ft, Indirect/Direct Asym 3000/3500/4000K



Project:		
Spec Type:		
Catalog No:	2225LxBLW	
Qty		
Line Notes:		

Philips Ledalite's MicroSquare gen2 has been re-engineered to furnish your space with the highest quality, discreet, narrow lines of continuous light. Elegant, low glare illumination with wide-throw upper and lower distributions improve visual comfort while allowing increased fixture spacing. This in turn, helps reduce initial and operating costs.


Ordering guide



* Nominal values within a range. Consult photometry data for color temp, lumens & distribution of chosen configuration.

[†] Not all wiring types are available with all configurations. Consult Philips Ledalite for a complete list of available options.

Mounting Hardware





5900 lm/4ft, Indirect/Direct Asym 3000/3500/4000K

Optical System

Upper hemisphere: Light from a linear array of upwardfacing LEDs is shaped into a homogeneous, wide-throw batwing distribution using either a freeform elliptical lens or an engineered light guide panel.

Lower hemisphere: Light from a linear array of downward-facing LEDs is diffused through a transmissive white engineered acrylic lens to deliver a highly uniform, luminous continuum without sacrificing efficacy.

Endcaps

Cubic aluminum endcaps with an internal draw-tight connector to minimize the joint line. Three styles available: solid cube, sculpted black acrylic insert or flush maple insert.

Finish

Standard finish is a textured matte powder coat in white, black or titanium silver.

Housing

Precision aluminum extrusion, post painted.

Weight

Maximum: Surface & Suspended Direct or Indirect - 7.5 lb/4ft; Suspended D/I - 9.5 lb/4ft; Wall D/I - 13.8 lb/4ft

Electrical

Factory pre-wired to section ends with quick-wire connectors.

Standard Driver

Philips Advance Xitanium 0-10V, 1-100%. Class 2 rated output. Consult Philips Ledalite for other available drivers.

Lumen Maintenance

LEDs have been tested by the manufacturer in accordance with IESNA LM-80-08. At an ambient temperature of 25°C, the LED lumen maintenance expectation according to IES TM-21-11 **Reported** methodology is: L₈₀ (12k) >72,000 hrs.

Source Color

LEDs rated for color rendering CRI >80, R9 >0 and fixture to fixture color accuracy within 2 SDCM.

Mounting

Suspended: Tamper-resistant aircraft cable gripper provides unlimited vertical adjustment. Aircraft cable, crimp and cable gripper are independently tested to meet stringent safety requirements.

Wall: A hidden steel rail and bracket system attaches the housing to the wall structure. Mount positioning is fully variable along the modules to accommodate site conditions, spaced up to 41½' on center and within 12" of an end or joint.

Surface: Fixture is mounted flush to surface using hidden brackets at ends and joints.

Approvals

Certified to UL, CSA and IES standards. Certain suspended indirect/direct versions are DesignLights Consortium® qualified. Please see the DLC QPL list for exact catalog numbers (www.designlights.org/QPL).

Warranty

Philips indoor professional luminaires 5 year LED warranty: www.philips.com/warranties.


Environment

Rated for dry or damp locations in operating ambient temperatures 0-40°C (32-104°F). Certain luminaire components may be adversely affected by contaminants. Damage caused by sulfur, chlorine, petroleum based solutions or other contaminants in the area of operation are not covered under warranty. Not suitable for natatorium environments.

Due to continuing product improvements, Philips Ledalite reserves the right to change the specifications without notice.

Dimensions - Cross Section






5900 lm/4ft, Indirect/Direct Asym

3000/3500/4000K


Dimensions - Modules

Wall Mount - Top view, no end caps



Optics and Styles


Endcap Details



5900 lm/4ft, Indirect/Direct Asym 3000/3500/4000K

Photometry - 3500K

Candela Distribution



Vertical	Horizontal Angle 0 45 90 135 180					Zonal
Angle						Lumens
0	476	476	476	476	476	
5	474	474	474	474	474	45
15	454	456	457	456	454	128
25	418	420	422	420	418	193
35	368	372	374	372	368	232
45	307	311	314	311	307	239
55	238	241	244	241	238	215
65	164	166	169	166	164	163
75	89	89	89	89	89	94
85	20	19	16	19	20	23
90	0	0	0	0	0	0
95	149	127	91	64	40	134
105	1063	910	294	269	236	557
115	1863	1266	464	442	413	806
125	1719	1198	592	569	551	779
135	1426	1062	685	664	650	670
145	1161	968	757	749	732	540
155	1007	929	814	831	807	403
165	936	917	849	872	871	251
175	907	898	868	872	876	84
180	871	871	871	871	871	0

s	Values per 4ft unit
	Fixture photometry has been conducted in accordance with IESNA LM-79-08
	IES files for this and other photometric options can be downloaded online at www.lightingproducts.philips.com

Coefficients of Utilization (%)

0.00	Ceiling:		8	0			70			50		0
RCR	Wall:	70	50	30	10	70	50	30	50	30	10	0
0		101	101	101	101	90	90	90	69	69	69	24
1		92	88	84	81	82	78	75	60	58	56	20
2		84	76	71	66	74	68	63	53	49	46	17
3		76	67	60	54	67	60	54	46	42	39	14
4		70	59	52	46	61	53	46	41	36	33	12
5		64	52	45	39	56	47	40	36	32	28	10
6		58	47	39	34	52	42	35	33	28	24	9
7		54	42	34	29	48	38	31	29	25	21	8
8		50	38	31	26	44	34	28	27	22	19	7
9		46	35	27	23	41	31	25	24	20	17	6
10		43	32	25	20	38	28	22	22	18	15	6

Avg. Luminance (cd/m2)

Vertical	Н	orizontal Ang	le
Angle	0	90	180
55	7144	7324	7144
65	6681	6884	6681
75	5920	5920	5920
85	3951	3161	3951

Distribution

Hemisphere	76% Up / 24% Down
Peak/Zenith	2.14
Peak Output	1863 cd
Glare Control	Meets RP-1-12 recommendations for VDT-Critical spaces

5900 lm/4ft, Indirect/Direct Asym 3000/3500/4000K

Optical Performance

Nominal CCT:	3000K	3500К	4000K
Flux (lm)	5397	5560	5538
Efficacy (lm/W)	109.5	113.2	111.9
Power (W)	49.3	49.1	49.5
CCT (K)	3159	3558	4224
CRI	84	84	84
R9	10	9	14
x	0.4248	0.4022	0.3705
У	0.3973	0.3894	0.3684
Duv	-0.0010	0.0000	-0.0010

Electrical Performance - 3500K

Input Voltage	120V	277V	347V		
Input Power	49.1W	48.9W	51.0W		
Input Current	0.41A	0.18A	0.15A		
Power Factor	0.994	0.962	0.964		
Total Harm. Distortion	6.9%	11.3%	10.0%		
Tested values . contact technical support for rated values. Off-state power zero unless certain controls are specified.					

© 2017 Philips Lighting Holding B.V. Il rights reserved. Philips reserves the right to make changes in specifications and/or to discontinue any product at any time without notice or obligation and will not be liable for any consequences resulting from the use of this publication. www.philips.com/luminaires



Philips Lighting, North America Corporation 200 Franklin Square Drive, Somerset, NJ 08873 Tel. 855-486-2216

Philips Lighting Canada Ltd., 281 Hillmount Rd, Markham, ON, Canada L6C 2S3 Tel. 800-668-9008