

PHILIPS

Wall light

myGarden

Drosera

black

LED



17393/30/P0



Enjoy a beautiful garden with light

The Philips Drosera LED outdoor light is fashioned from durable high quality anthracite aluminium. It's design can be used both for wall as ceiling application. It has a powerful diffused warm white light to fully enjoy your outdoor areas.

Sustainable light solutions

- Energy saving

Bring design into your garden

- High quality aluminum and superior synthetics

Advanced light for outdoors

- High power LED
- Philips offers 5 year warranty on the LED module and driver

Special characteristics

- Weather proof
- Long operating life up to 25 years

Highlights

Energy saving



This Philips light conserves energy compared to traditional light sources, helping you to save money on your electricity bills and do your bit for the environment.

High quality material

This Philips lamp is made specifically for outdoor spaces. It's hard-wearing and built to last, so it will light up your garden night after night. It's constructed from high quality die-cast aluminum and superior synthetics.

High power LED



Philips outdoor lighting uses the latest state-of-the-art LED technology. It offers strong light output and high light quality and long lifetime.

5 year warranty on LED system



On top of the standard 2 year warranty for this lamp, Philips offers 5 year warranty on the LED system, meaning the LED module and the driver in this lamp.

Weather proof



This Philips outdoor lamp is especially designed for humid outdoor environments and has undergone rigorous tests to ensure its water resistance. The IP level is described by two figures: the first one refers to the protection level against dust, the second against water. This lamp is designed with IP44: it is protected against splashing water, this product is most common and ideal for general outdoor use.

Long operating life



A light source you can trust. The LED bulb, delivered with this Philips LED lamp, will last up to 25.000 hours (which equals 25 years on basis of an average use of 3 hours / day with an amount of at least of 13.000 on/off switching cycles). It feels so comfortable to think that you won't have to worry about maintenance or light bulb replacement while having the perfect light ambience in your home.

Specifications

Design and finishing

- Color: black
- Material: aluminium

Extra feature/accessory incl.

- 5 years warranty on the LED module: Yes
- Fully weatherproof: Yes
- LED integrated: Yes

Miscellaneous

- Especially designed for: Garden & Patio
- Style: Contemporary
- Type: Wall light
- EyeComfort: No

Product dimensions & weight

- Height: 19 cm
- Length: 19 cm
- Net weight: 0.565 kg
- Width: 7.4 cm

Service

- Warranty: 2 year(s)

Technical specifications

- Lifetime up to: 25,000 hour(s)
- Light source equivalent to traditional bulb of: 83 W
- Total lumen output fixture: 1200 lm
- Bulb technology: 176 V
- Light color: warm white
- Mains power: 50 Hz
- Fixture dimmable: No
- LED: Yes
- Built in LED: Yes
- Energy class included light source: Built in LED
- Number of bulbs: 1
- Wattage bulb included: 12 W
- IP code: IP44
- Class of protection: II – double insulated
- Light source replaceable: No

Design and finishing

- Color: black
- Especially designed for: Garden & Patio
- EAN/UPC – product: 8718696165959
- Warranty: 2 year(s)
- 5 years warranty on the LED module: Yes
- Net weight: 0.565 kg
- Material: aluminium
- Style: Contemporary
- Gross weight: 0.660 kg
- Type: Wall light
- Height: 20.400 cm
- Height: 19 cm
- Lifetime up to: 25,000 hour(s)
- EyeComfort: No
- Length: 8.600 cm
- Width: 19.600 cm
- Material number (12NC): 915005554701
- Length: 19 cm
- Net weight: 0.565 kg
- Width: 7.4 cm
- Light source equivalent to traditional bulb of: 83 W
- Total lumen output fixture: 1200 lm
- Bulb technology: 176 V
- Light color: warm white
- Fully weatherproof: Yes
- LED integrated: Yes
- Mains power: 50 Hz
- Fixture dimmable: No
- LED: Yes
- Built in LED: Yes
- Energy class included light source: Built in LED
- Number of bulbs: 1
- Wattage bulb included: 12 W
- IP code: IP44
- Class of protection: II – double insulated
- Light source replaceable: No



Issue date: 2023-11-08
Version: 0.722

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com