

PHILIPS

Calla Outdoor bollard

Hue White and color
ambiance

LED integrated

White and color light

Low Volt system - base unit

Smart control with Hue bridge*



17421/30/V7



Plug in and light up your outdoors

Simply plug in and enjoy the 16 million colors available to enhance the beauty of your garden or use it more functional for path lighting. The Calla base unit provides 1 light point and all cables / power supply you need to get started.

Limitless possibilities

- Paint your outdoors with 16 million colors
- Unwind with warm to cool white light
- Special light for special occasions

Easy control and comfort

- Set your lights to welcome you home
- Set timers for your convenience
- Control it your way

Full control from smart device with Hue bridge

- Requires a Philips Hue bridge

Specially designed for your outdoors

- Easy to install and extend
- High-quality aluminum and superior synthetics
- Power supply and plug included
- Weather-proof

Highlights

Paint your outdoors



With Philips Hue outdoor lighting there's no limit to the magic you can add. Play with 16 million colors and all shades of white light to create the effect you want. Highlight objects, trees or pathways to make your space stand out. Use the Hue app to save your favorite light settings and recall them whenever you want with the tap of a finger.

Warm to cool white light



Extend your evenings with Philips Hue outdoor lighting. Set the right ambiance on your patio, balcony or porch and relax. From the warm white light of a summer sun, to the ice cool daylight of winter: you can enjoy any shade of white light to fit your mood throughout the year.

Special light for special occasions



Holiday cheer starts here — with smart light! Use your Philips Hue lights to transform your home into a festive experience: bright reds and greens for Christmas, subtle pastels for spring, or even an eerie purple glow to create the most haunted house on the block on Halloween.

Welcome you home



Experience the comfort of your lights turning on automatically when you arrive and turning off when you leave. Unpack your car, enter your house, all with the comfort of the right light. Just set the Hue app to Home or Away mode to switch on all your lights, or let geolocation do it for you, all without touching a button. It's as easy as that.

Set timers for convenience



Enjoy longer evenings outside, finish yard work or just bring the garbage outside after sunset. Have your Philips Hue lights turn on automatically by setting schedules or use sunset / sunrise routine. And of course, you can also turn off or dim your lights this way. You'll never again have to worry whether you've left any lights on.

Control it your way




Connect your Philips Hue lights with the Bridge and start discovering the endless possibilities. Control your lights from your smartphone or tablet via the Philips Hue app, or add the indoor switches to your system to change your lights. Set timers, notifications, alarms, and more for the full Philips Hue experience. Philips Hue even works with Amazon Alexa, Apple Homekit and the Google Assistant to allow you to control your lights with your voice.

Requires a Philips Hue bridge

Connect your Philips Hue lights with the Bridge to control your lights from your smart phone or tablet via the Philips Hue app. Or control your Philips Hue lights with the Philips Hue dimmer indoor switch for on/off and dimming functionalities.

Easy to install and extend

Brighten up dark paths, create highlights in your landscaping, or create a unique ambiance on the patio. You can do it yourself, using Hue spots or bollards. The products are based on low voltage, safe to use and easy to install. No more complexity to get lighting outdoors: go create and extend as you like.

High-quality

The products are made specifically for outdoor use. We are using the highest quality materials to ensure the best performance in the outdoor conditions as well as smart use of materials to optimize radio frequency.

Power supply and plug included

The base unit packs come with all elements you need to get started, this includes light points, power supply, extension cables and connectors. So all you have to do is unpack, install where you like and turn them on.

Weather-proof

This Philips Hue outdoor fixture is specially designed for use in outdoor environments and has undergone rigorous tests to ensure its performance. UL Wet Location rated. This means the product is suitable for use in wet locations.

Specifications

Design and finishing

- Color: black
- Material: aluminium

Extra feature/accessory incl.

- Dimmable with Hue app and switch: Yes

Light characteristics

- Color rendering index (CRI): 80

Miscellaneous

- Especially designed for: Garden & Patio
- Type: Pedestal/post

Power consumption

- Energy Efficiency Label (EEL): G

Product dimensions & weight

- Cable length: 0.5 m
- Height: 9.9 inch
- Length: 4.1 inch
- Net weight: 1.620 lb
- Width: 4.1 inch

Service

- Warranty: 2 year(s)

Technical specifications

- Lifetime up to: 25,000 hour(s)
- Mains power: Range 220 V – 240 V, 50–60 Hz
- Fixture dimmable: Yes
- LED: Yes
- Built in LED: Yes
- Number of bulbs: 1
- Wattage bulb included: 8 W
- IP code: IP65, dust tight, protection from jetting water
- Class of protection: II – double insulated
- Replaceability of light source: Non-Replaceable LED light source
- Replaceability of control gears: Replaceable control gear by end-user

Design and finishing

- Color: black
- Especially designed for: Garden & Patio
- EAN/UPC – product: 046677802097
- Cable length: 0.5 m
- Warranty: 2 year(s)
- Net weight: 0.735 kg
- Material: aluminium
- Gross weight: 2.145 kg
- Color rendering index (CRI): 80
- Type: Pedestal/post
- Height: 298.000 mm
- Lifetime up to: 25,000 hour(s)
- Length: 145.000 mm
- Width: 210.000 mm
- Height: 9.9 inch
- Length: 4.1 inch
- Net weight: 1.620 lb
- Width: 4.1 inch
- Dimmable with Hue app and switch: Yes
- Mains power: Range 220 V – 240 V, 50–60 Hz
- Fixture dimmable: Yes
- LED: Yes
- Built in LED: Yes
- Number of bulbs: 1
- Wattage bulb included: 8 W
- IP code: IP65, dust tight, protection from jetting water
- Class of protection: II – double insulated
- Replaceability of light source: Non-Replaceable LED light source
- Replaceability of control gears: Replaceable control gear by end-user



Issue date: 2023-11-07
Version: 0.904

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com