




5900 lm/4ft, Direct/Indirect Asym 3000/3500/4000K



Project:	
Spec Type:	
Catalog No:	2226LxBLW
Qty	
Line Notes:	

Philips Ledalite's MicroSquare gen2 has been re-engineered to furnish your space with the highest quality, discreet, narrow lines of continuous light. Elegant, low glare illumination with wide-throw upper and lower distributions improve visual comfort while allowing increased fixture spacing. This in turn, helps reduce initial and operating costs.


Ordering guide



* Nominal values within a range. Consult photometry data for color temp, lumens & distribution of chosen configuration.

† Not all wiring types are available with all configurations. Consult Philips Ledalite for a complete list of available options.

Mounting Hardware





5900 lm/4ft, Direct/Indirect Asym 3000/3500/4000K

Optical System

Upper hemisphere: Light from a linear array of upwardfacing LEDs is shaped into a homogeneous, wide-throw batwing distribution using either a freeform elliptical lens or an engineered light guide panel.

Lower hemisphere: Light from a linear array of downward-facing LEDs is diffused through a transmissive white engineered acrylic lens to deliver a highly uniform, luminous continuum without sacrificing efficacy.

Endcaps

Cubic aluminum endcaps with an internal draw-tight connector to minimize the joint line. Three styles available: solid cube, sculpted black acrylic insert or flush maple insert.

Finish

Standard finish is a textured matte powder coat in white, black or titanium silver.

Housing

Precision aluminum extrusion, post painted.

Weight

Maximum: Surface & Suspended Direct or Indirect - 7.5 lb/4ft; Suspended D/I - 9.5 lb/4ft; Wall D/I - 13.8 lb/4ft

Electrical

Factory pre-wired to section ends with quick-wire connectors.

Standard Driver

Philips Advance Xitanium 0-10V, 1-100%. Class 2 rated output. Consult Philips Ledalite for other available drivers.

Lumen Maintenance

LEDs have been tested by the manufacturer in accordance with IESNA LM-80-08. At an ambient temperature of 25°C, the LED lumen maintenance expectation according to IES TM-21-11 **Reported** methodology is: L₈₀ (12k) >72,000 hrs.

Source Color

LEDs rated for color rendering CRI >80, R9 >0 and fixture to fixture color accuracy within 2 SDCM.

Mounting

Suspended: Tamper-resistant aircraft cable gripper provides unlimited vertical adjustment. Aircraft cable, crimp and cable gripper are independently tested to meet stringent safety requirements.

Wall: A hidden steel rail and bracket system attaches the housing to the wall structure. Mount positioning is fully variable along the modules to accommodate site conditions, spaced up to 41½' on center and within 12" of an end or joint.

Surface: Fixture is mounted flush to surface using hidden brackets at ends and joints.

Approvals

Certified to UL, CSA and IES standards. Certain suspended indirect/direct versions are DesignLights Consortium® qualified. Please see the DLC QPL list for exact catalog numbers (www.designlights.org/QPL).

Warranty

Philips indoor professional luminaires 5 year LED warranty: www.philips.com/warranties.


Environment

Rated for dry or damp locations in operating ambient temperatures 0-40°C (32-104°F). Certain luminaire components may be adversely affected by contaminants. Damage caused by sulfur, chlorine, petroleum based solutions or other contaminants in the area of operation are not covered under warranty. Not suitable for natatorium environments.

Due to continuing product improvements, Philips Ledalite reserves the right to change the specifications without notice.

Dimensions - Cross Section






5900 lm/4ft, Direct/Indirect Asym

3000/3500/4000K


Dimensions - Modules

Wall Mount - Top view, no end caps



Optics and Styles


Endcap Details



5900 lm/4ft, Direct/Indirect Asym 3000/3500/4000K

Photometry - 3500K

Candela Distribution



/ertical	0	Horiz 45	ontal A 90	ngle 135	180	Zonal Lumens
Angle 0	922	922	922	922	922	
5	922	922 918	922	922	922 919	0 87
15	881	884	885	884	881	87 249
25 35	812	815	818	815	812	375
	713	719	724	719	713	449
45	594	602	607	602	594	463
55	459	466	473	466	459	416
65	313	318	323	318	313	315
75	167	169	169	169	167	179
85	42	41	38	41	42	48
90	0	0	0	0	0	0
95	105	90	64	45	28	95
105	752	644	208	190	167	394
115	1318	896	329	313	293	571
125	1216	848	419	403	390	552
135	1009	751	485	470	460	474
145	821	685	536	530	518	382
155	712	657	576	588	571	285
165	662	649	601	617	616	178
175	642	635	614	617	620	60
180	616	616	616	616	616	0

Coefficients of Utilization (%)

RCR	Ceiling:			0			70			50		0
	Wall:	70	50	30	10	70	50	30	50	30	10	0
0		106	106	106	106	98	98	98	81	81	81	46
1		97	92	89	85	89	85	82	71	69	66	39
2		88	81	74	69	81	74	69	62	58	55	32
3		80	71	63	57	73	65	59	55	50	46	27
4		73	62	55	48	67	58	51	48	43	39	23
5		67	56	47	41	61	51	44	43	38	33	20
6		62	50	42	36	57	46	39	39	33	29	18
7		57	45	37	31	52	42	34	35	30	26	15
8		53	41	33	28	49	38	31	32	27	23	14
9		49	37	30	24	45	34	28	29	24	20	12
10		46	34	27	22	42	32	25	27	22	18	11

Values per 4ft unit

IESNA LM-79-08 IES files for this and other photometric options can be downloaded online at

Fixture photometry has been conducted in accordance with

www.lightingproducts.philips.com

Avg. Luminance (cd/m2)

Vertical	н	orizontal Ang	le
Angle	0	90	180
55	13777	14197	13777
65	12751	13158	12751
75	11108	11242	11108
85	8296	7506	8296

Distribution

Hemisphere	54% Up / 46% Down
Spacing at 180 °	1.23

5900 lm/4ft, Direct/Indirect Asym 3000/3500/4000K

Optical Performance

Nominal CCT:	3000K	3500K	4000K
Flux (lm)	5409	5571	5555
Efficacy (lm/W)	109.9	113.7	112.4
Power (W)	49.2	49.0	49.4
ССТ (К)	3159	3558	4224
CRI	84	84	84
R9	10	9	14
x	0.4248	0.4022	0.3705
У	0.3973	0.3894	0.3684
Duv	-0.0010	0.0000	-0.0010

Electrical Performance - 3500K

Input Voltage	120V	277V	347V	
Input Power	49.0W	48.2VV	49.0W	
Input Current	0.41A	0.18A	0.14A	
Power Factor	0.999	0.977	0.981	
Total Harm. Distortion	5.6%	9.4%	7.0%	
Tested values . contact technical support for rated values. Off-state power zero unless certain controls are specified.				

© 2017 Philips Lighting Holding B.V. Il rights reserved. Philips reserves the right to make changes in specifications and/or to discontinue any product at any time without notice or obligation and will not be liable for any consequences resulting from the use of this publication. www.philips.com/luminaires



Philips Lighting, North America Corporation 200 Franklin Square Drive, Somerset, NJ 08873 Tel. 855-486-2216

Philips Lighting Canada Ltd., 281 Hillmount Rd, Markham, ON, Canada L6C 2S3 Tel. 800-668-9008