

A gimbal ring with a clean design for a close fit

PHILIPS LIGHTOLIER LYTESPAN GIMBAL RING PAR30 TRACK LUMINAIRE

The Philips Lightolier Lytespan Gimbal Ring PAR30 Track Luminaire offers a minimal form specifically designed to create a close fit with LED lamps, with cleanly miniaturized detailed yoke and ring-shaped lampholder. Front re-lamping for easy maintenance. Unit adjusts horizontally up to 350°, vertically up to 90°.

Ordering guide

example: 9030NWH


Catalog No.	Finish
<input type="text"/>	<input type="text"/>
9030N PAR30 gimbal ring	WH Matte White BK Matte Black AL Aluminum

Lamping: 75W PAR30 maximum. Order separately.

Track: Mounting compatible with all Philips Lytespan Track Systems.

9030N

LYTESPAN GIMBAL RING PAR30 TRACK LUMINAIRE



Project: _____

Location: _____

Catalog No: _____

Fixture Type: _____


Mfg: _____ Lamps: _____ Qty: _____

Notes: _____

9030N

LYTESPAN GIMBAL RING PAR30 TRACK LUMINAIRE

Dimensions



Descriptions

Minimal form specifically designed to create close fit with LED lamps, with cleanly miniaturized detailed yoke and ring-shaped lampholder. Front re-lamping for easy maintenance. Unit adjusts horizontally up to 350°, vertically up to 90°.

Features

- 1 Lytespan attachment fitting:** molded polycarbonate integral color fitter twists onto track and locks on.
- 2 Push tab:** molded polycarbonate, detaches unit
- 3 Yoke:** 3/4" x .05" steel
- 4 Tension spring washer**
- 5 Ring and socket cup:** molded polycarbonate
- 6 Moveable brass contact:** extends connection to 2nd circuit in Advent Lytespan Track
- 7 Polarity Keyway**
- 8 Pivot Mounting:** tensioned 350° stop

Finish

Black and white finished in molded PBT.
Aluminum finish in wet paint.

Material

PBT material to allow scratch free finish, more precise sizing to fit lamps, and miniaturized design.

Electrical

Porcelain socket, medium base, nickel-plated screw shell, no. 18 braided SF-1 leads with silicon sleeving.

Labels

cULus

Leadtime

All items are spec or service smart.



© 2015 Koninklijke Philips N.V. All rights reserved.
Specifications are subject to change without notice.
www.philips.com/luminaires

9030N 04/15 page 2 of 2

Philips Lighting
North America Corporation
200 Franklin Square Drive
Somerset, NJ 08873
Phone: 855-486-2216

Philips Lighting Company
281 Hillmount Road
Markham ON, Canada L6C 2S3
Phone: 800-668-9008