

HADCO

by @signify

Landscape

Transformer

TB100-12 Inground transformer



Project:

Location:

Cat.No:

Type:

Lamps:

Qty:

Notes:

Ordering Guide

Example: TB100-12

Product Code	TB100-12	Transformer
--------------	----------	-------------

Specifications

HOUSING:

Housing and cover are galvanized cast iron material. Gasketing is silicone. Internal transformer is epoxy encapsulated, wrapped in flexible insulation material. Note: Two (2) ½" bottom inlets, one has a plastic sealed plug. One ½" NPS threaded hole in cover to mount fixture.

ELECTRICAL ASSEMBLY:

The transformer is thermally protected and is shielded between the 120V input and the low voltage output, for safety. 12 volt output tap wires available, only. Connectors and / or conduit are sold separately.

CERTIFICATIONS:

ETL Listed to U.S. safety standards for wet locations. cETL listed to Canadian safety standards for wet locations. Manufactured to ISO 9001:2008 Standards.

WARRANTY:

Ten-year limited warranty.

Height :

5" (127mm)

Width:

4" (102mm)

