CHLORIDE

Exit/Emergency

45V series

Architectural LED edge-lit exit sign



Project:	
Location:	
Cat.No:	
Туре:	
Lamps:	Qty:
Notes:	

Ordering guide (back box not included, must be ordered separately)

Example: 45VL1RCAL

Item Type		Family		Mounting ²		No. of Faces		Housing Finish		Letter/Panel Color		Directional Indicator	
T ¹ Blank	Recessed (Trim and panel only) Surface Mount	45VL ER45VXL	LED (AC Only) Emergency LED w/Xtest	Blank ⁶ W ^{3.6} SC ⁷ SW ^{3,7}	Ceiling Wall Surface Ceiling Mount Surface Wall Mount	1 2	Single face Double face	Blank	Satin Aluminum	GC³ GW	Red on Clear Red on White Red on Mirror Green on Clear Green on White Green on Mirror	Blank AL AR AD LR	No chevrons Left Right Left & Right Left or Right or Double Face

Back boxes (must be ordered separately for each recessed item)

Unit	Catalog Number	Description					
45VL	BB45VL	Single or Double Face, Red or Green, AC only					
ER45VXL	BBER45VXL	Single or Double Face, Red or Green, Emergency					

Cut-out Dimension: 14-5/8" x 2-5/8"

Footnotes

- 1. Back box not included, must be ordered separately.
- 2. All exits are recessed mounted, unless indicated to be surface mounted.
- 3. Single face exit only.
- 4. Mirror background simulates clear background on single or double face.
- 5. Can not be used for surface mount.
- 6. Appropriate back box required.
- 7. Back box not required.

DIRECTION	LEGEND			
Panel Front	Panel Back			
<exit< td=""><td></td></exit<>				
EXIT>				
<exit></exit>				
<exit< td=""><td>EXIT></td></exit<>	EXIT>			
<exit></exit>	<exit></exit>			
	Panel Front <exit EXIT> <exit> <exit< td=""></exit<></exit></exit 			

Codes and standards

- UL listed to Standard 924 & damp location optional
- NFPA 101 (Life SafetyCode)
- NEC 70 (National Electric Code) and OSHA Standards
- California Energy Commission

Construction

- Universal mount recessed back box is constructed of 20 gauge zinc-plated steel and contains electronics and battery.
- Exit panel is ultrasonically welded together to eliminate visible hardware .
- Extruded aluminum trim plate on recessed mounted exit signs fit flush on ceiling or wall. Standard finishes are provided in brushed aluminum.
- · Panel is injection molded wedge shape acrylic panel.
- 6" letters with 3/4" stroke.
- Precision molded letters and chevrons (red or green).
- Clear background with optional white or mirror inserts.

Installation

- The recessed back box (rough-in-section) requires a 14-5/8" x 2-5/8" cut out .
- Back box is universal to accommodate recessed ceiling. Surface mounted exits do not require a recessed back box.
- Includes hanger bars for easy mounting.
- The leads on electronics and battery contained in back box include mating plugs to simplify installation .

Electronics

- Dual input voltage: 120/277VAC
- Standard emergency electronics provide a state-of-the art self-test/self-diagnostic circuitry.
- Features an exclusive system that aids in correcting wiring mistakes by checking power and wiring before applying a load to system components.
- All emergency units have built-in circuitry protection/low-voltage battery disconnect and transformer isolation.
- Solid state charger, test switch and green LED AC status indicator along with three red fault indicators.
- Power Consumption
- AC Only: (single or double)
- Red = 2.9 Watts, Green = 3.5 Watts
- Emergency Only: (single or double)
- Red = 2.9 Watts, Green = 3.5 Watts

LED

• The 45VL and ER45VXL exits utilize high lumen output light emitting diodes (LEDs) for greater visibility and uniformed illumination . The LEDs are independently wired with multiple circuits .

Battery

- Maintenance free, sealed nickel cadmium battery.
- Operating temperature range of -20°C to 40°C (-4°F to 104°F).
- Provides a minimum of 90 minutes of emergency illumination .

Warranty

• Five year warranty on unit.

Xtest

Xtest self-diagnostic/self-testing management system is standard.

- Multiple LED indicators flash warnings when attention is needed
- · Micro-controller verifies all systems operation
- Exceeds all UL and NFPA requirements for self-testing.
- Full open circuit testing every hour.

Testing Specifications

Automatic Test:

The system charger and lamps are continually being controlled via pre-determined parameters specific to each model configuration, automatically.The battery is controlled via a true open circuit test each hour after initial installation.Every thirty days the System illuminates lamps under load for 30 minutes, simulating a power outage with a true charger off condition, without affecting long-term battery life. This is above and beyond the requirements of the National Electric Code and/or the National Fire Protection Association. This gives you unequaled control and confidence, knowing you are meeting self-test code requirements each and every month.

Manual Test:

A manual test switch allows for the system to perform the following tests any time: Press Button: Once - 5 second, charger off, no load Twice - 60 second, charger off, lamps on Three - 90 minute, charger off, lamps on 6 second hold - fully reinitializes microprocessor Pressing once during any test will cancel/ abort testing.

Dimensions

Recessed Ceiling

Surface Ceiling

Recessed Wall

2-1/3"

l<mark>⊲^{3-3/4"}→</mark>|1-5/8"

4"

8"

≯||◄

3/4"









15-9/16"

12"

9-3/4"

*

© 2024 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.



Signify North America Corp. 400 Crossing Blvd, Suite 600 Bridgewater, NJ 08807 Telephone: 800-555-0050 Signify Canada Ltd. 281 Hillmount Road, Markham, ON, Canada L6C 2S3 Telephone: 800-668-9008

All trademarks are owned by Signify Holding or their respective owners.