# PHILIPS



# Recessed

Shine


20"x2', 3000 lm 3000/3500/4000K



Project:	
Spec Type:	
Catalog No:	3352xxxxL8xE
Qty	
Line Notes	

A family of uniformly luminous fixtures, Philips Ledalite Shine recessed delivers outstanding performance for superior energy savings. Available in a wide variety of sizes, Shine is a highly efficient and economical solution for any recessed lighting and energy challenge.

# Ordering guide



\* Nominal values within a range. Consult photometry data for CRI, color temp, lumens & distribution of chosen configuration. † Not all wiring types are available with all configurations. Consult Philips Ledalite for a complete list of available options.

Upgrades & Accessories Please indicate with check mark.

Integrated Controls Please indicate with check mark.

Flex Whip (6' length)

Response Daylight Single Zone (DS)



#### **Optical System**

Optical system consists of highly reflective painted interior reflectors and three flat acrylic lenses.

#### Finish

Housing and Frame: Post-painted, high quality powder coat. Available in white.

#### Housing

Die-formed, post-painted, 22 gauge cold-rolled steel. Wire entrance is positioned on top and the sides of housing to allow easy wiring access for installation. Access to boards and drivers from below via side lens cavity. T-bar clips built into the luminaire ends for quick and easy installation. Optional perforated or solid filler panels for 20"x48" fixtures to accommodate 60" ceiling grid.

#### Weight

Maximum 40lbs

#### **Optical System**

Optical system consists of highly reflective painted interior reflectors and three flat acrylic lenses.

#### Electrical

LED boards are easily field replaceable, if required. Fixtures are factory pre-wired and tested for all circuits and emergency battery packs; all leads pulled to a side access with cover plate..

#### **Standard Driver**

Philips Advance Xitanium 0-10V, 1-100%. Class 2 rated output. Consult Philips Ledalite for other available drivers.

#### **Standard Battery Pack**

Philips Bodine, 90 min, 10W, Class 2 rated output, Emergency lumen output = 10W x luminaire efficacy x 1.1. Typical output: 1200lm.

#### Lumen Maintenance

LEDs have been tested by the manufacturer in accordance with IESNA LM-80-08. At an ambient temperature of 25°C, the LED lumen maintenance expectation according to IES TM-21-11 is: L80 (12k) >72,000 hrs (Reported methodology).

#### Source Color

LEDs rated for color rendering CRI >80, R9 >0 and fixture to fixture color accuracy within 3 SDCM.

#### Controls

Available with the following integrated controls: Response daylight sensor (for single zone).

#### Mounting

Compatible with 15/16" lay-in acoustical ceilings using exposed grid suspension (NEMA type G). For 9/16" slot T-grid ceilings, fixture will sit 5/16" above bottom of Tee. Integrated tabs are provided for different T-grid heights.

#### Wiring

Optional armored cable flex whips are supplied in 6' lengths.

#### Approvals

Certified to UL & CSA Standards. City of Chicago Approved CCEA (housing option C).

#### Warranty

Five-year luminaire limited warranty including LED boards and driver.

USA: http://www.usa.lighting.philips.com/support/ support/warranty

Canada: http://www.lighting.philips.ca/support/support/ warranty


#### Environment

Rated for dry & damp locations in operating in ambient temperatures of 25°C. Many luminaire components, such as reflectors, refractors, lenses, and LEDs are made from various types of plastics which can be adversely affected by airborne contaminants. If sulfur based chemicals, petroleum based products, cleaning solutions, or other contaminants are expected in the intended area of use, consult factory for compatibility. Damage caused by sulfur, chlorine, petroleum based solution or other contaminants are not covered under warranty


Due to continuing product improvements, Philips Ledalite reserves the right to change the specifications without notice.

# **Options and Details**


#### Mounting




#### **Cross Section**







## Photometry @ CRI>80, 3500K



0% Up / 100% Down

#### Candela Distribution

Vertical	/ertical Horizontal Angle					Zonal
Angle	0	22.5	45	67.5	90	Lumens
0	1233	1233	1233	1233	1233	0
5	1218	1223	1222	1227	1225	116
15	1149	1164	1162	1177	1172	328
25	1017	1053	1042	1063	1049	483
35	857	907	885	902	886	557
45	684	721	700	724	703	547
55	495	529	509	524	502	462
65	314	339	319	329	312	324
75	154	169	148	158	143	167
85	22	33	17	24	17	33
90	0	0	0	0	0	0
95	0	0	0	0	0	0
105	0	0	0	0	0	0
115	0	0	0	0	0	0
125	0	0	0	0	0	0
135	0	0	0	0	0	0
145	0	0	0	0	0	0
155	0	0	0	0	0	0
165	0	0	0	0	0	0
175	0	0	0	0	0	0
180	0	0	0	0	0	0

Fixture photometry has been conducted in accordance with IESNA LM-79-08

IES files for this and other photometric options can be downloaded online at www.lightingproducts.philips.com

#### Coefficients of Utilization (%)

RCR	Ceiling:		8	0			70			50		0
RCR	Wall:	70	50	30	10	70	50	30	50	30	10	0
0		119	119	119	119	116	116	116	111	111	111	100
1		110	105	101	97	107	103	99	99	96	93	85
2		100	92	86	80	97	90	84	87	82	78	72
3		92	82	74	67	89	80	73	77	71	66	61
4		84	73	64	58	82	71	63	69	62	56	53
5		78	65	56	50	75	64	56	62	55	49	46
6		72	59	50	44	70	58	50	56	49	43	41
7		67	53	45	39	65	53	45	51	44	39	36
8		62	49	41	35	61	48	40	47	40	35	32
9		58	45	37	32	57	44	37	43	36	31	29
10		55	42	34	29	53	41	34	40	33	29	27

#### Avg. Luminance (cd/m2)

Vertical	Horizontal Angle			
Angle	0	45	90	
55	3082	3165	3126	
65	2652	2694	2635	
75	2127	2038	1975	
85	899	698	689	

# **Distribution Summary**

Hemisphere	0% Up / 100% Down
Spacing Along (0°)	1.15
Spacing Across (90°)	1.18

# **Optical Performance**

Flux (lm)	3010	3016	2857	
Efficacy (lm/W)	112.7	112.1	107.0	
Power (W)	26.7	26.9		
ССТ (К)	3900	3348	2995	
CRI	82	82	81	
R9	11	6	3	
x	0.3865	0.4162	0.4397	
У	0.3849	0.4002	0.4092	
Duv	0.0020	0.0020	0.0020	

## Electrical Performance @ CRI>80, 3500K

Input Voltage	120V	277V	347V
Input Power	26.9W	26.6W	25.2W
Input Current	0.22A	0.10A	0.08A
Power Factor	0.997	0.966	0.942
Total Harm. Distortion	6.2%	13.2%	12.0%

 $Tested \ values - \ contact \ technical \ support \ for \ rated \ values. \ Off-state \ power \ zero \ unless \ certain \ controls \ are \ specified.$ 

© 2018 Philips Lighting Holding B.V. Il rights reserved. Philips reserves the right to make changes in specifications and/or to discontinue any product at any time without notice or obligation and will not be liable for any consequences resulting from the use of this publication.

www.philips.com/luminaires



Philips Lighting, North America Corporation 200 Franklin Square Drive, Somerset, NJ 08873 Tel. 855-486-2216

Philips Lighting Canada Ltd., 281 Hillmount Rd, Markham, ON, Canada L6C 2S3 Tel. 800-668-9008