





220 V 240 V






























	System light output (Lm)	Color temperature (K)	kg	<u> </u>	٦
WT120C LED18S/840 PSU L600	2100	4000	0,93	·	'
WT120C LED22S/840 PSU L1200	2900	4000	1,53		
WT120C LED40S/840 PSU L1200	4100	4000	1,53		
WT120C LED34S/840 PSU L1500	3500	4000	1,82		
WT120C LED60S/840 PSU L1500	6000	4000	1,82		
WT120C LED80S/840 PSU L1500	8000	4000	1,82		ر



























## SERVICE (DRIVER REPLACEMENT)

Light source (LED) is non-user replaceable. The light source contained in this luminaire shall only be replaced by the manufacturer or his agent or a similar qualified person.




Do not touch electronic components! Electronic components maybe under high voltage. Caution, risk of electric shock!







_								
		LED18S	LED22S	LED34S	LED40S	LED60S	LED80S	
	Ipeak [A]	8	8	8	8	8	6,02	
	Twidth [μs]	60	60	60	60	60	62	
		Max. Nr of products						
	Drivers / MCB 16A type B [max.]	24	24	24	24	24	18	
lĺ	Drivers / MCB 10A type B [max.]	15	15	15	15	15	11	
	Drivers / MCB 16A type C [max.]	40	40	40	40	40	30	
Ц	Drivers / MCB 10A type C [max.]	24	24	24	24	24	18	



## Maintenance instructions

To assure the lighting quality of this unique LED lighting concept there are only a few instructions regarding the maintenance of this LED luminaire:

- \* Do not stare into LED light beam.
- \* The luminaire shall be installed by a qualified electrician and wired in accordance with the latest IEE electrical regulations or the national requirements.
- \* Above average concentration of sulfur effects the useful lifetime of the product. E.g. Light color changes from white to blue. Typically in chicken & pig farms.

