



6500 lm/4ft w/ 100% Down Kit* 3000/3500/4000K



Brilliant design and intuitive engineering fearlessly combine to deliver unprecedented performance. BoldPlay's striking contrast of effortless style and urban edginess makes a distinctive statement in any space. Available tunable white technology gives you the ability to vary color temperature and intensity, harmonizing lighting with your daily life.

Ordering guide



Mounting Hardware Mount Type Suspension Length Consult separate mounting spec sheet for mount type options Distance from ceiling to top of luminaire in inches Integrated Controls Please indicate with check mark. Endcaps -Sculpted Gloss white flat Response Daylight Single Zone (DS) SpaceWise DT Occupancy & Daylight Sensor (SZ) Gloss black flat Solid flat



^{*} Nominal values within a range. Down kits reduce output & efficacy. Consult photometry data for color temp, lumens & distribution of chosen configuration.

[†] Not all wiring types are available with all configurations. Consult Philips Ledalite for a complete list of available options.

BoldPlay Suspended

6500 lm/4ft w/ 100% Down Kit* 3000/3500/4000K

Optical System

The optical system contains arrays of LEDs edge-lighting a low profile light-guide panel, using total internal reflection to homogenize the sources. The microstructured surface of the panel optimizes light extraction to create an efficacious direct/indirect distribution. Light is purified and controlled by MesoOptics film as it passes through a non-glare acrylic lens. Standard distribution is 75% up / 25% down for suspended and 65% up / 35% down for wall mount version.

Endcaps

Diecast aluminum endcaps.

Suspended: Available in sculpted (standard) or three flat (optional) versions: gloss black, gloss white & solid flat. **Wall**: Three flat versions available: gloss black, gloss white & solid flat.

Finish

Standard finish is a textured matte powder coat in white, black or titanium silver. White sensors only.

Housing

Precision formed 18 gauge cold-rolled steel.

Weight

Maximum: Suspended 3.75lb/ft & Wall 3.0lb/ft.

Electrical

Factory pre-wired to section ends with quick-wire connectors.

Standard Driver

Philips Advance Xitanium 0-10V, 1-100%. Philips Advance Xitanium SR, 5-100% (for SpaceWise DT). Class 2 rated output. Consult Philips Ledalite for other available drivers.

Standard Battery Pack

Philips Bodine, 90 min, 10W, Class 2 rated output, 1000lm nominal (@ 100lm/W; Flux = W x lm/W).

Lumen Maintenance

LEDs have been tested by the manufacturer in accordance with IESNA LM-80-08. At an ambient temperature of 25° C, the LED lumen maintenance expectation according to IES TM-21-11 is: L₈₀ (12k) >72,000 hrs (Reported methodology).

Source Color

LEDs rated for color rendering CRI >80 and fixture to fixture color accuracy within 2 SDCM.

Controls

Suspended version available with the following integrated controls:

Response daylight sensor (for single zone). SpaceWise DT occupancy & daylight sensor w/ advanced grouping & dwell time. SpaceWise DT commissioning via Android phone and Philips Field App. Compatible dimming wireless wall switches are available. For more information, please refer to www.philips.com/spacewise

Mounting

Suspended: Tamper-resistant aircraft cable gripper provides unlimited vertical adjustment. Aircraft cable, crimp and cable gripper are independently tested to meet stringent safety requirements.

Wall: Fixture is mounted flush to wall using hidden wall brackets which attach to existing structure, variable within 2"-5" of end or joint.

Joints

Self-aligning joining system with hands-free pre-joining wire access

Approvals

Certified to UL, CSA and IES standards.
Certain suspended versions without down kits are
DesignLights Consortium® qualified. Please see the DLC
QPL list for exact catalog numbers
(www.designlights.org/QPL).

Warranty


Philips indoor professional luminaires 5 year LED warranty: www.philips.com/warranties.

Environment

Rated for dry or damp locations in operating ambient temperatures 0–40°C (32–104°F). Certain luminaire components may be adversely affected by contaminants. Damage caused by sulfur, chlorine, petroleum based solutions or other contaminants are not covered under warranty. Not suitable for natatorium environments.

Due to continuing product improvements, Philips Ledalite reserves the right to change the specifications without notice.

Dimensions - Cross Section



BoldPlay Suspended 6500 lm/4ft w/ 100% Down Kit*

3000/3500/4000K

Dimensions - Modules

Module length excludes end caps. Nominal mounting spacing for individually mounted modules.

Sculpted


- 4' (1219.2mm) 4 ft. 8' (2438.8mm) ·

Note: Refer to installation instructions for exact mount.

Optics and Styles



8 ft.




Flat


BoldPlay Suspended

6500 lm/4ft w/ 100% Down Kit* 3000/3500/4000K

Photometry - 3500K



0% Up / 100% Down



Candela Distribution

Vertical		Hor	izontal A	ngle		Zonal
Angle	0	22.5	45	67.5	90	Lumens
0	1657	1657	1657	1657	1657	0
5	1663	1663	1671	1679	1681	161
15	1693	1707	1776	1841	1859	505
25	1701	1732	1868	1983	2024	855
35	1569	1588	1675	1734	1742	1029
45	1186	1170	1154	1134	1123	894
55	771	756	734	728	728	669
65	458	452	454	460	470	452
75	189	191	193	197	199	211
85	36	37	41	41	41	48
90	0	0	0	0	0	0
95	2	2	2	2	0	2
105	2	4	4	6	2	4
115	4	4	6	4	4	5
125	4	6	4	4	4	4
135	4	4	4	6	6	3
145	4	4	4	6	6	3
155	4	4	4	4	6	2
165	4	4	4	2	4	1
175	2	2	2	2	2	0
180	2	2	2	2	2	0

Values per 4ft unit

Fixture photometry has been conducted in accordance with IESNA LM-79-08

IES files for this and other photometric options can be downloaded online at www.lightingproducts.philips.com

Coefficients of Utilization (%)

DCD	Ceiling:		8	0			70			50		0
RCR	Wall:	70	50	30	10	70	50	30	50	30	10	0
0		119	119	119	119	116	116	116	111	111	111	100
1		110	106	102	98	107	103	100	99	96	93	86
2		101	93	87	82	98	91	86	88	83	79	73
3		92	83	75	69	90	81	74	78	72	67	63
4		85	74	66	59	83	72	65	70	63	58	54
5		78	66	58	51	76	65	57	63	56	51	47
6		73	60	51	45	71	59	51	57	50	45	42
7		67	54	46	40	66	54	46	52	45	40	37
8		63	50	42	36	61	49	41	48	41	36	33
9		59	46	38	32	57	45	38	44	37	32	30
10		55	42	35	29	54	42	34	41	34	29	27

Avg. Luminance (cd/m2)

Vertical	H	Iorizontal Ang	le
Angle	0	45	90
55	13050	12416	12316
65	10509	10419	10781
75	7101	7249	7471
85	3954	4613	4613

Distribution

Hemisphere	0% Up / 100% Down	
Glare Control	None	
Spacing Along (0°)	1.44	
Spacing Across (90°)	1.5	

BoldPlay Suspended

6500 lm/4ft w/ 100% Down Kit* 3000/3500/4000K

Optical Performance

Nominal CCT:	3000K	3500K	4000K
Flux (lm)	4641	4848	4985
Efficacy (lm/W)	81.6	85.5	88.2
Power (W)	56.9	56.7	56.5
CCT (K)	3045	3312	3931
CRI	84	82	83
R9	10	-1	5
x	0.4338	0.4167	0.3849
у	0.4031	0.3968	0.3837
Duv	0.0000	0.0000	0.0020

Electrical Performance - 3500K

Input Voltage	120V	277V	347V	
Input Power	56.7W	56.2W	56.9W	
Input Current	0.47A	0.21A	0.17A	
Power Factor	0.995	0.987	0.970	
Total Harm. Distortion	9.4%	10.2%	11.0%	

Tested values . contact technical support for rated values. Off-state power zero unless certain controls are specified.

With SpaceWise DT, standby power <0.5W (120V) or <0.8W (277V).

© 2017 Philips Lighting Holding B.V. ll rights reserved. Philips

reserves the right to make changes in specifications and/or to

and will not be liable for any consequences resulting from the

discontinue any product at any time without notice or obligation



Philips Lighting Canada Ltd.,

Tel. 800-668-9008

281 Hillmount Rd, Markham, ON, Canada L6C 2S3

use of this publication.

www.philips.com/luminaires