

A black and white photograph of a Philips Lumec LED Contemporary Lantern luminaire. The luminaire is a tall, black, ornate post with a lantern-style top. The lantern has a decorative crown and a cage-like structure around the light source. The background shows a row of houses with gabled roofs and bare tree branches in the foreground.

**PHILIPS
LUMEC**

Urban

Contemporary Lantern

L80 / L81 Post top luminaires



Timeless **confidence**

The Philips Lumec LED contemporary lantern luminaires bring the lantern style of design into the 21st century. It offers unique lighting that is at once timeless and intimate. Whether in public places or pedestrian spaces, the LED contemporary lantern luminaires are able to accentuate traditional as well as modern architectural environments. The ornamental crown projects confidence and drops down into pure sleek lines around the cage, providing a perfect balance of modern architecture and old world charm. Without question, the contemporary lantern luminaires offer a discerning quality that adds a timeless finishing touch to the most beautiful installations.

Contemporary Lantern

LED luminaires

The Philips Lumec LED contemporary lantern luminaires offer a unique style that appeals to a variety of audiences with various ornamental crown and cage options.

Prior to ordering, consult specification sheets for the most current information, notes, and exclusions.



Benefits

- Meets a range of lighting applications.
- Gently obscures the light source without compromising photometric performance.
- Multiple lumen packages with output of up to 6,148 lumens.
- Type 2, 3, 4, & 5 optics available.
- Highly efficient IP66 optics are protected from the elements and ensure optimal photometric performance.
- Color temperatures 4000K and 3000K are available.
- Dimming driver standard.
- Maximizes energy savings with multiple driver options and programmed dimming options.



Lumen range: 2,253–6,148

Wattage range: 37–81

Efficacy range: 56–78

Post top




L80




L81

Dimensions



L80-LE5-SF80

EPA: 1.32 sq. ft.
Weight: 45 lbs (20.4 kg)



L81-LE3-SF80

EPA: 1.32 sq. ft.
Weight: 44 lbs (20.0 kg)

© 2017 Philips Lighting Holding B.V. All rights reserved.
Philips reserves the right to make changes in specifications and/or to discontinue any product at any time without notice or obligation and will not be liable for any consequences resulting from the use of this publication.



Philips Lighting, North America Corporation
200 Franklin Square Drive, Somerset, NJ 08873
Tel. 855-486-2216

Philips Lighting Canada Ltd.
281 Hillmount Rd, Markham, ON, Canada L6C 2S3
Tel. 800-668-9008