

Project:

Location:


Cat.No:

Type:

Lamps:

Qty:

Notes:



Ordering Guide

Example: WBML14 F A S7

Product Code	WBML14	Aluminum Floodlyte
Lens	F	Frosted Lens *1
Finish	A B G H	Black White Verde Bronze
Mounting	S7	Mounting Stake

*1 Frosted lens is optional.

Specifications

HOUSING:

Die-cast aluminum. Gasketing is silicone. Fully-adjustable swivel arm with vibration-proof locking teeth. Fasteners are 300 series stainless steel. 1/2" NPS male threads to screw onto accessory mounting stake or junction box, sold separately.

FINISH:

Thermoset polyester powdercoat is electrostatically applied after a five-stage conversion cleaning process and bonded by heat fusion thermosetting. Laboratory tested for superior weatherability and fade resistance in accordance with ASTM B117 specifications.

OPTICAL ASSEMBLY:

Frosted tempered glass lens. Clear tempered glass lens.

LAMPING:

35W maximum T3 halogen. Lamp is included with fixture. Lower wattage lamps are acceptable.

ELECTRICAL ASSEMBLY:

Bi-pin socket type (GY6.35) with 250° C high temperature teflon coated wire leads. 12 Volt fixture is pre-wired with 3-ft pigtail of 18-2 AWG, 105° C, SPT-1W wire. Low voltage quick connector, catalog #LVC3 included for easy hook-up to the low voltage supply cable, not included. 12 Volt system requires remote transformer, not included.

WARRANTY:

Three-year limited warranty.

CERTIFICATIONS:

ETL listed to U.S. safety standards for wet locations. cETL listed to Canadian safety standards for wet locations. Manufactured to ISO 9001:2008 Standards.

Height :	Width:	Width:	Length:	Max. Weight:
4 7/8" (123mm)	6 7/8" (175mm)	6 7/8" (175mm)	3 7/8" (96mm)	1.7 lb

