

# iW Flex Compact

Flexible strands of high-intensity LED nodes with tunable white light

Date: \_\_\_\_\_  
 Type: \_\_\_\_\_  
 Firm Name: \_\_\_\_\_  
 Project: \_\_\_\_\_

iW Flex Compact are flexible strands of large, high-intensity, tunable-white LED nodes designed for extraordinary effects and expansive installations without the constraints of luminaire size, shape, or space. Each iW Flex Compact strand consists of 50 individually addressable LED nodes, featuring dynamic integration of power, communication, and control. The flexible form factor accommodates two- and three-dimensional configurations, while high light output affords superior long-distance viewing for architectural accent and perimeter lighting, large-scale signage, and building-covering video displays.

- Tunable white light—iW Flex Compact nodes contain warm and cool white LEDs, allowing you to find just the right color temperature for any application. Color temperatures range from 2700 K to 6500 K.
- Multiple lens options—Clear flat, translucent dome, and narrow beam lenses are standard. Optional marquee lenses, available in clear, semi-frosted, and translucent, snap onto flat lens nodes to create the appearance of bulbs on a traditional theatre marquee. You can mount marquee lenses in front of a substrate or directly to mounted strands.



[Product page](#)

Viewing Angle	36°, 105°, 165°
Lumens per node*	28 to 80
Color Temperature <sup>§</sup>	2700 K to 6500 K

Input Voltage	24 VDC via PDS-60ca 24V, sPDS-60ca 24V, or sPDS-480ca 24V
Power Consumption	1 W
Weight	1 kg (2.2 lb) 4 inch spacing 1.5 kg (3.3 lb) 12 inch spacing
Housing Material	Polycarbonate
Approbations	UL/cUL, FCC Class A, CE
Environment	Dry/Damp/Wet Location, IP66
Applications	Direct View

## Specification Sheets

PDF Download	Viewing Angle	Lumens*	Efficacy	Weight	Item Number	12 NC
<a href="#">Narrow Beam Lens, Black Housing, 4 in On-Center Node Spacing</a>	36°	67	70.1	1.5 kg (3.3 lb)	501-000016-09	912400135824
<a href="#">Narrow Beam Lens, White Housing, 4 in On-Center Node Spacing</a>	36°	67	70.1	1.5 kg (3.3 lb)	501-000016-08	912400135823
<a href="#">Narrow Beam Lens, Black Housing, 12 in On-Center Node Spacing</a>	36°	67	70.1	1.74 kg (3.84 lb)	501-000016-11	912400135826
<a href="#">Narrow Beam Lens, White Housing, 12 in On-Center Node Spacing</a>	36°	67	70.1	1.74 kg (3.84 lb)	501-000016-10	912400135825
<a href="#">Clear Flat Lens, Black Housing, 4 in On-Center Node Spacing</a>	105°	80	79.4	1.5 kg (3.3 lb)	501-000016-01	912400135816
<a href="#">Clear Flat Lens, White Housing, 4 in On-Center Node Spacing</a>	105°	80	79.4	1.5 kg (3.3 lb)	501-000016-00	912400135815
<a href="#">Clear Flat Lens, Black Housing, 12 in On-Center Node Spacing</a>	105°	80	79.4	1.74 kg (3.84 lb)	501-000016-05	912400135820
<a href="#">Clear Flat Lens, White Housing, 12 in On-Center Node Spacing</a>	105°	80	79.4	1.74 kg (3.84 lb)	501-000016-04	912400135819

## Specification Sheets (cont.)

<a href="#">PDF Download</a>	Viewing Angle	Lumens*	Efficacy	Weight	Item Number	12 NC
<a href="#">Translucent Dome Lens, Black Housing, 4 in On-Center Node Spacing</a>	165°	28	29.2	1.5 kg (3.3 lb)	501-000016-03	912400135818
<a href="#">Translucent Dome Lens, White Housing, 4 in On-Center Node Spacing</a>	165°	28	29.2	1.5 kg (3.3 lb)	501-000016-02	912400135817
<a href="#">Translucent Dome Lens, Black Housing, 12 in On-Center Node Spacing</a>	165°	28	29.2	1.74 kg (3.84 lb)	501-000016-07	912400135822
<a href="#">Translucent Dome Lens, White Housing, 12 in On-Center Node Spacing</a>	165°	28	29.2	1.74 kg (3.84 lb)	501-000016-06	912400135821

\* Lumen output measurements comply with IES LM-79-08 testing procedures.

<sup>5</sup> Correlated color temperature (CCT) complies with ANSI C78.377-2008 for the chromaticity of solid state lighting products.



© 2019 Signify Holding. All rights reserved. Specifications are subject to change without notice. No representation or warranty as to the accuracy or completeness of the information included herein is given and any liability for any action in reliance thereon is disclaimed.

Color Kinetics  
[www.colorkinetics.com/lis/intelliwhite/iw-flex-compact/](http://www.colorkinetics.com/lis/intelliwhite/iw-flex-compact/)