

Philips Lighting



EU Declaration of Conformity

Document No.: 0104/C/PLP

Year in which CE Mark was first affixed: 17

Manufacturer: Philips Lighting

I.B.R.S./C.C.R.I. /Numéro 10461

5600 VB Eindhoven, The Netherlands

This declaration of conformity is issued under the sole responsibility of the manufacturer.

Product Range:	NAME: Coreline Recessed - family DESCRIPTION: Recessed luminaires
Product Code:	RC134B...; RC135B...- series (see page 2 to 2) 220V÷240V; 50/60Hz; class. I; IK02; IP20/IP44; LED 27S-37S 830/840; PSU/PSD;

The designated products are in conformity with the following Union harmonization legislation and with the applicable requirements of the following harmonized standards and technical specifications:

Radio Equipment Directive 2014/53/EU

- EN 60598-1:2015+AC:2015+AC:2016
- EN 60598-2-2:2012
- EN61347-1:2015
- EN 62471:2008
- EN 55015:2013+A1:2015
- EN 61000-3-2:2014
- EN 61000-3-3:2013
- ETSI EN 301 489-1 V1.9.2:2011-09
- ETSI EN 300 220-2 V3.1.1:2017
- EN 62493:2015

Restriction of the use of certain Hazardous Substances in electrical and electronic equipment Directive (RoHS), 2011/65/EU

- EN 50581:2012

EcoDesign requirements for energy-related products Directive (ErP), 2009/125/EC and applicable Implementing Measures

- 1194/2012

ENEC-30 certified by:	Certificate number:
ITE PREDOM Division, 53, Krakowiaków Str, 02-255 Warsaw, Poland	ENEC 0164/ENEC/17/M1

and are produced under a quality scheme at least in conformity with ISO 9001 or CENELEC permanent documents.

Eindhoven, August 31th, 2018
High Tech Campus 48
5656 AE Eindhoven The Netherlands

Peter Linssen
Head of Quality,
RBU Prof Europe

Signature:

Philips Lighting



EU Declaration of Conformity


Document No.: 0104/C/PLP

Specification of the products:

Choice sheet of the Recessed luminaires Coreline Recessed family, RC134B...-series, RC135B...-series

Example:

RC134B LED37S/840 PSD W60L60 IA1 OC



Designations used on the marking of luminaires:

1	RC134B	Recessed Luminaire
1	RC135B	Recessed DACH Luminaire
LUMEN OUTPUT		
2	LED27S	2700lm
2	LED37S	3700lm
COLOUR LAMP		
3	830	Warm White (3000K)
3	840	Neutral White (4000K)
LIGHT REGULATION		
4	PSD	power supply driver-programmable output
4	PSU	power supply unit- fixed output
DIMENSIONS		
5	W60L60	Square 597x597mm
5	W62L62	Square 622x622mm
5	W30L120	Rectangular 297x1197mm
INTERACT		
6	IA1	Wireless communication driver
VERSION		
7	OC	Office Compliant
7	NOC	No Office Compliant