













accessories

- For use with emergency lighting units, exit signs and remote lamp heads.

mounting plates


| | | Thermoplastic Round Wedge Base/Big Pin | Thermoplastic Rectangular Wedge Base | Thermoplastic Round Sealed Beam Par 36 | Chrome Plated Steel Sealed Beam Par 36 | Heavy Industrial Sealed Beam Par 36 |
|---|--|--|--------------------------------------|--|--|-------------------------------------|
|  | Chrome Single Head Fits Single Gang Wall Box | MP1 | MP1 | MP1 | MP1S | MP1 |
|  | Double Head Fits Three Gang Wall Box | MP3 | MP3 | MP3 | MP3S | MP3 |
|  | Cast Aluminum Weatherproof Single Head Fits 3" or 4" round box | CRMP1 | CRMP1 | CRMP1 | MP1WP | CRMP1 |
|  | Double Head Fits 3" or 4" round box | CRMP2 | CRMP2 | CRMP2 | MP2WP | CRMP2 |
|  | Cast Aluminum Weatherproof Fits Single Gang Box | | | | | |
|  | Single Head | CSMP1 | CSMP1 | CSMP1 | MP1R | CSMP1 |
| | Double Head | CSMP2 | CSMP2 | CSMP2 | MP2 | CSMP2 |
|  | Thermoplastic 5" Diameter Mounts Dir. to Single Gang Wall Box | | | | | MG1WP |
|  | Single Head, Gray | MW1 | MW1 | MW1 | | included* |
| | Single Head, White | MBLK1 | MBLK1 | MBLK1 | | |
| | Single Head, Black | -WP | -WP | -WP | | |
| | Weatherproof Option | | | | | |
|  | Double Head, Gray | MW2 | MW2 | MW2 | | MG2WP |
|  | Double Head, White | MBLK2 | MBLK2 | MBLK2 | | included* |
| | Double Head, Black | -WP | -WP | -WP | | |
| | Weatherproof Option | | | | | |
|  | Same As Above With 45° Mounting Holes, Fits 3.5" octagonal box | | | | | MG2SWP |
|  | Double Head, Gray | MW2S | MW2S | MW2S | | included* |
| | Double Head, White | -WP | -WP | -WP | | |
| | Weatherproof Option | | | | | |

* Mounting plates include weatherproof gasket.

Emergency Accessories

Accessories

Mounting Plates, Wire Guards
Vandal Shield, Mounting Shelves



Specifier's Reference

| |
|-----------|
| Project |
| Type |
| Model No. |
| Comments |




wire guard and polycarbonate vandal shield

- Wire guards and the polycarbonate vandal shield provide protection from accidental or intentional abuse of emergency lighting equipment.
- Ideal for high traffic areas such as schools, gymnasiums and public buildings.

| Cat.# | For Use With: | A | AA | B | BB | C |
|-------------|--|---|-------------------|--------------------|-------------------|-------------------|
| WG | TMF/TNM Series (200-450 W), ZMF Series (300 & 450 W), Max-Lite Series, Steel-Lite Series, 65X | 20.0" (50.8cm) | 26.0" (66.0cm) | 20.0" (50.8cm) | 26.0" (66.0cm) | 11.0" (27.9cm) |
| WG3 | SPU Series, CFX Series | 10.0" (25.4cm) | 12.0" (30.5cm) | 10.0" (25.4cm) | 12.0" (30.5cm) | 5.5" (14.0cm) |
| WG4 | Wall Mount Thermoplastic, Die Cast, & Steel Standard Exits SPU Series (fully recessed), Patron, SL Series | 12.5" (31.8cm) | 14.5" (36.8cm) | 15.0" (38.1 cm) | 17.0" (43.2cm) | 5.5" (14.0cm) |
| WG5 | 4X Series, 6M/2M Series, CMF/CNM Series (25-100 W), HZ Series, Steel-Lite Series, Symmetry Series (units), Symmetry Series Combination, TMF/TNM Series, (25-150 W), ZMF Series (100 W) | 16.0" (40.6cm) | 18.0" (45.7cm) | 21.0" (53.3cm) | 23.0" (58.4cm) | 10.0" (25.4cm) |
| WG8 | CR6/CR12 Series, Top and Back Mount NEMA Standard Exits | 12.0" (30.5cm) | 14.0" (35.6cm) | 12.0" (30.5cm) | 14.0" (35.6cm) | 13.0" (33.0cm) |
| WG10 | 60 Line | 8.8" (22.4cm) | N/A | N/A | 15.0" (38.1cm) | 15.0" (38.1cm) |
| PCS1 | All Standard Exits, 4X Series, 6M/2M Series, CR6/CR12 Series, 30V, CCHX Combo, CTX Units (All Wall Mount) | 19.4" (W) X 12.3" (H) X 9.0" (D) Outside 19.2" (W) X 12.1" (H) X 8.9" (D) Inside | | | | |
| PVS2 | VE, CXX, 55 Line Contemporary, SL Series (All Wall Mount) | 13.3" (W) X 9.2" (H) X 2.75" (D) Inside | | | | |
| PVS3 | CCAX | 15" (W) X 22" (H) X 8" (D) Inside | | | | |



PCS1



C = depth




PVS2



PVS3

mounting shelves

| Cat.# | For Use With: | A | AA | B |
|-------------|--|---------------------|--------------------|-------------------|
| SSMP | CMF/CNM Series (25-50 W) TMF/TNM Series (25-50 W) | 13.0" (33.02cm) | 8.0" (20.32cm) | 2.75" (6.98cm) |
| SMMP | CMF/CNM Series (75-100 W), TMF/TNM Series (75-150 W), ZMF Series (100 W) | 15.25" (38.73cm) | 9.0" (22.86cm) | 6.0" (15.24cm) |
| SLMP | TMF/TNM Series (200-450 W) ZMF Series (300 W, 450 W) | 19.0" (48.26cm) | 11.0" (27.94cm) | 7.5" (19.05cm) |



©2015 Koninklijke Philips N.V. All rights reserved.
Philips reserves the right to make changes in specifications and/or to discontinue any product at any time without notice or obligation and will not be liable for any consequences resulting from the use of this publication.
philips.com/luminaires



Philips Lighting, North America Corporation
200 Franklin Square Drive, Somerset, NJ 08873
Tel. 855-486-2216

Philips Lighting Canada Ltd.
281 Hillmount Rd, Markham, ON, Canada L6C 2S3
Tel. 800-668-9008