PHILIPS



Recessed

Shine


20"x2', 4000 lm 3000/3500/4000K



Project:	
Spec Type:	
Catalog No:	3352xxxxL8xD
Qty	
Line Notes	

A family of uniformly luminous fixtures, Philips Ledalite Shine recessed delivers outstanding performance for superior energy savings. Available in a wide variety of sizes, Shine is a highly efficient and economical solution for any recessed lighting and energy challenge.

Ordering guide



* Nominal values within a range. Consult photometry data for CRI, color temp, lumens & distribution of chosen configuration. † Not all wiring types are available with all configurations. Consult Philips Ledalite for a complete list of available options.

Upgrades & Accessories Please indicate with check mark.

Integrated Controls Please indicate with check mark.

Flex Whip (6' length)

Response Daylight Single Zone (DS)



Optical System

Optical system consists of highly reflective painted interior reflectors and three flat acrylic lenses.

Finish

Housing and Frame: Post-painted, high quality powder coat. Available in white.

Housing

Die-formed, post-painted, 22 gauge cold-rolled steel. Wire entrance is positioned on top and the sides of housing to allow easy wiring access for installation. Access to boards and drivers from below via side lens cavity. T-bar clips built into the luminaire ends for quick and easy installation. Optional perforated or solid filler panels for 20"x48" fixtures to accommodate 60" ceiling grid.

Weight

Maximum 40lbs

Optical System

Optical system consists of highly reflective painted interior reflectors and three flat acrylic lenses.

Electrical

LED boards are easily field replaceable, if required. Fixtures are factory pre-wired and tested for all circuits and emergency battery packs; all leads pulled to a side access with cover plate..

Standard Driver

Philips Advance Xitanium 0-10V, 1-100%. Class 2 rated output. Consult Philips Ledalite for other available drivers.

Standard Battery Pack

Philips Bodine, 90 min, 10W, Class 2 rated output, Emergency lumen output = 10W x luminaire efficacy x 1.1. Typical output: 1200lm.

Lumen Maintenance

LEDs have been tested by the manufacturer in accordance with IESNA LM-80-08. At an ambient temperature of 25°C, the LED lumen maintenance expectation according to IES TM-21-11 is: L80 (12k) >72,000 hrs (Reported methodology).

Source Color

LEDs rated for color rendering CRI >80, R9 >0 and fixture to fixture color accuracy within 3 SDCM.

Controls

Available with the following integrated controls: Response daylight sensor (for single zone).

Mounting

Compatible with 15/16" lay-in acoustical ceilings using exposed grid suspension (NEMA type G). For 9/16" slot T-grid ceilings, fixture will sit 5/16" above bottom of Tee. Integrated tabs are provided for different T-grid heights.

Wiring

Optional armored cable flex whips are supplied in 6' lengths.

Approvals

Certified to UL & CSA Standards. City of Chicago Approved CCEA (housing option C).

Warranty

Five-year luminaire limited warranty including LED boards and driver.

USA: http://www.usa.lighting.philips.com/support/ support/warranty

Canada: http://www.lighting.philips.ca/support/support/ warranty


Environment

Rated for dry & damp locations in operating in ambient temperatures of 25°C. Many luminaire components, such as reflectors, refractors, lenses, and LEDs are made from various types of plastics which can be adversely affected by airborne contaminants. If sulfur based chemicals, petroleum based products, cleaning solutions, or other contaminants are expected in the intended area of use, consult factory for compatibility. Damage caused by sulfur, chlorine, petroleum based solution or other contaminants are not covered under warranty


Due to continuing product improvements, Philips Ledalite reserves the right to change the specifications without notice.

Options and Details


Mounting




Cross Section







Photometry @ CRI>80, 3500K



0% Up / 100% Down

Candela Distribution

Vertical	Horizontal Angle					Zonal
Angle	0	22.5	45	67.5	90	Lumens
0	1618	1618	1618	1618	1618	0
5	1599	1605	1603	1610	1607	152
15	1508	1528	1525	1545	1538	431
25	1335	1382	1367	1395	1376	633
35	1124	1190	1162	1184	1163	731
45	897	946	919	951	923	718
55	650	694	667	688	659	606
65	412	445	419	431	409	425
75	202	222	194	207	188	219
85	29	43	22	31	22	44
90	0	0	0	0	0	0
95	0	0	0	0	0	0
105	0	0	0	0	0	0
115	0	0	0	0	0	0
125	0	0	0	0	0	0
135	0	0	0	0	0	0
145	0	0	0	0	0	0
155	0	0	0	0	0	0
165	0	0	0	0	0	0
175	0	0	0	0	0	0
180	0	0	0	0	0	0

Fixture photometry has been conducted in accordance with IESNA LM-79-08

IES files for this and other photometric options can be downloaded online at www.lightingproducts.philips.com

Coefficients of Utilization (%)

RCR	Ceiling:		8	0			70			50		0
RCR	Wall:	70	50	30	10	70	50	30	50	30	10	0
0		119	119	119	119	116	116	116	111	111	111	100
1		110	105	101	97	107	103	99	99	96	93	85
2		100	92	86	80	97	90	84	87	82	78	72
3		92	82	74	67	89	80	73	77	71	66	61
4		84	73	64	58	82	71	63	69	62	56	53
5		78	65	56	50	75	64	56	62	55	49	46
6		72	59	50	44	70	58	50	56	49	43	41
7		67	53	45	39	65	53	45	51	44	39	36
8		62	49	41	35	61	48	40	47	40	35	32
9		58	45	37	32	57	44	37	43	36	31	29
10		55	42	34	29	53	41	34	40	33	29	27

Avg. Luminance (cd/m2)

Vertical	He	orizontal Ang	įle
Angle	0	45	90
55	4044	4153	4102
65	3481	3535	3458
75	2791	2675	2592
85	1179	916	905

Distribution Summary

Hemisphere	0% Up / 100% Down
Spacing Along (0°)	1.15
Spacing Across (90°)	1.18

Optical Performance

Flux (lm)	3953	3959	3754
Efficacy (lm/W)	110.1	109.7	104.6
Power (W)	35.9	36.1	35.9
ССТ (К)	3900	3348	2995
CRI	82	82	81
R9	11	6	3
x	0.3865	0.4162	0.4397
У	0.3849	0.4002	0.4092
Duv	0.0020	0.0020	0.0020

Electrical Performance @ CRI>80, 3500K

Input Voltage	120V	277V	347V			
Input Power	36.1W	35.5W	33.8W			
Input Current	0.30A	0.13A	0.10A			
Power Factor	0.998	0.976	0.964			
Total Harm. Distortion	5.2%	11.9%	9.0%			

 $Tested \ values - \ contact \ technical \ support \ for \ rated \ values. \ Off-state \ power \ zero \ unless \ certain \ controls \ are \ specified.$

© 2018 Philips Lighting Holding B.V. Il rights reserved. Philips reserves the right to make changes in specifications and/or to discontinue any product at any time without notice or obligation and will not be liable for any consequences resulting from the use of this publication.

www.philips.com/luminaires



Philips Lighting, North America Corporation 200 Franklin Square Drive, Somerset, NJ 08873 Tel. 855-486-2216

Philips Lighting Canada Ltd., 281 Hillmount Rd, Markham, ON, Canada L6C 2S3 Tel. 800-668-9008