

Spectrum

SPP368

Mounting instruction 安装说明

4441 000 63022



IEC
60598

GB
7000

ta
25°

Gear
IP44
电器腔




Optic
IP65
光源腔

IK05






Type Number 型号	Lamp 光源	Voltage/Frequency 电压/频率	Glass 玻璃	Weight 重量(kg)	Dimming 调光
SPP368	SON-T 150W	220V/50Hz	FFG (铝框平面) / FG (平面)	13.1	
			GB (曲面)	13.3	
	SON-T 250W	220V/50Hz	FFG (铝框平面) / FG (平面)	15	
			GB (曲面)	15.3	
	SON-T 400W	220-230V/50Hz	GB (曲面) / FG (平面)	16.15	SD
		220V/50Hz	FFG (铝框平面) / FG (平面)	16.3	
		240V/50Hz	GB (曲面)	17.3	
			GB (曲面) / FG (平面)	18.15	
			GB (曲面) / FG (平面)	18.15	
	SON-T 600W	220V/50Hz	GB (曲面)	19	SD
		240V/50Hz			


150W/250W/400W




600W



M10 Allen Bolt Max. tighted: 25N.m
M10 内六角螺钉 最大扭矩: 25N.m



Open & Close
开合方式



Philips Lighting Luminaires (Shanghai) Co., Ltd.
Address: No. 2688, Huyi Road, Jiading, Shanghai, China
Postalcode: 201801

飞利浦灯具（上海）有限公司
地址：中国上海市嘉定区马陆镇沪宜公路
邮编：201801

PHILIPS

