




PHILIPS








LUXSPACE SQUARE







DN572B




	LEDs	A	B	C	T° K	P max	kg
DN572B	LED12S	300mm	700mm	≥3mm	827	15 W	1,55 kg
DN572B	LED12S	300mm	700mm	≥3mm	830	12 W	1,55 kg
DN572B	LED12S	300mm	700mm	≥3mm	840	12 W	1,55 kg
DN572B	LED12S	300mm	700mm	≥3mm	930	15 W	1,55 kg
DN572B	LED20S	300mm	700mm	≥3mm	827/830/840/930	20 W	1,55 kg
DN572B	LED24S	300mm	700mm	≥3mm	827/830/840/930	24 W	1,55 kg








DALI dimming
range 1-100%





	XITANIUM 20W LH 0.15-0.5A 48V Is 230V	XITANIUM 20W LH 0.15-0.5A 48V TD/Is 230V	XITANIUM 20W WH 0.15-0.5A 48V TD/Is 230V	XITANIUM 36W LH 0.3-1A 48V I 230V	XITANIUM 36W WH 0.3-1A 54V TD/Is 230V
Electrical Characteristics					
Current AC / Current DC					
Inom (A)	0.12	0.11	0.11	0.18	0.19
Imax (A)	18	16	20.4	14.5	20.4
Tref (µs)	240	220	195	220	195
MCB Nr. Drivers Max					
B-10A	x20	x15	x15	x20	x15
B-16A	x32	x24	x24	x32	x24
C-10A	x33	x24	x24	x32	x24
C-16A	x54	x40	x40	x54	x40

ZBS260 OCS.



Chiffon doux
Soft cloth
Weiches Tuch
Zacht doekje
Panno morbido
Tejido Suave
Blødt stykke stof
Pehmeā kangas
Miekkā sciēcēczka
Pāno macio

EL Version



DN572B EL

LED12S	LED20S	LED24S
Flux NP		
1110 lm	1900 lm	2200 lm
Flux P		
1110 lm	1900 lm	2200 lm

DN572B EL-CLO

LED12S	LED20S	LED24S
Flux NP		
888 lm	1520 lm	1760 lm
Flux P		
888 lm	1520 lm	1760 lm



DALI drivers: With DC supply the current output decrease to 15% → **Setting can be changed by customer.**
Drivers DALI: En Alimentation DC, courant de sortie limité à 15% → Modifiable par l'installateur.
 DALI drivers: De uitgangsstroom wordt 15% lager op DC voeding → **Kan worden aangepast door de klant.**
Equipos DALI: Con DC alimentación, salida de corriente de 15% menos → Ajuste necesita ser cambiado por el cliente.
 DALI drivers: Met DC leveren de huidige output daling tot 15% → **Instelling nodig hebben door de klant worden gewijzigd.**

CLO Version

	LEDs	T° K	Pmax @ t=0h	Pmax @ t=50kh
DN572B	LED12S	827	12 W	15 W
DN572B	LED12S	830	9,6 W	12 W
DN572B	LED12S	840	9,6 W	12 W
DN572B	LED12S	930	12 W	15 W
DN572B	LED20S	827/830/840/930	16 W	20 W
DN572B	LED24S	827/830/840/930	19,2 W	24 W







DO NOT REPROGRAM THE DRIVER
 Constant light Output Option stopped @ 50 000h

CLO Table

Step	time (h)	P %
0	0	80%
1	3000	81%
2	7000	83%
3	10000	84%
4	13000	85%
5	17000	87%
6	20000	88%
7	23000	89%
8	27000	91%
9	30000	92%
10	33000	93%
11	37000	95%
12	40000	96%
13	43000	97%
14	47000	99%
15	50000	100%


RIMLESS Version



RIM Accessory




DN572B □200 ±2mm




6a

PLASTERBOARD GLUE




6b




6c


6d



6e



6f



DN572B LED24S 4000K : Groupe de risque 1 suivant la norme IEC 62471:2006 / Risk group 1 according to IEC 62471:2006



© 2016 Philips Lighting Holding B.V.
All rights reserved. Reproduction in whole or in part is prohibited without the prior written consent of the copyright owner.
The information presented in this document does not form part of any quotation or contract, is believed to be accurate and reliable
and may be changed without notice. No liability will be accepted by the publisher for any consequence of its use.
Publication thereof does not convey nor imply any license under patent- or other industrial or intellectual property rights.

Philips Lighting Holding B.V.
The Netherlands