PHILIPS

Linear

TruGroove recessed


Flush MesoOptics Lens 1500 lm/4ft, 3000/3500/4000K



Project:		
Spec Type:		
Catalog No:	3901LxKQ	
Qty		
Line Notes:		

TruGroove recessed delivers unrivaled performance and a truly innovative design – making a definitive statement in any architectural space. TruGroove recessed corners provide endless opportunities for creative freedom with geometric patterns in walls and ceilings.

Ordering guide




* Nominal values within a range. Consult photometry data for CRI, color temp, lumens & distribution of chosen configuration.

† Not all wiring types are available with all configurations. Consult Philips Ledalite for a complete list of available options.

≈ Available in continuous run lengths from 6ft in steps as small as 1/8in for 1500lm/4ft & 2200lm/4ft symmetric configurations.

 \thickapprox All 3000lm/4ft, 4000lm/4ft and asymmetric configurations can be specified in 1ft steps.






Drywall Trim

Integrated Controls Please indicate with check mark.

Response Daylight Single Zone (DS)



mesoOptics RESPONSE

Drywall Trimless

TruGrvRecsPerfm_15lm_Q 07.18 page 1 of 5

Flush MesoOptics Lens 1500 lm/4ft, 3000/3500/4000K

Optical System

Performance version: White light emitted from the LED sources is internally reflected and exits through the optical lens assembly. This assembly contains acrylic extrusion profiles to retain a layer of MesoOptics film, creating both an uninterrupted continuum of light and an optical batwing distribution.

Definition version: Light passes through a diffuse white acrylic lens to deliver a highly uniform luminous continuum.

Finish

Extruded aluminum trim and die-cast endplates coated with electrostatically applied and thermally cured polyester. Powder coat paint finish. White sensors only.

Housing

Die-formed 20 gauge cold-rolled steel. Multiple upper wire entrances available for continuous row mounting of fixtures.

Weight

Maximum 3.5lb/ft.

Electrical

Factory pre-wired to section ends with quick-wire connectors.

Wall Options

Wall mounted luminaires are only available with the Drywall Trimless ceiling / trim option. A continuous ceiling to wall pattern with an inside corner can use a different ceiling / trim option on the ceiling if required. Regressed lens and 4000 lm/4ft configurations are not available for wall mounting.

Standard Drivers

Philips Advance Xitanium 0-10V, 1-100%. Philips Advance Xitanium Sensor Ready, 5-100%. Class 2 rated output. Consult Philips Ledalite for other available drivers.

Standard Battery Pack

Philips Bodine, 90 min, 10W, Class 2 rated output, Emergency lumen output = 10W x luminaire efficacy x 1.1. Typical output: 1100lm.

Lumen Maintenance

LEDs have been tested by the manufacturer in accordance with IESNA LM-80-08. At an ambient temperature of 25°C in non-insulated contact applications the LED lumen maintenance expectation according to IES TM-21-11 is: L90 (10k) >60,000 hrs (**Reported** methodology) L80 (10k) 120,000 hrs (**Calculated** methodology).

Source Color

LEDs rated for color rendering CRI >80, R9 >0 and fixture to fixture color accuracy within 2 SDCM.

Controls

Certain configurations available with: Response Daylight Sensors SpaceWise DT Occupancy & Daylight Sensors w/ advanced grouping & Dwell Time.

*SpaceWise DT commissioning is via a compatible Android phone and Philips Field App. Compatible wireless dimming wall switches are available for dimming. 347V is not available as a standard option. For more information, please refer to www.philips.com/spacewise

Mounting

Mounting brackets on housing sides support T-Grid installation. 1/16" diameter aircraft cable with self-locking, tamper-resistant, miniature cable gripper provides vertical adjustment for drywall. Aircraft cable, crimp and gripper independently tested to meet stringent safety requirements.

Compatible with 4" Armstrong TechZone ceiling grid.

Joints

Self-aligning joining system with hands-free pre-joining wire access.

Approvals

Certified to UL, CSA and IES standards. Insulation Contact (IC) rated. Most symmetric, flush lens versions between 1500-3000lm/4ft in 3500K and 4000K are DesignLights Consortium® qualified. Please see the DLC QPL list for exact catalog numbers under DLC family code WWWBXQ (www.designlights.org/QPL).


Warranty

Five-year luminaire limited warranty including LED boards and driver. USA: http://www.usa.lighting.philips.com/support/ support/warranty Canada: http://www.lighting.philips.ca/support/support/ warranty


Environment

Rated for dry & damp locations in operating in ambient temperatures of 25°C. Many luminaire components, such as reflectors, refractors, lenses, and LEDs are made from various types of plastics which can be adversely affected by airborne contaminants. If sulfur based chemicals, petroleum based products, cleaning solutions, or other contaminants are expected in the intended area of use, consult factory for compatibility. Damage caused by sulfur, chlorine, petroleum based solution or other contaminants are not covered under warranty


Due to continuing product improvements, Philips Ledalite reserves the right to change the specifications without notice.












Overall Trim

2x2ft Flat

25.7"/653mm

Inside 90° Corner Kit (Side View)




25.9"/658mm

23.6"/600mm

27.1"/689mm

26.3"/667mm






Nominal Length	
2x2ft Outside	26.8"/681mm

TruGrvRecsPerfm_15lm_Q 07.18 page 2 of 5

N/A


Flush MesoOptics Lens 1500 lm/4ft, 3000/3500/4000K


Ceiling Types



Module Details & Dimensions

Standalone






T-grid*

4.72" 120 mm

 ∇


Standalone							
Nominal	Housing	Lens	Mounting Points	Trim - T- Grid	Trim - Drywall Trimless	Trim - Drywa ll Trim	
2ft	23.9″/607mm	23.0″/584mm	23.4"/594mm	23.8″/605mm	26.4"/670mm	24.5"/622mm	
3ft	35.9″/912mm	35.0″/889mm	35.4″/899mm	35.8″/909mm	38.4″/975mm	36.5″/927mm	
4ft	47.9″/1217mm	47.0~/1194mm	47.4″/1204mm	47.8°/1214mm	50.4~/1280mm	48.5"/1232mm	
5ft	59.9″/1521mm	59.0~/1499mm	59.4~/1509mm	59.8″/1519mm	62.4"/1585mm	60.5″/1537mm	
6ft	71.9″/1826mm	71.0″/1803mm	71.4″/1814mm	71.8″/1824mm	74.4″/1889mm	72.5″/1841mm	
8ft	95.9″/2436mm	95.0″/2413mm	95.4″/2423mm	95.8″/2433mm	98.4"/2499mm	96.5″/2451mm	

End-Run




End-Run						
Nominal	Housing	Lens	Mounting Points	Trim -T-Grid	Trim - Drywall Trimless	Trim - Drywa ll Trim
2ft	24.0~/610mm	23.5″/597mm	23.2~/589mm	23.9″/606mm	25.7°/653mm	24.8~/629mm
3ft	36.0~/914mm	35.5″/901mm	35.2″/894mm	35.9″/910mm	37.7″/957mm	36.7″/933mm
4ft	48.0~/1219mm	47.5"/1206mm	47.2°/1199mm	47.9″/1215mm	49.7″/1262mm	48.7″/1238mm
5ft	60.0″/1524mm	59.5″/1511mm	59.2°/1504mm	59.9″/1520mm	61.7″/1567mm	60.7″/1543mm
6ft	72.0″/1829mm	71.5~/1816mm	71.2″/1809mm	71.9″/1825mm	73.7″/1872mm	72.8″/1848mm
8ft	96.0″/2438mm	95.5″/2425mm	95.2″/2418mm	95.8″/2434mm	97.7″/2481mm	96.7″/2457mm
Incremental	L	L-0.5″	L-0.8"	L-0.1″	L+1.7″	L+0.75"

*Compatible with TechZone™ 4" Ceiling Grid



Mid-Run




Mid-Run		
Nominal	Housing & Lens	Mounting Points
2ft	24.0~/610mm	23.2"/589mm
3ft	36.0″/914mm	35.2"/894mm
4ft	48.0″/1219mm	47.2″/1199mm
5ft	60.0″/1524mm	59.2″/1504mm
6ft	72.0″/1829mm	71.2″/1809mm
8ft	96.0″/2438mm	95.2″/2418mm
Incremental	L	L-0.8"

Flush MesoOptics Lens 1500 lm/4ft, 3000/3500/4000K

Photometry @ CRI>80, 3500K

0% Up / 100% Down



All results are according to IESNA LM-79-2008: Approved Method for the Electrical and Photometric Testing of Solid-State Lighting. The U.S. Department of Energy (DOE) verifies product lest data and results.

Visit www.lightingfacts.com for the Label Reference Guide.

Registration Number: F46Z-R53P6P (10/31/2017) Model Number: 39x1LBKQxx04 Type: Luminaire - Linear

Candela Distribution

Vertical	Horizontal Angle					Zonal
Angle	0	22.5	45	67.5	90	Lumens
0	485	485	485	485		0
5	474	482	490	498	494	47
15	447	469	515	557	563	145
25	397	440	534	605	618	240
35	335	393	515	574	573	301
45	269	325	433	454	442	302
55	203	240	308	308	297	247
65	132	148	178	176	168	162
75	60	65	74	74	71	75
85	11	11	13	14	14	16
90	0	0	0	0	0	0
95	0	0	0	0	0	0
105	0	0	0	0	0	0
115	0	0	0	0	0	0
125	0	0	0	0	0	0
135	0	0	0	0	0	0
145	0	0	0	0	0	0
155	0	0	0	0	0	0
165	0	0	0	0	0	0
175	0	0	0	0	0	0
180	0	0	0	0	0	0
						•

Coefficients of Utilization (%)

RCR	Ceiling: Wall:	70	8 50	0 30	10	70	70 50	30	50	50 30	10	0
)	vvdii.	119	119	119	119	116	116	116	111	111	111	100
ĺ		110	105	101	97	107	103	99	99	96	93	85
2		100	92	86	80	97	90	84	87	82	77	72
3		91	81	73	67	89	80	72	77	71	65	61
÷		84	72	64	57	82	71	63	68	61	56	52
5		77	65	56	49	75	63	55	61	54	48	45
5		71	58	49	43	69	57	49	55	48	42	40
7		66	53	44	38	64	52	44	50	43	37	35
3		61	48	40	34	60	47	39	46	39	33	31
9		57	44	36	30	56	43	36	42	35	30	28
0		54	40	33	27	52	40	32	39	32	27	25

Avg. Luminance (cd/m2)

-			
Vertical	He	orizontal Ang	gle
Angle	0	45	90
55	3799	5782	5575
65	3356	4531	4272
75	2483	3074	2957
85	1319	1626	1677

Distribution

Hemisphere	0% Up / 100% Down
Glare Control	Meets RP-1-12 recommendations for VDT-Normal spaces
Spacing Along (0°)	1.14
Spacing Across (90°)	1.64

Values per 4ft unit

IESNA LM-79-08 IES files for this and other photometric options can be downloaded online at

Fixture photometry has been

conducted in accordance with

www.lightingproducts.philips.com

Flush MesoOptics Lens 1500 lm/4ft, 3000/3500/4000K

Optical Performance @ 120V

Nominal Spec:	830	835	840
Flux (lm)	1481	1535	1543
Efficacy (lm/W)	105.0	108.9	110.2
Power (W)	14.1	14.1	14.0
CCT (K)	3040	3437	3948
CRI	84	82	84
R9	16	10	14
x	0.4334	0.4097	0.3836
У	0.4017	0.3945	0.3813
Duv	0.0006	0.0007	0.0013

Electrical Performance @ CRI>80, 3500K

Input Voltage	120V	277V	347V		
Input Power	14.1W	14.3W	14.7W		
Input Current	0.12A	0.05A	0.04A		
Power Factor	0.990	0.940	0.946		
Total Harm. Distortion	11.3%	15.4%	15.5%		
Tested values – contact technical support for rated values. Off-state power zero unless certain controls are specified.					

With SpaceWise DT, standby power <0.5W (120V) or <0.8W (277V).

© 2017 Philips Lighting Holding B.V. Il rights reserved. Philips reserves the right to make changes in specifications and/or to discontinue any product at any time without notice or obligation and will not be liable for any consequences resulting from the use of this publication. www.philips.com/luminaires



Philips Lighting, North America Corporation 200 Franklin Square Drive, Somerset, NJ 08873 Tel. 855-486-2216

Philips Lighting Canada Ltd., 281 Hillmount Rd, Markham, ON, Canada L6C 2S3 Tel. 800-668-9008