

by (s) ignify

Site & Area

PureForm

P26 medium area light



Gardco PureForm LED area medium P26 features a sleek, low profile design and optimal performance. PureForm area medium is designed to achieve maximum pole spacing, with lumen output up to 28,900 lumens. Multiple distribution and shielding options are available to achieve maximum control. A full range of control options provides additional energy savings.

Project:	
_ocation:	
Cat.No:	
Гуре:	
_umens:	Qty:
Notes:	

Ordering guide

example: P26-64L-800-NW-G2-AR-3-120-HIS-MGY

Prefix P26	Number of LEDs	Drive (Current	LED Colo	r - Generatio	n	Mour	nting	Dis	stribution			Volt	age
P26 PureForm area medium, 26"	48L 48 LEDs (3 modules) 64L 64 LEDs (4 modules)	400 500 600 700 600 700 800	400 mA 500 mA 600 mA 700 mA 600 mA 700 mA	NW-G2 CW-G2	Warm White 70 CRI Gene Neutral Wh 70 CRI Gene Cool White 70 CRI Gene Warm Yello 80 CRI Gene	eration 2 ite 4000K, eration 2 5000K, eration 2 w 2700K, eration 2	mus	Arm Mount (standard) ² following mounting kit t be ordered separate accessories) Slip Fitter Mount ³ (fits to 2 ³ / ₈ " O.D. tenon) Wall mount with	2 2- 2- 2- Ty 3 3- 3-	pe 2	AFR	Type 5 Type 5W Auto Front Row -90 Auto Front Row, rotated at 90° t-270 Auto Front Row, rotated at 270°	208 240 277 347 480 UNV	
Options Dimming controls	80L 80 LEDs (5 modules)	700 800 900	700 mA 800 mA 900 mA Motion ser	AM-G2	Balanced W 80CRI Gene Direct Amb Generation	eration 2 ¹ er (590nm)	RAM	wan mount with rea entry permitted Retrofit arm mount	4-	90 Rotated at 90° 270 Rotated at 270°	BLC	rotated at 90° -270 Back Light Control rotated at 270° Luminaire	Finis	h
DCC Dual Circuit FAWS Field Adjusta LLC Integral wire BL Bi-level func DynaDimmer: Autom CS50 Security 509 CM50 Median 50%	ble Wattage Seletes module 4.6.7.17 tionality 4.17 atic Profile Dimming 6 Dimming, 7 hours Dimming, 8 hours 6 Dimming, 7 hours 6 Dimming, 7 hours	ng 3 ^{4,7}		•	ch #3 lens ¹⁵	TLRD5 Twis TLRD7 Twis TLRPC Twis	t Loc t Loc t Loc	trol Button ^{7,8} k Receptacle 5 Pin ⁹ k Receptacle 7 Pin ⁹ k Receptacle sell ^{8,19}	F2 F3 Pole N FP1 FP2 FP3	g Single (120, 277, 347VA Double (208, 240, 480 Canadian Double Pull (240, 480VAC) 8.12 Mount Fusing Single (120, 277, 347VA Double (208, 240, 480 Canadian Double Pull (208, 240, 480VAC) 8 Protection (10kA star Increased 20kA	VAC) ⁸ (208, AC) ⁸ VAC) ⁸	Square Pole Adapter included as standard TB Terminal Block ¹¹ RPA Round Pole Adapter (fits to 3"– 3.9" O.D. pole) ¹² HIS Internal Housing Side Shield	BK WH BZ DGY MGY	Black White Bronze Dark Gray Medium Gray tomer specified Specify optional color or RAL (ex: RAL7024) Custom color (Must supply color chip for required factory quote)

- 1. Extended lead times apply. Contact factory for details.
- 2. Mounts to a 4-5" round pole with adapter included for square poles.
- 3. Limited to a maximum of 45 degrees aiming above horizontal.
- 4. Not available with other dimming control options.
- 5. Not available with motion sensor.
- 6. Not available with photocontrol.
- 7. Not available in 347 or 480V.

- 8. Must specify input voltage.
- Dimming will not be connected to NEMA receptacle if ordering with other control options.
- Not available in 480V. Order photocell separately with TLRD5/7.
- 11. Not available with DCC.
- 12. Not available with SF and WS. RPAs provided with black finish standard.
- 13. HIS not available with Type 5, 5W, and BLC optics.
- 14. Limited to max. 600mA configurations.
- 15. Not available with DD, DCC, and FAWS dimming control options.
- Not available with DD, DCC, FAWS and LLC dimming control options.
- 17. Must specify a motion sensor lens.









Area light

PureForm P26² Accessories (ordered separately, field installed)

Shielding Access	sories	Mounting Accessories								
House Side shie	eld	PureForm PTF2 (pole t	top fitter fits 23/8-21/2" OD x 4" depth tenon)							
Standard optic		PTF2-P26/34-1-90-(F	1 luminaire at 90°							
HIS-48-H ¹	Internal House Side Shield for 48 LEDs	PTF2-P26/34-2-90-(I	F) 2 luminaires at 90°							
	(3 modules)	PTF2-P26/34-2-180-((F) 2 luminaires at 180°							
HIS-64-H1	Internal House Side	PTF2-P26/34-3-90-(I	F) 3 luminaires at 90°							
	Shield for 64 LEDs	PTF2-P26/34-4-90-(I	F) 4 luminaires at 90°							
IIIC 00 III	(4 modules) Internal House Side	PTF2-P26/34-3-120-((F) 3 luminaires at 120°							
HIS-80-H1	Shield for 80 LEDs	PureForm PTF3 (pole t	top fitter fits 3-31/2" OD x 6" depth tenon)							
	(5 modules)	PTF3-P26/34-1-90-(F	1 luminaire at 90°							
		PTF3-P26/34-2-90-(I	F) 2 luminaires at 90°							
Optic at 90 or 2 HIS-48-V 1	270 orientation: Internal House Side	PTF3-P26/34-2-180-((F) 2 luminaires at 180°							
1110 40 V	Shield for 48 LEDs	PTF3-P26/34-3-90-(I	F) 3 luminaires at 90°							
	(3 modules)	PTF3-P26/34-4-90-(I	F) 4 luminaires at 90°							
HIS-64-V1	Internal House Side	PTF3-P26/34-3-120-((F) 3 luminaires at 120°							
	Shield for 64 LEDs (4 modules)	PureForm PTF4 (pole t	top fitter fits 31/2-4" OD x 6" depth tenon)							
HIS-80-V1	Internal House Side	PTF4-P26/34-1-90-(F								
	Shield for 80 LEDs	PTF4-P26/34-2-90-(I	F) 2 luminaires at 90°							
	(5 modules)	PTF4-P26/34-2-180-((F) 2 luminaires at 180°							
		PTF4-P26/34-3-90-(I	F) 3 luminaires at 90°							
		PTF4-P26/34-4-90-(I	F) 4 luminaires at 90°							
		PTF4-P26/34-3-120-((F) 3 luminaires at 120°							
		P26-SF-G2-(F) Sli	p Fitter Mount (fits to 2 3/8" O.D. tenon)							
			etrofit Arm mount kit							
			all mount with surface conduit rear entry permitted							
		• • •	rd deterrent							
		(F) = Specify finish								

- 1. HIS not available with Type 5, 5W, and BLC optics.
- 2. Consult Signify to confirm whether specific accessories are BAA-compliant.

Area light

LED Wattage and Lumen Values - 3000K

		LED		Average		Type 2			Type 3		Type 4			
Ordering Code	Total LEDs	Current (mA)	Color Temp.	System Watts	Lumen Output	BUG Rating	Efficacy (LPW)	Lumen Output	BUG Rating	Efficacy (LPW)	Lumen Output	BUG Rating	Efficacy (LPW)	
P26-48L-400-WW-G2-x	48	400	3000	60	7,673	B2-U0-G2	128	7,420	B1-U0-G2	124	7,698	B1-U0-G2	128	
P26-48L-500-WW-G2-x	48	500	3000	74	9,380	B2-U0-G2	126	9,070	B2-U0-G2	122	9,409	B2-U0-G2	127	
P26-48L-600-WW-G2-x	48	600	3000	89	10,967	B3-U0-G2	123	10,604	B2-U0-G2	119	10,999	B2-U0-G2	124	
P26-48L-700-WW-G2-x	48	700	3000	101	12,477	B3-U0-G2	123	12,064	B2-U0-G2	119	12,514	B2-U0-G2	124	
P26-64L-600-WW-G2-x	64	600	3000	114	14,493	B3-U0-G3	127	14,013	B2-U0-G3	123	14,536	B2-U0-G3	127	
P26-64L-700-WW-G2-x	64	700	3000	133	16,402	B3-U0-G3	124	15,859	B2-U0-G3	119	16,451	B3-U0-G3	124	
P26-64L-800-WW-G2-x	64	800	3000	153	18,384	B3-U0-G3	121	17,775	B3-U0-G3	117	18,438	B3-U0-G3	121	
P26-80L-700-WW-G2-x	80	700	3000	169	20,727	B3-U0-G3	123	20,041	B3-U0-G4	119	20,788	B3-U0-G4	123	
P26-80L-800-WW-G2-x	80	800	3000	192	22,735	B3-U0-G3	119	21,983	B3-U0-G4	115	22,803	B3-U0-G4	119	
P26-80L-900-WW-G2-x	80	900	3000	219	24,409	B3-U0-G3	111	23,602	B3-U0-G4	108	24,482	B3-U0-G4	112	

		LED		Average		Type 5			Type 5W			Type AFR			Type BLC	
Ordering Code	Total LEDs	Current (mA)	Color Temp.	System Watts	Lumen Output	BUG Rating	Efficacy (LPW)									
P26-48L-400-WW-G2-x	48	400	3000	60	7,916	B3-U0-G2	132	7,948	B3-U0-G2	132	7,854	B2-U0-G1	131	5,872	B0-U0-G2	98
P26-48L-500-WW-G2-x	48	500	3000	74	9,674	B3-U0-G2	130	9,716	B4-U0-G2	131	9,599	B2-U0-G2	129	7,178	B0-U0-G2	97
P26-48L-600-WW-G2-x	48	600	3000	89	11,308	B4-U0-G2	127	11,359	B4-U0-G2	128	11,223	B3-U0-G2	126	8,392	B1-U0-G2	94
P26-48L-700-WW-G2-x	48	700	3000	101	12,863	B4-U0-G2	127	12,923	B4-U0-G2	128	12,769	B3-U0-G2	126	9,548	B1-U0-G2	94
P26-64L-600-WW-G2-x	64	600	3000	114	14,940	B4-U0-G2	131	15,011	B4-U0-G2	131	14,832	B3-U0-G2	130	11,091	B1-U0-G2	97
P26-64L-700-WW-G2-x	64	700	3000	133	16,907	B4-U0-G2	127	16,988	B5-U0-G3	128	16,786	B3-U0-G2	126	12,552	B1-U0-G2	95
P26-64L-800-WW-G2-x	64	800	3000	153	18,949	B4-U0-G2	124	19,041	B5-U0-G3	125	18,814	B3-U0-G2	123	14,068	B1-U0-G3	92
P26-80L-700-WW-G2-x	80	700	3000	169	21,363	B5-U0-G3	127	21,468	B5-U0-G3	127	21,212	B3-U0-G2	126	15,861	B1-U0-G3	94
P26-80L-800-WW-G2-x	80	800	3000	192	23,463	B5-U0-G3	122	23,548	B5-U0-G3	123	23,267	B3-U0-G2	121	17,398	B1-U0-G3	91
P26-80L-900-WW-G2-x	80	900	3000	219	25,202	B5-U0-G3	115	25,282	B5-U0-G4	115	24,981	B3-U0-G2	114	18,679	B1-U0-G3	85

LED Wattage and Lumen Values - 4000K

		LED		Average		Type 2			Type 3			Type 4	
Ordering Code	Total LEDs	Current (mA)	Color Temp.	System Watts	Lumen Output	BUG Rating	Efficacy (LPW)	Lumen Output	BUG Rating	Efficacy (LPW)	Lumen Output	BUG Rating	Efficacy (LPW)
P26-48L-400-NW-G2-x	48	400	4000	60	8798	B2-U0-G2	146	8509	B2-U0-G2	142	8827	B2-U0-G2	147
P26-48L-500-NW-G2-x	48	500	4000	74	10755	B2-U0-G2	145	10401	B2-U0-G2	140	10789	B2-U0-G2	145
P26-48L-600-NW-G2-x	48	600	4000	89	12574	B3-U0-G2	141	12160	B2-U0-G2	137	12614	B2-U0-G3	142
P26-48L-700-NW-G2-x	48	700	4000	101	14305	B3-U0-G3	142	13834	B2-U0-G3	137	14351	B2-U0-G3	142
P26-64L-600-NW-G2-x	64	600	4000	114	16617	B3-U0-G3	145	16069	B2-U0-G3	141	16670	B3-U0-G3	146
P26-64L-700-NW-G2-x	64	700	4000	133	18806	B3-U0-G3	142	18186	B3-U0-G3	137	18866	B3-U0-G4	142
P26-64L-800-NW-G2-x	64	800	4000	153	21078	B3-U0-G3	138	20383	B3-U0-G4	134	21145	B3-U0-G4	139
P26-80L-700-NW-G2-x	80	700	4000	169	23764	B3-U0-G3	141	22981	B3-U0-G4	136	23840	B3-U0-G4	141
P26-80L-800-NW-G2-x	80	800	4000	192	26067	B3-U0-G3	136	25208	B3-U0-G4	132	26150	B3-U0-G4	137
P26-80L-900-NW-G2-x	80	900	4000	219	27986	B3-U0-G3	128	27064	B3-U0-G4	123	28076	B3-U0-G4	128

Values from photometric tests performed in accordance with IESNA LM-79 and are representative of the configurations shown. Actual performance may vary due to installation and environmental variables, LED and driver tolerances, and field measurement considerations. It is highly recommended to confirm performance with a photometric layout.

 $NOTE: Some\ data\ may\ be\ scaled\ based\ on\ tests\ of\ similar\ (but\ not\ identical)\ luminaires.\ Contact\ factory\ for\ configurations\ not\ shown.$

Area light

LED Wattage and Lumen Values - 4000K (continued)

		LED		Average		Type 5			Type 5W			Type AFR			Type BLC	
Ordering Code	Total LEDs	Current (mA)	Color Temp.	System Watts	Lumen Output	BUG Rating	Efficacy (LPW)									
P26-48L-400-NW-G2-x	48	400	4000	60	9068	B3-U0-G2	151	9114	B4-U0-G2	152	9006	B2-U0-G1	150	6735	BO-UO-G2	` '
P26-48L-500-NW-G2-x	48	500	4000	74	11083	B4-U0-G2	149	11141	B4-U0-G2	150	11009	B3-U0-G2	148	8233	B1-U0-G2	111
P26-48L-600-NW-G2-x	48	600	4000	89	12954	B4-U0-G2	146	13025	B4-U0-G2	146	12871	B3-U0-G2	145	9626	B1-U0-G2	108
P26-48L-700-NW-G2-x	48	700	4000	101	14736	B4-U0-G2	146	14819	B4-U0-G2	147	14643	B3-U0-G2	145	10951	B1-U0-G2	108
P26-64L-600-NW-G2-x	64	600	4000	114	17116	B4-U0-G2	150	17214	B5-U0-G3	151	17009	B3-U0-G2	149	12721	B1-U0-G2	111
P26-64L-700-NW-G2-x	64	700	4000	133	19369	B5-U0-G3	146	19481	B5-U0-G3	147	19249	B3-U0-G2	145	14396	B1-U0-G3	108
P26-64L-800-NW-G2-x	64	800	4000	153	21708	B5-U0-G3	142	21834	B5-U0-G3	143	21575	B3-U0-G2	141	16136	B1-U0-G3	106
P26-80L-700-NW-G2-x	80	700	4000	169	24474	B5-U0-G3	145	24617	B5-U0-G4	146	24325	B3-U0-G2	144	18192	B1-U0-G3	108
P26-80L-800-NW-G2-x	80	800	4000	192	26880	B5-U0-G3	140	27003	B5-U0-G4	141	26682	B3-U0-G3	139	19955	B1-U0-G3	104
P26-80L-900-NW-G2-x	80	900	4000	219	28872	B5-U0-G3	132	28991	B5-U0-G4	132	28647	B4-U0-G3	131	21425	B1-U0-G4	98

LED Wattage and Lumen Values - 5000K

		LED		Average	e Type 2				Type 3			Type 4	
Ordering Code	Total LEDs	Current (mA)	Color Temp.	System Watts	Lumen Output	BUG Rating	Efficacy (LPW)	Lumen Output	BUG Rating	Efficacy (LPW)	Lumen Output	BUG Rating	Efficacy (LPW)
P26-48L-400-CW-G2-x	48	400	5000	60	8,237	B2-U0-G2	137	7,965	B1-U0-G2	133	8,262	B2-U0-G2	138
P26-48L-500-CW-G2-x	48	500	5000	74	10,069	B2-U0-G2	135	9,736	B2-U0-G2	131	10,100	B2-U0-G2	136
P26-48L-600-CW-G2-x	48	600	5000	89	11,772	B3-U0-G2	132	11,383	B2-U0-G2	128	11,807	B2-U0-G2	133
P26-48L-700-CW-G2-x	48	700	5000	101	13,393	B3-U0-G2	133	12,950	B2-U0-G2	128	13,433	B2-U0-G3	133
P26-64L-600-CW-G2-x	64	600	5000	114	15,557	B3-U0-G3	136	15,042	B2-U0-G3	132	15,603	B2-U0-G3	137
P26-64L-700-CW-G2-x	64	700	5000	133	17,607	B3-U0-G3	133	17,024	B3-U0-G3	128	17,659	B3-U0-G3	133
P26-64L-800-CW-G2-x	64	800	5000	153	19,734	B3-U0-G3	129	19,080	B3-U0-G3	125	19,792	B3-U0-G4	130
P26-80L-700-CW-G2-x	80	700	5000	169	22,248	B3-U0-G3	132	21,512	B3-U0-G4	128	22,315	B3-U0-G4	132
P26-80L-800-CW-G2-x	80	800	5000	192	24,404	B3-U0-G3	127	23,597	B3-U0-G4	123	24,477	B3-U0-G4	128
P26-80L-900-CW-G2-x	80	900	5000	219	26,201	B3-U0-G3	119	25,335	B3-U0-G4	115	26,280	B3-U0-G4	120

		LED		Average		Type 5			Type 5W			Type AFR			Type BLC	
Ordering Code	Total LEDs	Current (mA)	Color Temp.	System Watts	Lumen Output	BUG Rating	Efficacy (LPW)									
P26-48L-400-CW-G2-x	48	400	5000	60	8,497	B3-U0-G2	141	8,532	B4-U0-G2	142	8,430	B2-U0-G1	140	6,304	B0-U0-G2	105
P26-48L-500-CW-G2-x	48	500	5000	74	10,384	B4-U0-G2	140	10,429	B4-U0-G2	140	10,305	B2-U0-G2	139	7,705	B1-U0-G2	104
P26-48L-600-CW-G2-x	48	600	5000	89	12,138	B4-U0-G2	136	12,193	B4-U0-G2	137	12,047	B3-U0-G2	135	9,008	B1-U0-G2	101
P26-48L-700-CW-G2-x	48	700	5000	101	13,808	B4-U0-G2	137	13,872	B4-U0-G2	137	13,706	B3-U0-G2	136	10,249	B1-U0-G2	101
P26-64L-600-CW-G2-x	64	600	5000	114	16,037	B4-U0-G2	140	16,113	B5-U0-G3	141	15,921	B3-U0-G2	139	11,905	B1-U0-G2	104
P26-64L-700-CW-G2-x	64	700	5000	133	18,149	B4-U0-G2	137	18,236	B5-U0-G3	137	18,018	B3-U0-G2	136	13,473	B1-U0-G3	101
P26-64L-800-CW-G2-x	64	800	5000	153	20,340	B5-U0-G3	133	20,439	B5-U0-G3	134	20,195	B3-U0-G2	132	15,101	B1-U0-G3	99
P26-80L-700-CW-G2-x	80	700	5000	169	22,932	B5-U0-G3	136	23,044	B5-U0-G3	137	22,769	B3-U0-G2	135	17,026	B1-U0-G3	101
P26-80L-800-CW-G2-x	80	800	5000	192	25,186	B5-U0-G3	131	25,277	B5-U0-G4	132	24,975	B3-U0-G2	130	18,675	B1-U0-G3	97
P26-80L-900-CW-G2-x	80	900	5000	219	27,053	B5-U0-G3	123	27,138	B5-U0-G4	124	26,815	B3-U0-G3	122	20,051	B1-U0-G3	91

Values from photometric tests performed in accordance with IESNA LM-79 and are representative of the configurations shown. Actual performance may vary due to installation and environmental variables, LED and driver tolerances, and field measurement considerations. It is highly recommended to confirm performance with a photometric layout.

NOTE: Some data may be scaled based on tests of similar (but not identical) luminaires. Contact factory for configurations not shown.

Area light


Predicted Lumen Depreciation Data


Predicted performance derived from LED manufacturer's data and engineering design estimates, based on IESNA LM-80 methodology. Actual experience may vary due to field application conditions. L_{70} is the predicted time when LED performance depreciates to 70% of initial lumen output. Calculated per IESNA TM21-11. Published L_{70} hours limited to 6 times actual LED test hours


Ambient Temperature °C	Driver mA	Calculated L ₇₀ Hours	L ₇₀ per TM-21	Lumen Maintenance % at 60,000 hrs
25°C	up to 900 mA	>100,000 hours	>60,000 hours	>88%


Optical Distributions


Based on 20' mounting height



















Area light

Dimensions


Standard Arm (AR) Weight: 27 Lbs (12.4 Kg) EPA: 0.26ft² (.024m²)




Retrofit Arm (RAM) Weight: 28 Lbs (12.7 Kg) EPA: 0.28ft² (.026m²)




4 module configuration



3 module configuration





Wall (WS) Weight: 30 Lbs. (13.7 Kg)EPA: 0.30ft² (.028m²)




Slip fitter (SF)


Weight: 32 Lbs (14.6 Kg) EPA: 0.38ft² (.035m²)








Standard Arm (AR) drill pattern



Retrofit arm (RAM) drill pattern




Area light

Optical Orientation Information

Standard Optic Position


Luminaires ordered with asymmetric optical systems in the standard optic position will have the optical system oriented as shown below:



Note: The hand hole will normally be located on the pole at the 0° point.

Optic Rotated Left (90°) Optic Position


Luminaires ordered with optical systems in the Optic Rotated Left (90°) optic position will have the optical system oriented as shown below (Type 5 and 5W optics are not available with factory set rotatable optics):



Note: The hand hole will normally be located on the pole at the 0° point.

Optic Rotated Right (270°) Optic Position


Luminaires ordered with optical systems in the Optic Rotated Right (270°) optic position will have the optical system oriented as shown below (Type 5 and 5W optics are not available with factory set rotatable optics):



Note: The hand hole will normally be located on the pole at the 0° point.

Twin Luminaire Assemblies with Type-90/Type-270 Rotated Optical Systems

Twin luminaire assemblies installed with rotated optical systems are an excellent way to direct light toward the interior of the site (Street Side) without additional equipment. It is important, however, that care be exercised to insure that luminaires are installed in the proper location.



Luminaires with Optic Rotated Right (270°) are installed on the LEFT Side of Pole Luminaires with Optic Rotated Left (90°) are installed on the RIGHT Side of Pole

Note: The hand hole location will depend on the drilling configuration ordered for the pole.

Area light

Specifications

Housing

Two-piece sealed enclosure with main part of the housing designed as the structural and heat sink frame enclosed by cover to give its unique form. It also includes integral arm and separate, self-retained hinged, one-piece die cast door frame. All die-cast parts made of low copper die cast aluminum alloy for a high resistance to corrosion. The sleek profile with optimized surface area allows housing to provide excellent convection heat transfer with minimum use of heat fins, giving the freedom to have a clean minimalist aesthetic design. Luminaire housing rated to IP66, tested in accordance to Section 9 of IEC 60598-1.

Vibration resistance

Luminaire is tested and rated 3G over 100,000 cycles conforming to standards set forth by ANSI C136.31-2010. Testing includes vibration in three axes, all performed on the same luminaire.

Light engine

Light engine comprises of a module of 16-LED aluminum metal clad board fully sealed with optics offered in multiples of 3, 4 and 5 modules or 48, 64 and 80 LEDs. Module is RoHS compliant. Color temperatures: 3000K +/- 125K, 4000K, 5000K +/- 200K. Minimum CRI of 70. Also available in 2700K, 3500K, and Direct Amber with extended lead times. Direct Amber LED is narrow spectrum with dominant wavelength at 596 nm (peak wavelength at 601 nm). Contact factory for details. LED light engine is rated IP66 in accordance to Section 9 of IEC 60598-1.

Energy saving benefits

System efficacy up to 150 lms/W with significant energy savings over Pulse Start Metal Halide luminaires. Optional control options provide added energy savings during unoccupied periods.

Optical systems

Type 2, 3, 4, 5, 5W, and AFR distributions available. Internal Shield option mounts to LED optics and is available with Type 2, 3, 4, and AFR distributions including a dedicated BLC optic to provide the best backlight control possible for those stringent requirements around property lines. Types 2, 3, 4, AFR, and BLC when specified and used as rotated, are factory set only. Performance tested per LM-79 and TM-15 (IESNA) certifying its photometric performance. Luminaire designed with 0% uplight (UO per IESNA TM-15).

Mounting

Standard luminaire arm mounts to 4" O.D. round poles. Can also be used with 5" O.D. poles. Square pole adapter included with every luminaire. Round Pole Adapter (RPA) required for 3-3.9" poles. PureForm features a retrofit arm kit. When specified with the retrofit arm (RAM) option, PureForm seamlessly simplifies site conversions to LED by eliminating the need for additional pole drilling on most existing poles. RAM will be boxed separately. Also optional are slipfitter and wall mounting accessories. Note that only fixed mounts (AR, RAM, WS) are required to meet IDA compliance. SF mounting will not meet IDA.

Control options

0-10V dimming (DD): Access to 0-10V dimming leads supplied through back of luminaire (for secondary dimming controls by others). Cannot be used with other control options.

Dual Circuit Control (DCC): Luminaire equipped with the ability to have two separate circuits controlling drivers and light engines independently. Permits separate switching of separate modules controlled by use of two sets of leads, one for each circuit. Not recommended to be used with other control options, motion response, or photocells.

Field Adjustable Wattage Selector (FAWS): Luminaire equipped with the ability to manually adjust the wattage in the field to reduce total luminaire lumen output and light levels. Comes pre-set to the highest position at the lumen output selected. Use chart below to estimate reduction in lumen output desired. Cannot be used with other control options or motion response.

FAWS Position	Percent of Typical Lumen Output
1	25%
2	50%
3	55%
4	65%
5	75%
6	80%
7	85%
8	90%
9	95%
10	100%


Note: Typical value accuracy +/- 5%


Automatic Profile Dimming (CS/CM/CE/CA): Standard dimming profiles provide flexibility towards energy savings goals while optimizing light levels during specific dark hours. Dimming profiles include two dimming settings including dim to 30% or 50% of the total lumen output. When used in combination with not programmed motion response it overrides the controller's schedule when motion is detected. After 5 minutes with no motion, it will return to the automatic diming profile schedule. Automatic dimming profile scheduled with the following settings:

- CS50/CS30: Security for 7 hours night duration (Ex., 11 PM 6 AM)
- CM50/CM30: Median for 8 hours night duration (Ex., 10 PM 6 AM) All above profiles are calculated from mid point of the night. Dimming is set for 6 hours after the mid point and 1 or 2 hours before depending of the duration of dimming. Cannot be used with other dimming control options.

Wireless system (LLC): Optional wireless controller integral to luminaire ready to be connected to a Limelight system (sold by others). The system allows you to wirelessly manage the entire site, independent lighting groups or individual luminaires while on-site or remotely. Based on a high-density mesh network with an easy to use web-based portal, you can conveniently access, monitor and manage your lighting network remotely. Wireless controls can be combined with site and area, pedestrian, and parking garage luminaires as well, for a completely connected outdoor solution. Equipped with motion response with #3 lens for 8-25' mounting heights.

LLC-IMRI3 Luminaire with #3 lens





Motion response options

Bi-Level Infrared Motion Response (BL-IMRI): Motion Response module is mounted integral to luminaire factory pre-programmed to 50% dimming when not ordered with other control options. BL-IMRI is set/operates in the following fashion: The motion sensor is set to a constant 50%. When motion is detected by the PIR sensor, the luminaire returns to full power/ light output. Dimming on low is factory set to 50% with 5 minutes default in "full power" prior to dimming back to low. When no motion is detected for 5 minutes, the motion response system reduces the wattage by 50%, to 50% of the normal constant wattage reducing the light level. Other dimming settings can be provided if different dimming levels are required. This can also be done with FSIR-100 Wireless Remote Programming Tool (contact Technical Support for details).


Area light


Specifications (cont'd)

Infrared Motion Response with Other Controls: When used in combination with other controls (Automatic Dimming Profile), motion response device will simply override controller's schedule with the added benefits of a combined dimming profile and sensor detection. In this configuration, the motion response device cannot be re-programmed with FSIR-100 Wireless Remote Programming Tool. The profile can only be re-programmed via the controller.


Infrared Motion Response Lenses (IMRI3/IMRI7): Infrared Motion Response Integral module is available with two different sensor lens types to accommodate various mounting heights and occupancy detection ranges. Lens #3 (IMRI3) is designed for mounting heights up to 20' with a 40' diameter coverage area. Lens #7 is designed for higher mounting heights up to 40' with larger coverage areas up to 100' diameter coverage area. See charts for approximate detection patterns:


IMRI3 Luminaire with #3 lens





IMRI7 Luminaire with #7 lens





Electrical

Twist-Lock Receptacle (TLRD5/TLRD7/ TLRPC): Twist Lock Receptacle with 5 pins enabling dimming or with 7 pins with additional functionality (by others) can be used with a twistlock photoelectric cell or a shorting cap. Dimming Receptacle Type B (5-pin) and Type D-24 (7-pin) in accordance to ANSI C136.41. Can be used with third-party control system. Receptacle located on top of luminaire housing. When specifying receptacle with twistlock photoelectric cell, voltage must be specified. When ordering Twist-lock receptacle (TLRD5 or TLRD7), photocell or shorting cap is not included. TLRPC is shipped standard with 5 pin.

Driver: Driver efficiency (>90% standard). 120-480V available (restrictions apply). Open/short circuit protection. Optional 0-10V dimming to 10% power. RoHS compliant.

Button Photocontrol (PCB): Button style design for internal luminaires mounting applications. The photocontrol is constructed of a high impact UV stabilized polycarbonate housing. Rated voltage of 120V or 208–277V with a load rating of 1000 VA. The photocell will turn on with 1-4Fc of ambient light.

Surge protection (SP1/SP2): Surge protection device tested in accordance with ANSI/IEEE C62.45 per ANSI/IEEE C62.41.2 Scenario I Category C High Exposure 10kV/10kA waveforms for Line-Ground, Line-Neutral and Neutral-Ground, and in accordance with DOE MSSLC Model Specification for LED Roadway Luminaires Appendix D Electrical Immunity High test level 10kV/10kA. 20kV / 10kA surge protection device that provides extra protection beyond the SP1 10kV/10kA level

Listings

UL/cUL wet location listed to the UL 1598 standard, suitable for use in ambient temperatures from -40° to 40°C (-40° to 104°F). Most PureForm P26 configurations are qualified under Premium DesignLights Consortium® category. Consult DLC Qualified Products list to confirm your specific luminaire selection is approved. CCTs 3000K and warmer are Dark Sky Approved.

Finish

Each standard color luminaire receives a fade and abrasion resistant, electrostatically applied, thermally cured, triglycidal isocyanurate (TGIC) textured polyester powdercoat finish. The surface treatment achieves a minimum of 1000 hours for salt spray resistant finish in accordance with testing performed and per ASTM B117 standard. Standard colors include bronze (BZ), black (BK), white (WH), dark gray (DGY), and medium gray (MGY). Consult factory for specs on optional or custom colors.

Warranty

PureForm luminaires feature a 5-year limited warranty.
See signify.com/warranties for complete details and exclusions.

Buy American Act of 1933 (BAA):

This product is manufactured in one of our US factories and, as of the date of this document, this product was considered a commercially available off-the-shelf (COTS) item meeting the requirements of the BAA. This BAA designation hereunder does not address (i) the applicability of, or availability of a waiver under, the Trade Agreements Act, or (ii) the "Buy America" domestic content requirements imposed on states, localities, and other non-federal entities as a condition of receiving funds administered by the Department of Transportation or other federal agencies. Prior to ordering, please visit www.signify.com/baa to view a current list of BAA-compliant products to confirm this product's current compliance.



© 2022 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Signify North America Corporation 400 Crossing Blvd, Suite 600 Bridgewater, NJ 08807 Telephone 855-486-2216 Signify Canada Ltd. 281 Hillmount Road, Markham, ON, Canada L6C 2S3 Telephone 800-668-9008

Il trademarks are owned by Signify Holding or their respective owners.