






Project:		
Spec Type:		
Catalog No:	24x5LxCAJ	
Qty		
Line Notes		

4500 lm/4ft w/ 100% Down Kit* 3000/3500/4000K

With FloatPlane LED, it's easier than ever to integrate sleek and sporty style into your layout and within budget. Fresh and playful, with Curve and Edge profile options, FloatPlane's performance rivals that of high-end LED luminaires with the affordability of fluorescent. Available tunable white technology gives you the ability to vary color temperature and intensity, harmonizing lighting with your daily life.

Ordering guide



- * Nominal values within a range. Down kits and dust covers reduce output & efficacy. Consult photometry data for color temp, lumens & distribution of chosen configuration.
- † Not all wiring types are available with all configurations. Consult Philips Ledalite for a complete list of available options.

Mount Type Consult separate mounting spec sheet for mount type options Suspension Length Distance from ceiling to top of luminaire in inches Options & Integrated Controls Please indicate with check mark. Dust Cover Response Daylight Single Zone (DS) SpaceWise DT Occupancy & Daylight Sensor (SZ)



4500 lm/4ft w/ 100% Down Kit* 3000/3500/4000K

Optical System

White light emitted from dual linear arrays of lateral-facing LEDs is diffused and redirected into the upper and lower hemispheres with a combination of high reflectivity elements and acrylic diffusers. This delivers a highly efficient 70% up / 30% down indirect/direct distribution with a wide, homogeneous batwing distribution in the upper hemisphere. Twin polymer diffusers on the lower surface combine for an optical aperture of 5-1/2" to deliver a uniform, controlled brightness, maximizing visual comfort and luminaire efficacy. Factory or field installable variable optics kits are available to modify the distribution to 75% down or close to 100% down light. Field installable dust covers available on suspended versions.

Endcaps

Diecast aluminum endcaps in either Edge or Curve versions to match housing.

Finish

High quality powder coated, available in matte white, black or titanium silver. Other custom colors, including Pacific Aqua and Surf Yellow, available on request. White sensors only.

Housing

Precision formed 18 gauge cold-rolled steel. Approx. cross section size: 1.5"h x 8"w (suspended) or 5.7"w (wall mount).

Weight

Maximum: Suspended 3.5lb/ft, Wall 3.3lb/ft

Electrical

Factory pre-wired to section ends with quick-wire connectors

Standard Drivers

Philips Advance Xitanium 0-10V, 1-100%. Philips Advance Xitanium SR, 5-100% (for SpaceWise DT).

Class 2 rated output. Consult Philips Ledalite for other available drivers.

Standard Battery Pack

Philips Bodine, 90 min, 10W, Class 2 rated output, Emergency lumen output = 10W x luminaire efficacy x 1.1. Typical output 1400lm.

Lumen Maintenance

LEDs have been tested by the manufacturer in accordance with IESNA LM-80-08. At an ambient temperature of 25°C, the LED lumen maintenance expectation according to IES TM-21-11 is: L₈₀ (12k) 70,000 hrs suspended / 64,000 hrs wall. (Reported methodology)
L₇₀ (12k) 108,000 hrs suspended / 98,000 hrs wall. (Projected methodology)

Source Color

LEDs rated for color rendering CRI >80, R9 >0 and fixture to fixture color accuracy within 2 SDCM.

Controls

Suspended version available with the following integrated controls:
Response daylight sensor (for single zone).
SpaceWise DT occupancy & daylight sensor w/ advanced grouping & dwell time.
SpaceWise DT commissioning via Android phone and Philips Field App. Compatible dimming wireless wall switches are available. For more information, please refer to www.philips.com/spacewise

Mounting

Suspended: Rapid installation sling mount at joints and ends. High strength aircraft cable and stainless steel gripper provide unlimited vertical adjustment and are independently tested to stringent safety standards. Wall: A hidden steel rail and bracket system attaches to the existing structure and supports housings close to the wall. Mount positioning is fully variable along the modules to accommodate site conditions, spaced up to 4½' on center and within 12" of an end or joint.

loints

Self-aligning, gasketed joining system. Access panels in the driver channel allow quick and hassle-free wiring of modules either before or after mechanical joints are completed.

Approvals

Certified to UL, CSA and IES standards. Certain suspended versions (24x5L) are DesignLights Consortium® qualified. Please see the DLC QPL list for exact catalog numbers (www.designlights.org/QPL).

Warranty


Philips indoor professional luminaires 5 year LED warranty: http://www.philips.com/warranties


Environment

Rated for dry or damp locations in operating ambient temperatures 0-40°C (32-104°F). Certain luminaire components may be adversely affected by contaminants. Damage caused by sulfur, chlorine, petroleum based solutions or other contaminants in the area of operation are not covered under warranty. Not suitable for natatorium environments.

Due to continuing product improvements, Philips Ledalite reserves the right to change the specifications without notice.


Dimensions - Cross Section






4500 lm/4ft w/ 100% Down Kit* 3000/3500/4000K

Dimensions - Modules




Optics and Styles




4500 lm/4ft w/ 100% Down Kit* 3000/3500/4000K

Photometry - 3500K



1% Up / 99% Down



Candela Distribution

Vertical		Hor	izontal A	ngle		Zonal
Angle	0	22.5	45	67.5	90	Lumen:
0	1206	1206	1206	1206	1206	0
5	1202	1202	1202	1202	1201	114
15	1168	1161	1163	1163	1158	328
25	1089	1082	1086	1083	1079	499
35	973	966	970	964	960	605
45	827	820	821	814	814	631
55	650	645	644	638	638	574
65	451	448	444	439	439	439
75	240	236	235	233	233	249
85	53	56	59	60	60	68
90	0	0	0	0	0	0
95	3	1	0	0	0	1
105	4	3	3	1	1	3
115	4	6	4	3	3	4
125	6	6	6	4	4	5
135	7	7	7	6	6	5
145	9	7	7	7	6	4
155	9	7	7	6	6	3
165	7	7	7	7	7	2
175	7	7	6	6	6	1
180	7	7	7	7	7	0

Photometry based on 4ft white luminaire. Dust covers and non-white finishes reduce delivered lumens. Custom color finishes may shift output color temperature.

Fixture photometry has been conducted in accordance with IESNA LM-79-08

IES files for this and other photometric options can be downloaded online at www.lightingproducts.philips.com

Coefficients of Utilization (%)

RCR	Ceiling:		8	0			70			50		0
KCK	Wall:	70	50	30	10	70	50	30	50	30	10	0
0		119	119	119	119	116	116	116	111	111	111	99
1		108	104	99	95	106	101	97	97	94	91	83
2		98	90	83	77	96	88	82	84	79	75	69
3		90	79	71	64	87	77	70	74	68	62	58
4		82	70	61	54	80	69	60	66	59	53	49
5		75	62	53	47	73	61	53	59	51	46	42
6		70	56	47	41	68	55	47	53	46	40	37
7		64	51	42	36	63	50	42	48	41	35	33
8		60	46	38	32	58	46	37	44	37	31	29
9		56	42	34	29	55	42	34	41	33	28	26
10		52	39	31	26	51	39	31	38	31	26	24

Avg. Luminance (cd/m2)

v ei ticai	1.10	JIIZOIILAI AII	КIС
Angle	0	45	90
55	5569	5520	5471
65	5244	5161	5111
75	4567	4458	4431
85	2987	3310	3391

Distribution

Hemisphere	1% Up / 99% Down		
Spacing Along (0 °)	1.27		
Spacing Across (90 °)	1.26		

4500 lm/4ft w/ 100% Down Kit* 3000/3500/4000K

Optical Performance


Nominal CCT:	3000K	3500K	4000K
Flux (lm)	3463	3537	3564
Efficacy (lm/W)	97.3	99.4	100.1
Power (W)	35.6	35.6	35.6
CCT (K)	3028	3344	3907
CRI	81	82	83
R9	2	5	10
x	0.4379	0.4178	0.3867
у	0.4097	0.4036	0.3864
Duv	0.0020	0.0030	0.0030

Electrical Performance - 3500K

Input Voltage	120V	277V	347V
Input Power	35.6W	34.9W	30.2W
Input Current	0.30A	0.13A	0.09A
Power Factor	0.990	0.980	0.956
Total Harm. Distortion	6.0%	12.9%	11.0%

Tested values . contact technical support for rated values. Off-state power zero unless certain controls are specified.

With SpaceWise DT, standby power <0.5W (120V) or <0.8W (277V).



Tel. 800-668-9008