


PHILIPS ADVANCE


High Pressure Sodium Lamp Ballast

Catalog Number 71A8196
For 150W S56
60 Hz CWA
Status: Active

DIMENSIONS AND DATA




0.25" WIDE
2 SLOTS




INPUT VOLTS		120	208	240	277	
CIRCUIT TYPE		CWA				
POWER FACTOR (min)		90%				
REGULATION		±10%				
Line Volts		WITHIN TRAPEZOID				
Lamp Watts						
LINE CURRENT (Amps)						
Operating.....		1.75	1.00	0.88	0.75	
Open Circuit.....		0.80	0.50	0.40	0.35	
Starting.....		1.20	0.70	0.60	0.50	
UL TEMPERATURE RATINGS						
Insulation Class		H(180°C)				
Coil Temperature Code		1029				
MIN. AMBIENT STARTING TEMP.		-20°F or -30°C				
NOM. OPEN CIRCUIT VOLTAGE		180				
INPUT VOLTAGE AT LAMP DROPOUT.....		90	156	180	208	
INPUT WATTS		188				
RECOMMENDED FUSE (Amps).....		5	3	3	3	
CORE and COIL						
Dimension (A)		2.50				
Dimension (B)		4.10				
Weight (lbs.)		8.5				
Lead Lengths		12"				
CAPACITOR REQUIREMENT						
Microfarads		20.0				
Volts (min.)		280				
Fault Current Withstand (amps)						
60 Hz TEST PROCEDURES (Refer to Advance Test Procedure for HID Ballasts - Form 1270)						
High Potential Test (Volts)						
1 minute		2000				
2 seconds		2500				
Open Circuit Voltage Test (Volts)		165-200				
Short-Circuit Current Test (Amps)						
Secondary Current		2.20-2.70				
Input Current.....		0.80-1.20	0.45-0.70	0.40-0.60	0.35-0.55	-

Capacitor: 7C200P30RA



Capacitance: 20
Dia/Oval Dim: 1.58
Height: 3.62
Temp Rating: 105°C

Wiring Diagram:



Ordering Information

Order Suffix

Description

Ignitor:

LI501-H4



Red (X1)
White (X2)
Blue (X3)

Ballast to Lamp Distance
(BTL) = 2 feet
Temp Rating: 105°C

Data is based upon tests performed by Philips Lighting Electronic N.A. in a controlled environment and representative of relative performance. Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.

Philips Lighting Electronic N.A.

10275 West Higgins Road · Rosemont, IL 60018 · Tel:800-322-2086 Fax:888-432-1882
Customer Support/ Technical Service:800-372-3331 · OEM Support: 866-915-5886

06/24/13