






Project:	
Spec Type:	
Catalog No: 7726LxAVA	
Qty	_
Line Notes:	

Incredible efficacy & boundless lighting choices mean the re-engineered Sona suspended LED is destined to become a future classic. Flexible up/down distributions and tailored LED optics mean you always have the right light for every task.

Ordering guide



^{*} Nominal values within a range. Down kits reduce output & efficacy. Consult photometry data for CRI, color temp, lumens & distribution of chosen configuration.


Mounting Hardware

Mount Type

Consult separate mounting spec sheet for mount type options:

Ledalite Suspended Mounting Options

Suspension Length
Distance from ceiling to top of luminaire in inches







[†] Not all wiring types are available with all configurations. Consult Philips Ledalite for a complete list of available options.

6700 lm/4ft 50%-60% Down 3000/3500/4000K

Optical System

 $\label{light Chamber Upper: Lateral-facing LED arrays deliver light into both the upper and lower hemispheres, giving a highly efficient, native 70% up / 30% down distribution with a wide, homogeneous upper batwing distribution. A fully indirect version with a solid lower housing can be specified, as well as a 50% down-light kit option.$

1 Light Chamber Lower: A downward-facing LED array aims light into the lower hemisphere, for a highly efficient, fully direct distribution or optional 80% down version.

2 Light Chambers: Both lateral-facing and downward-facing LED arrays are combined in separate upper and lower chambers for the ultimate in up/down distribution control.

Lenses: On the upper surface an engineered diffuser smooths the light distribution on the ceiling and acts as a dust cover. On the lower surface, two 4" wide optics are available: either a curved, engineered acrylic diffuse lens flush to the housing; or a white louver with regressed diffuser for improved high angle cut-off and visual comfort.

Endcaps

Diecast aluminum endcaps, either Sculpted (curved) or Flat

Finish

High quality powder coated, available in matte white, black or titanium silver. Other custom colors, including pacific aqua, are available on request. White sensors only.

Housing

Precision formed 18 gauge cold-rolled steel. Cross section size (approx.): 2.6"h x 9"w (suspended) or 7.4"w (wall mount).

Weight

Maximum: Suspended 4.9lb/ft, Wall 3.4lb/ft

Electrical

Factory pre-wired to section ends with quick-wire connectors.

Standard Drivers

Philips Advance Xitanium 0-10V, 1-100%. Philips Advance Xitanium Sensor Ready, 5-100%. Class 2 rated output. Consult Philips Ledalite for other available drivers.

Standard Battery Pack

Philips Bodine, 90 min, 10W, Class 2 rated output, Emergency lumen output = 10W x luminaire efficacy x 1.1. Typical output: suspended 1400lm, wall 1200lm.

Lumen Maintenance

LEDs have been tested by the manufacturer in accordance with IESNA LM-80-08. At an ambient temperature of 25°C, the LED lumen maintenance expectation according to IES TM-21-11 is: L80 (12k) >72,000 hrs (Reported methodology) L80 (12k) 110,000 hrs (Projected methodology).

Source Color

LEDs rated for color rendering CRI >80, R9 >0 and fixture to fixture color accuracy within 3 SDCM.

Controls

Suspended version (1 light chamber only) available with the following integrated controls: Response Daylight Sensors SpaceWise DT Occupancy & Daylight Sensors w/ advanced grouping & Dwell Time.

*SpaceWise DT commissioning is via a compatible Android phone and Philips Field App. Compatible wireless dimming wall switches are available for dimming. 347V is not available as a standard option. For more information, please refer to www.philips.com/spacewise

Mounting

Suspended: Rapid installation sling mount at joints and ends. High strength aircraft cable and stainless steel gripper provide unlimited vertical adjustment and are independently tested to stringent safety standards. Variable mounting along the length of the housing is available for certain configurations upon request. Wall: A hidden steel rail and bracket system attaches to the existing structure and supports housings close to the wall. Mount positioning is fully variable along the modules to accommodate site conditions, spaced up to 4½' on center and within 6" of an end or joint.

Joints

Self-aligning, gasketed joining system with hands-free wiring feature.

Approvals

Certified to UL, CSA and IES standards. Most suspended versions (except 1 light chamber down with louver) are DesignLights Consortium® qualified. Please see the DLC QPL list for exact catalog numbers (www.designlights.org/QPL).

Warranty


Philips indoor professional luminaires 5 year LED warranty: www.philips.com/warranties

Environment

Rated for dry or damp locations in operating ambient temperatures 0-40°C (32-104°F). Certain luminaire components may be adversely affected by contaminants. Damage caused by sulfur, chlorine, petroleum based solutions or other contaminants in the area of operation are not covered under warranty. Not suitable for natatorium environments.

Due to continuing product improvements, Philips Ledalite reserves the right to change the specifications without notice.


Dimensions - Cross Section




6700 lm/4ft 50%-60% Down 3000/3500/4000K

Dimensions - Modules

Suspended - Side view, no end caps




Optics and Styles




6700 lm/4ft 50%-60% Down 3000/3500/4000K

Photometry @ CRI>80, 3500K



54% Up / 46% Down



Candela Distribution

Vertical			izontal A		00	Zonal
Angle	0	22.5	45	67.5	90	Lumens
0	1612	1612	1612	1612	1612	
5	1562	1579	1586	1602	1609	150
15	1347	1376	1431	1504	1537	404
25	1065	1106	1196	1318	1386	556
35	752	807	920	1069	1161	586
45	443	505	641	791	885	501
55	235	257	378	501	567	347
65	146	156	185	246	276	201
75	75	80	91	103	106	98
85	19	23	33	34	30	33
90	1	9	18	19	8	0
95	51	67	76	80	79	82
105	172	214	263	290	289	268
115	316	430	571	639	653	528
125	463	643	894	1052	1088	740
135	541	692	933	1122	1179	693
145	568	658	824	954	997	507
155	579	622	714	794	822	329
165	585	599	631	666	680	180
175	588	589	585	588	589	57
180	580	580	580	580	580	0

Values per 4ft unit

Fixture photometry has been conducted in accordance with IESNA LM-79-08

IES files for this and other photometric options can be downloaded online at www.lightingproducts.philips.com

Coefficients of Utilization (%)

nen	Ceiling:		8	0			70			50		0
RCR	Wall:	70	50	30	10	70	50	30	50	30	10	0
0		106	106	106	106	97	97	97	81	81	81	46
1		98	94	90	87	89	86	83	72	70	68	40
2		89	83	77	72	82	76	71	64	61	58	35
3		82	73	66	61	75	68	62	57	53	49	30
4		76	65	58	52	69	61	54	51	47	43	27
5		70	59	51	45	64	54	48	46	41	37	24
6		64	53	45	40	59	49	42	42	37	33	21
7		60	48	40	35	55	45	38	38	33	29	19
8		55	44	36	31	51	41	34	35	30	26	17
9		52	40	33	28	48	37	31	32	27	24	16
10		48	37	30	25	45	34	28	30	25	22	15

Avg. Luminance (cd/m2)

Vertical	Horizontal Angle				
Angle	0	45	90		
55	3686	5594	8246		
65	3101	3611	5235		
75	2585	2696	3017		
85	1876	2201	1811		

Distribution

Hemisphere	54% Up / 46% Down				
Glare Control	Meets RP-1-12 recommendations for VDT-Normal spaces				
Spacing Along (0°)	0.92				
Spacing Across (90°)	1.18				

6700 lm/4ft 50%-60% Down 3000/3500/4000K

Optical Performance @ 120V

Nominal Spec:	3000K	3500K	4000K	
Flux (lm)	5981	6261	6405	
Efficacy (lm/W)	112.6	117.9	120.2	
Power (W)	53.1	53.1	53.3	
CCT (K)	3020	3378	3958	
CRI	84	83	84	
R9	11	9	11	
x	0.4361	0.4138	0.3835	
у	0.4048	0.3976	0.3820	
Duv	0.0003	0.0012	0.0016	

Electrical Performance @ CRI>80, 3500K

Input Voltage	120V	277V	347V
Input Power	53.1W	53.0VV	53.5W
Input Current	0.45A	0.20A	0.16A
Power Factor	0.994	0.951	0.948
Total Harm. Distortion	8.3%	11.7%	12.0%

Tested values – contact technical support for rated values. Off-state power zero unless certain controls are specified.

