

The HCF Compact Fluorescent luminaire is energy saving and efficient. The prismatic acrylic reflector is available in an open version with lens assemblies optional. The precision spun heavy gauge aluminum reflector is available in an open or enclosed version.

The low bay optical assembly consists of a precision spun painted aluminum reflector and injection molded prismatic acrylic lens.



HCF


COMPACT FLUORESCENT LUMINAIRE

**COST EFFICIENT
& IDEAL FOR GYMS,
WAREHOUSES,
INDUSTRIAL,
EDUCATIONAL, RETAIL,
AND COMMERCIAL
APPLICATIONS!**



PHILIPS
Day-Brite

PHILIPS
CFI



A DIMENSION

- AR22CF**
 OPEN - 20" (508mm)
 FL- 20" (508mm)
 CL- 22-1/8" (562mm)
 DL - 22-3/4" (577.9mm)




- AR25CF**
 OPEN - 22-3/4" (577.9)
 FL- 22-3/4" (577.9mm)
 DL- 25-3/4 (654.1 mm)

B DIMENSION

- AR22CF**
 22-7/16" (569.9mm)
AR25CF
 25-3/8" (644.5mm)

DIMENSIONS/LOW BAY




FEATURES

- 26, 32, 42, or 57 watt compact fluorescent lamps.
- Universal voltage, 2-lamp electronic ballasts.
- Locking sockets
- Up to four levels of light by switching power to the ballasts.
- Dimming ballast options for up to 8 lamps (0-10V Advance Mark VII standard).
- Emergency ballast option.

ORDERING MATRIX

HIGH BAY SAMPLE CATALOG NUMBER: HCF826/32/42CU A24CF LOW BAY SAMPLE CATALOG NUMBER: HCF826/32/42CU LR28CF



ACCESSORIES (ORDER SEPARATELY)

- 24BE - Flat Tempered 24" Glass bottom Enclosure (A24CF only)
- 22FL - 22" Flat Acrylic lens (AR22CF only)
- 22CL - 22" Conical lens (AR22CF only)
- 22DL - 22" Drop Acrylic lens (AR22CF only)
- 25FL - 25" Flat Acrylic lens (AR25CF only)
- 25DL - 25" Drop Acrylic lens (AR25CF only)
- CH - Cover Half for Power Hook (use with PB)
- PB - Power Box for Power Hook (use with CH)
- HP12 - Hook-Cord-Plug Assembly 120V
- HP25 - Hook-Cord-Plug Assembly 208-240V
- HP27 - Hook-Cord-Plug Assembly 277V
- HMR - Suspension Hook Male
- LMR - Suspension Loop Male
- WGN24 - Wire Guard (A24CF only)
- WCG25-HCF - Wire cage for 22" and 25" Acrylic Reflectors
- WGA22 - Wire Guard 22" Acrylic
- WGA25 - Wire Guard 25" Acrylic

General Notes:

All accessories are field installed.
 GX24q lamp base only.
 All options are factory installed.
 Dimming ballasts are 0-10V standard.

Data subject to change without notice.

ENERGY DATA	LAMP WATTS	LAMP QUANTITY	INPUT WATTS
	26	6	165
		8	220
	32	6	204
		8	272
42	6	279	
	8	372	
57	4	248	



© 2013 Koninklijke Philips Electronics N.V. All rights reserved.
 Specifications are subject to change without notice.
 www.philips.com/luminaires

Philips Lighting Company
 200 Franklin Square Drive
 Somerset, NJ 08873
 Phone: 855-486-2216

Philips Lighting Company
 281 Hillmount Road
 Markham ON, Canada L6C 2S3
 Phone: 800-668-9008