


# 40471LW

## Decorative, Pendalyte 9" LED Pendant

Page 1 of 2



### Suspension

Catalog No.	Color	Description
404GLS	Gray	Track Mounting Kit
404BLS	Black	
404SKG	Gray	Cable/Straight Cord and Coil Cord 120" Length
404SKB	Black	
404S36	Gray	36" Length 5/8" Stem
404S36B	Black	
404S60	Gray	60" Length 5/8" Stem
404S60B	Black	
404S120	Gray	120" Length 5/8" Stem
4912CTCGR*	Gray	Direct to Ceiling Kit, Std. 9" Pendalyte
404SB5**	Black	120" 5-wire straight cord only
404SG5**	Gray	

\*Not compatible with Deco Kit

\*\*Dimming requires 5-wire suspension

### Power Head (Finish powder coated textured dark gray or titanium)

Catalog No.	Color	Lamp	Watts	CCT	Volts
40471LW27U	Gray	LED	20W	27K	Universal 120-277V
40471LW30U				30K	
40471LW35U				35K	
40471LW27UTM	Titanium			27K	
40471LW30UTM				30K	
40471LW35UTM				35K	

Complete Unit Consists of: Power Head, Reflector or Glass Shade & Suspension (order each separately)

### Reflector/Glass Shade

Cat. No.	Description
40411	Semi Specular Anodized Reflector
40413	Satin & Anodized Reflector
409WH	White Glass Shade
409BL	Cobalt Blue Glass Shade
409AB	Amber Glass Shade

### Optional Extension Kits


Catalog No.	Color	Description
404EXT300G5**	Gray	25' Extension Cable/Cord Kits
404EXT300***	Gray	
404EXTB***	Black	

\*\*Dimming requires 5-wire suspension

\*\*\* Use with Standard Cord or Deco Suspension Kits.

Job Information	Type:
Job Name:	
Cat. No.:	
Notes:	

## Decorative, Pendalyte 9" LED Pendant



### Features

- 1. Reflector/Glass Shade:** 16 gauge high purity anodized aluminum or pressed colored glass with inner white frit.
- 2. Power Head Housing:** Two-piece extruded aluminum. Removable door allows for ease of installation and servicing. Dark Gray or Titanium baked enamel powder coat finish.
- 3. Thermal Management:** Heat sink design maintains junction temperature for consistent, reliable performance and 50,000 hour lifetime at 70% lumen maintenance.
- 4. Suspension:** Cable/Cord: 1/16" Stainless Steel/SJT 18-3, Gray or Black. Cable/Coiled Cord: 1/16" Stainless Steel/SJT 18-3, Gray or Black. Stem: 5/8" Steel Tubing and Canopy, with 35° swivel hanger, Gray or Black finish.

### Electrical

**LED Board:** Array of (16) high brightness white LEDs.

#### Power Supply:

Input Voltage	120 Vac	277 Vac
50/60 Hz Input Frequency		
Input Current	0.3A	0.1A
1.05A LED Drive Current		
Input Power	28W (+/- 5%)	
20W LED Power		
Power Factor	0.92	

**Dimming:** Dimmable with 0-10V controls. Use 5-wire suspension.

### Labels

cULus listed. Suitable for damp locations.

**Note:** See Specification sheet 409DK for deco kits.



Philips Lightolier  
 e: lol.webmaster@philips.com  
 t: (508) 679-8131  
 w: www.lightolier.com

40471LW May 11, 2015

Specifications are subject to change without notice.  
 © Koninklijke Philips Electronics N.V., 2010. All rights reserved.