


(4) Ø 0.75
ANCHOR RODS

STREET SIDE



VERIFY BOLD LINE
IS 9.5" LONG


HAND HOLE THIS SIDE

HOUSE SIDE

Ø 9.50
BOLT CIRCLE

2 PIECE
BASE COVER

(2) CAPTIVE SCREW



- NOTES:
1. SUGGESTED BOLT CIRCLE: 9 1/2" DIAMETER.
 2. HADCO STRONGLY RECOMMENDS USING LEVELING NUTS TO MOUNT THE POST BASE. IF FOUNDATION IS NOT LEVEL, INCREASE "X" DIMENSION ACCORDINGLY WHEN USING LEVELING NUTS WITH WASHERS.

X = 2 3/4" MINIMUM WITH LEVELING NUTS.
X = 1 3/4" MINIMUM WITHOUT LEVELING NUTS.
 3. IF USING GROUTING TO CONCEAL GAP BETWEEN BASE AND FOUNDATION, ALLOW FOR WATER DRAINAGE.

HADCO by @ignify	CONFIDENTIAL: This drawing is confidential and proprietary to Signify Holdings and may not be reproduced in whole or in part without the express written consent of Signify Holdings. © 2018 Signify Holdings. All rights reserved.			TITLE: TEMP.AR,290	
	UNLESS OTHERWISE SPECIFIED: *ALL DIMENSIONS ARE IN INCHES. *ALL THREADS ARE UNC-2B OR UNF-2B AFTER COATING. *ALL THREADS ARE TO BE VERIFIED WITH A THREAD GAGE.	DRAWN BY: M.N. BANKERT	DATE: 3/5/97	MATERIAL: 17X 22 WHITE BOND PAPER,	
		CHECKED BY: B. DORON	DATE: 8/4/09		
		APPR BY: E. HADDAD	DATE: 3/5/97		
* DO NOT SCALE THIS DRAWING *		EF-04-01-11 Rev.09	SCALE 1:1	SHEET 1 OF 1	PART NO: 101700455