

# PHILIPS

## Flourish table light

Hue White and color  
ambiance

Includes E26 LED bulb

White

Smart control with Hue Bridge\*

Control with your voice\*



40904/31/U7



## Limitless possibilities

Create the perfect ambiance and get a diffused light for any occasion with the white and color ambiance Flourish table lamp, whether it's relaxing on the couch, reading a book or adding a color accent to create the perfect ambiance.

### Limitless possibilities

- Be creative with 16 million colors
- Sync lights with music and movies
- Create your ambiance with warm white to cool daylight


# Highlights

## Be creative with colors



Play with light and choose from 16 million colors to instantly change the look and atmosphere of your room. Set the scene effortlessly with one touch of a button. Use a favourite photo and relive that special moment with splashes of light. Save your favourite light settings and recall them whenever you want with the tap of a finger

## Sync with music and movies



Extend your TV viewing experience to the whole room or sync light to your favorite music and see how light reacts to the rhythm. Download the third party apps and discover the amazing things you can do with Philips Hue.

## Create your ambiance



Set the right ambiance for any moment and decorate your home with warm to cool white light. Enjoy different styles throughout the year, no matter if it's the crisp white light reminding you of a spring breeze, the warm white light of a summer sun, or the ice cool daylight of winter.

# Specifications

## Design and finishing

- Color: white
- Material: glass

## Miscellaneous

- Especially designed for: Living- & Bedroom, Home office & Study
- Style: Contemporary
- Type: Table lamp
- EyeComfort: No

## Power consumption

- Energy Efficiency Label (EEL): built in LED + bulb of class A+

## Product dimensions & weight

- Cable length: 1.8 m
- Height: 6.9 inch
- Length: 10.3 inch
- Net weight: 2.510 lb
- Width: 10.3 inch

## Service

- Warranty: 2 year(s)

## Technical specifications

- Lifetime up to: 25,000 hour(s)
- Lumen output bulb included: 800 lumen
- Light source equivalent to traditional bulb of: 60 W
- Total lumen output fixture: 800 lm
- Light color: cool white
- Mains power: 50-60 Hz
- Fixture dimmable: Yes
- LED: Yes
- Built in LED: Yes
- Energy class included light source: built in LED + bulb of class A+
- Fixture is compatible with bulb(s) of class: A++ to E
- Number of bulbs: 1
- Fitting/cap: E26
- Wattage bulb included: 10 W
- Maximum wattage replacement bulb: 10 W
- IP code: IP20
- Class of protection: II - double insulated
- Light source replaceable: Yes

**Packaging dimensions and weight**

- EAN/UPC – product: 046677802325
- Net weight: 1.138 kg
- Gross weight: 1.701 kg
- Height: 255.000 mm
- Length: 328.000 mm
- Width: 328.000 mm
- Material number (12NC): 915005689201



Issue date: 2023-11-08  
Version: 0.53

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)