

Project: \_\_\_\_\_


Location: \_\_\_\_\_

Cat.No: \_\_\_\_\_

Type: \_\_\_\_\_

Lamps: \_\_\_\_\_ Qty: \_\_\_\_\_

Notes: \_\_\_\_\_



### Ordering Guide

Example: FPB 4 1 12 A

Product Code	FPB	Flower Pot Bracket
Pole Diameter	4	4"
	5	5"
# of Arms	1	One
	2	Two at 180°
Length	12	12"
Finish	A	Black
	B	White
	G	Verde
	H	Bronze
	J	Green

### Specifications

#### FINISH:

Thermoset polyester powdercoat is electrostatically applied after a five-stage conversion cleaning process and bonded by heat fusion thermosetting. Laboratory tested for superior weatherability and fade resistance in accordance with ASTM B117 specifications. For larger projects where a custom color is required, contact the factory for more information.

#### WARRANTY:

Three-year limited warranty.

