



PHILIPS
myLiving
Floor lamp
Drin
black



42261/30/16

Living the moment with joy

Add some retro flair to your home with this classic black floor lamp. It radiates warm white light and you can adjust the height. Direct the light exactly where you need it and settle with a good book in your sofa.

Special characteristics

- On/off switch on cable

Curved shapes for perfect harmony

- Timeless materials

High light quality and strong light output

- Diffused warm white light
- Energy saving

PHILIPS

Highlights

On/off switch on cable



With the switch discreetly integrated onto the cable, you can easily switch the lamp on and off.

Timeless materials

The use of metal and glass gives a neutral and elegant look to your home. Solid, uncomplicated materials appeal to every contemporary mind.

Diffused warm white light



This light uses the latest energy-saver lamp technology by Philips to provide a flood of warm white natural light. Its diffused light will illuminate your room with warm white light, allowing you to combine functionality and respect for the environment. Diffused light is perfect for general illumination.

Energy saving



This Philips light conserves energy compared to traditional light sources, helping you to save money on your electricity bills and do your bit for the environment.

Specifications

Design and finishing

- Color: black
- Material: metal

Extra feature/accessory incl.

- Fluorescent lamp(s) included: Yes
- On/off switch on wire: Yes
- Tilttable head (up-down): Yes

Miscellaneous

- Especially designed for: Living- & Bedroom
- Style: Contemporary
- Type: Floor lamp
- EyeComfort: No

Power consumption

- Energy Efficiency Label: A

Product dimensions & weight

- Height: 191 cm
- Length: 25 cm
- Net weight: 3.620 kg
- Width: 36 cm

Service

- Warranty: 2 year(s)

Technical specifications

- Lifetime up to: 10,000 hour(s)
- Total lumen output fixture (hidden): 1,570 lumen
- Lumen output bulb included: 1,570 lumen
- Light source equivalent to traditional bulb of: 110 W
- Bulb technology: fluorescent, 230 V
- Light color: warm white
- Mains power: Range 220 V - 240 V, 50-60 Hz
- Fixture dimmable: No
- LED: No
- Built in LED: No
- Energy class included light source: A
- Fixture is compatible with bulb(s) of class: A+ to E
- Number of bulbs: 1
- Fitting/cap: E27
- Wattage bulb included: 23 W

- Maximum wattage replacement bulb: 42 W
- IP code: IP20, protection against objects bigger than 12.5 mm, no protection against water
- Class of protection: II - double insulated

Packaging dimensions & weight

- SAP EAN/UPC - Piece: 8718291439752
- Height: 115.1 cm
- SAP Gross Weight EAN (Piece): 4.970 kg
- Weight: 4.970 kg
- Net Weight (Piece): 3.620 kg
- SAP Length (Piece): 0.000 mm
- SAP Width (Piece): 0.000 mm
- Width: 24.8 cm
- Length: 28.8 cm



Issue date: 2019-04-22
Version: 0.409

© 2019 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com