


GreenUp Highbay 飞利浦LED高天棚灯

BY550P PSD/BY550X ACW2


Mounting instruction/ 安装说明

4441 700 96391



产品名称 Description	色温 Color	配光 Optics	重量 Weight	系统功率 Wattage
BY550P(X) LED200/CW PSD WB (ACW2 IS WB)	CW	WB	6.3kg	160W
BY550P(X) LED200/CW PSD NB (ACW2 IS NB)		NB		
BY550P(X) LED200/CW PSD HRO (ACW2 IS HRO)		HRO		
BY550P(X) LED200/NW PSD WB (ACW2 IS WB)	NW	WB		
BY550P(X) LED200/NW PSD NB (ACW2 IS NB)		NB		
BY550P(X) LED200/NW PSD HRO (ACW2 IS HRO)		HRO		
BY550P(X) LED140/CW PSD WB (ACW2 IS WB)	CW	WB	5.5kg	110W
BY550P(X) LED140/CW PSD NB (ACW2 IS NB)		NB		
BY550P(X) LED140/CW PSD HRO (ACW2 IS HRO)		HRO		
BY550P(X) LED140/NW PSD WB (ACW2 IS WB)	NW	WB		
BY550P(X) LED140/NW PSD NB (ACW2 IS NB)		NB		
BY550P(X) LED140/NW PSD HRO (ACW2 IS HRO)		HRO		
BY550P(X) LED100/CW PSD WB (ACW2 IS WB)	CW	WB	3.5kg	80W
BY550P(X) LED100/CW PSD NB (ACW2 IS NB)		NB		
BY550P(X) LED100/CW PSD HRO (ACW2 IS HRO)		HRO		
BY550P(X) LED100/NW PSD WB (ACW2 IS WB)	NW	WB		
BY550P(X) LED100/NW PSD NB (ACW2 IS NB)		NB		
BY550P(X) LED100/NW PSD HRO (ACW2 IS HRO)		HRO		

Dimensions 尺寸




Type 型号	Dimension 尺寸(mm)			
	L	W	H	S
BY550P LED200 PSD BY550X LED200 ACW2	720	380	77	522
BY550P LED140 PSD BY550X LED140 ACW2	720	380	77	522
BY550P LED100 PSD BY550X LED100 ACW2	440	380	77	250


Philips (China) Investment Co., Ltd.
Address: Room 1602-1605, No.218 Tianmuxe Road, Shanghai, P.R. China
Postalcode: 200070
飞利浦（中国）投资有限公司
地址：中国上海市天目西路218号1602-1605
邮编：200070

PHILIPS

Installation 安装应用 Suspending/悬吊安装



Adjust to be balance
调节平衡




Rope slings should be big enough for installation.
为了便于安装吊绳扣应该大一些




Note: Hanging hook must be inserted the hole completely at the label location. Check it is not pulled from the mounting hole.
注意: 挂钩插入标示安装孔位且其上的卡扣必须完全嵌入安装孔中, 检查其不能往回拔出安装孔方为安装到位!

Electric connection/电器连接

Using screw driver to
open the DALI board
用螺丝刀打开DALI接线板




Using screw driver to
open the terminal board
用螺丝刀打开接线板



Connect DALI cable/连接调光控制线


* Only for PSD and ACW2 type / 仅适用于PSD和ACW2型号



2x0.5mm² -1.5 mm²

For ACW2 type, DALI port maximum load is 3 DALI luminaire.
ACW2版本的DALI输出口最大负载灯具数量为3套

1 HRO应用实例 HRO application



Photometric direction

*灯具的发光方向与悬挂附件垂直
The lighting direction is perpendicular to suspension accessories.

Commissioning tool (optional) 系统调试工具 (可选)

- 1.1 遥控器型号: IRT9090/01 Extended IR Programming Tool
遥控器12NC: 913700359103
- 1.1 Remote control type: IRT9090/01 Extended IR Programming Tool
Remote control 12NC: 913700359103
- 1.2 遥控器用于组网和灯具工作模式设定
- 1.2 Remote control is used for zoning and operation model programming of luminaires
- 1.3 详细使用说明请参考遥控器操作手册
- 1.3 Detailed operating instructions refers to manual of remote control



1. The luminaire shall be installed by a qualified electrician and wired in accordance with the latest IEE electrical regulations or the national requirements.

灯具应由有资格的电工安装, 接线要符合IEE电气标准或国家标准。

2. The luminaire is complied to IEC 60598-1 ed. 6 or GB 7000.1-2007.

此灯具是依据IEC 60598-1 ed. 6 或国标GB 7000.1-2007所制造。

3. In order to ensure optimum performance, please clean the luminaire regularly (recommended twice a year). While cleaning the luminaire, please use a soft cotton pad only.

为了保持灯具明亮效果, 请定期 (半年一次) 进行清洁。灯具清洁时请使用软布擦拭。

4. This luminaire is only suitable for 5-13 meters high indoor usage. And not suitable for the corrosive environment and area prone to hurricane and extreme winds.

本灯具适用于安装在室内5-13m高空使用。且不适合安装在会产生酸碱性腐蚀的环境及海边、港口等强台风多发地区。