





220 V 240 V










































_							
		LED18S	LED22S	LED34S	LED40S	LED60S	LED80S
	Ipeak [A]	21	21	21	21	21	4,5
	Twidth [μs]	280	280	280	280	280	1000
		Max. Nr of products					
	Drivers / MCB 16A type B [max.]	24	24	24	24	24	18
	Drivers / MCB 10A type B [max.]	15	15	15	15	15	11
	Drivers / MCB 16A type C [max.]	40	40	40	40	40	30
	Drivers / MCB 10A type C [max.]	24	24	24	24	24	18



## Maintenance instructions

To assure the lighting quality of this unique LED lighting concept there are only a few instructions regarding the maintenance of this LED luminaire:

- \* Do not stare into LED light beam.
- \* The luminaire shall be installed by a qualified electrician and wired in accordance with the latest IEE electrical regulations or the national requirements.
- \* Above average concentration of sulfur effects the useful lifetime of the product. E.g. Light color changes from white to blue. Typically in chicken & pig farms.

