


GreenPerform Highbay II 飞利浦LED高天棚灯

BY688P/BY689P

Mounting instruction / 安装说明书


4441 000 86781



产品名称 Description	色温 Color	配光 Optics	重量 Weight	系统功率 Wattage
BY688P LED140/CW PSU WB	CW	WB	7kg	140W
BY688P LED140/CW PSU NB		NB		
BY688P LED140/NW PSU WB	NW	WB	7kg	140W
BY688P LED140/NW PSU NB		NB		
BY689P LED90/CW PSU WB	CW	WB	5kg	90W
BY689P LED90/CW PSU NB		NB		
BY689P LED90/NW PSU WB	NW	WB	5kg	90W
BY689P LED90/NW PSU NB		NB		

Dimensions 尺寸


Type 型号	Dimension 尺寸 (mm)		
	D	W	H
BY688P	Φ457	466	158
BY689P	Φ366	374	153





安装附件/Mounting accessories
1. 挂钩组件/Mounting hook 2. 支架组件/Mounting bracket
a. Hook a. BY618Z MB
b. BY619Z MB

1 Installation 安装应用

Hook mounting/吊装





Pipe mounting/杆装



Pipe dim.
铁管尺寸

Bracket mounting/支架安装



2 Connect entry cable

Please use IP65 or above waterproof terminal block, it is not provided by Philips.

连接电源线

请使用IP65以上的接线盒 (接线端子尺寸不小于10x20x25mm), 飞利浦不提供接线盒。

Cable/外部接线:

- 60227IEC53 3x1.0~1.5mm²
- 60245IEC57 3x1.0~1.5mm²

外部3芯线定义如下:

- 棕Brown - L
- 黄绿YellowGreen - G
- 蓝Blue - N

- The luminaire shall be installed or maintained By a qualified electrician and wired in accordance with the latest IEE electrical regulations or the national requirements.
灯具应由有资格的电工安装或维修, 接线要符合IEE 电气标准或国家标准。
- The luminaire shall ,under no circumstance,be covered with insulation matting or similar material.
灯具不适合被隔热或类似材料覆盖。
- The cable of the luminaire should use “Y” type connection. It should be maintained by professional electrician.
灯具电源线使用Y型连接, 电源线损坏需专业人士更换。