




BDPI00 / BDPI01 / BDPI02 / BDPI03 / BDPI04

Instruzioni di montaggio

Monteringsvejledning

Instrukcja montażu




 830	 840	 850	MCB B 16A	Inrush current
W	W	W	PCS	A / μ s

12NC 4427 101 46650
Versiondate: 16/12/2013
Data subject to change without notice
Printed in Poland
www.philips.com/lighting


PHILIPS

For version without cable


1




2




3




4




5




6




7



8




1b




⊕		Ⓝ blue Ⓟ yellow-green Ⓛ brown	⊕		Ⓝ blue Ⓛ brown
⊕		Ⓝ grey Ⓟ black Ⓛ yellow-green Ⓝ blue Ⓛ brown	⊕		Ⓝ grey Ⓟ black Ⓛ blue Ⓛ brown
⊕		Ⓛ black Ⓝ yellow-green Ⓟ blue Ⓛ brown	⊕		Ⓛ black Ⓝ blue Ⓛ brown

2b





3b



4b


Ø mm
Ø 90 - BDP...90PA...




Ø mm
Ø 48 - BDP...48P...
Ø 60 - BDP...62P...
Ø 76 - BDP...76P...

5b

Ø mm
Ø 90 - BDP...90PA...




Ø mm
Ø 48 - BDP...48P...
Ø 60 - BDP...62P...
Ø 76 - BDP...76P...





BDP ... DS ...

LOGO




BDP ... DN ...
BDP ... DM ...
BDP ... DW ...

LOGO




BDP ... DDFx ...

DYNADIMMER



BDP ... LS-x ...

LUMISTEP



BDP ... RF ...

RF LLC7300/00 - STARSSENSE WIRELESS 1-10V/DALI

Designed for collaboration with the system LFC 7300/00 Stersense Wireless SC Kit - 913700344403. See installation instructions for system.

Operating frequency 868,3 MHz; emission of power short range devices below 25mW.

WARNING!!! The 2 barcodes, stuck on the spigot, must not be removed, lost, damaged or even thrown away before the network is fully addressed (meaning: all the barcodes must be scanned).

